# JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD.


# AD-DTC114T Series Digital Transistor (Built-In Resistors)

# AD-DTC114TM/DTC114TE/DTC114TUA/DTC114TKA /DTC114TCA/DTC114TSA Digital transistor (NPN)


# FEATURES

- Built-in bias resistors enable the configuration of an inverter circuit without connecting external input resistors (see equivalent circuit)
- The bias resistors consist of thin-film resistors with complete isolation to allow negative biasing of the input. They also have the advantage of almost completely eliminating parasitic effects.
- Only the on/off conditions need to be set for operation, making device design easier
- AEC-Q101 qualified

# **PIN CONNECTIONS**



## **EQUIVALENT CIRCUIT**



# **ORDERING INFORMATION**

Part number	Marking	Package	Packing method	Pack quantity
AD-DTC114TM	04	SOT-723	Reel	8000pcs/reel
AD-DTC114TE	04	SOT-523	Reel	3000pcs/reel
AD-DTC114TUA	04	SOT-323	Reel	3000pcs/reel
AD-DTC114TKA	04	SOT-23-3L	Reel	3000pcs/reel
AD-DTC114TCA	04	SOT-23	Reel	3000pcs/reel
AD-DTC114TSA	<b>C</b> 114 T XXX <sup>1)</sup>	TO-92S	Bulk	1000pcs/bag
AD-DTC114TSA-TA	<b>C</b> 114 T XXX <sup>1)</sup>	TO-92S	Таре	3000pcs/box

1) XXX = Date code


# MAXIMUM RATINGS (T<sub>j</sub> = 25°C unless otherwise specified)

Parameter	Symbol			Va	lue			Unit
		М	Е	UA	KA	СА	SA	
Collector-base voltage	V <sub>CBO</sub>			5	0			V
Collector-emitter voltage	V <sub>CEO</sub>	50						V
Emitter-base voltage	$V_{\text{EBO}}$	5						V
Collector current -continuous	lc			1(	00			mA
Power dissipation	PD	100	150	200	200	200	300	mW
Operating junction and storage temperature range	T <sub>j</sub> , T <sub>stg</sub>			-55 ~	+150			°C


# ELECTRICAL CHARACTERISTICS ( $T_j = 25^{\circ}C$ unless otherwise specified)


Parameter	Symbol	Test condition	Min	Тур	Мах	Unit
Collector-base breakdown voltage	V <sub>(BR)CBO</sub>	$I_{C} = 50 \mu A, I_{E} = 0 A$	50	-	-	
Collector-emitter breakdown voltage	V <sub>(BR)CEO</sub>	I <sub>C</sub> = 1mA, I <sub>B</sub> = 0A	50	-	-	V
Emitter-base breakdown voltage	V <sub>(BR)EBO</sub>	$I_{E} = 50 \mu A, I_{C} = 0 A$	5	-	-	
Collector cut-off current	I <sub>СВО</sub>	$V_{CB} = 50V, I_E = 0A$	-	-	0.5	μA
Emitter cut-off current	I <sub>EBO</sub>	$V_{EB} = 4V, I_{C} = 0A$	-	-	0.5	μA
Collector-emitter saturation voltage	V <sub>CE(sat)</sub>	$I_{\rm C}$ = 10mA, $I_{\rm B}$ = 1mA	-	-	0.3	V
DC current gain	h <sub>FE</sub>	V <sub>CE</sub> = 5V, I <sub>C</sub> = 1mA	100	300	600	-
Input resistor	R <sub>1</sub>		7	10	13	kΩ
Transition frequency	f⊤	V <sub>CE</sub> = 10V, I <sub>E</sub> = 5mA, f = 100MHz	-	250	-	MHz


# **TYPICAL CHARACTERISTICS**



# SOT-723 PACKAGE OUTLINE DIMENSIONS








Sumbol	Dimensions	In Millimeters	Dimension	s In Inches
Symbol	Min.	Max.	Min.	Max.
A	0.430	0.500	0.017	0.020
A1	0.000	0.050	0.000	0.002
b	0.170	0.270	0.007	0.011
b1	0.270	0.370	0.011	0.015
С	0.080	0.150	0.003	0.006
D	1.150	1.250	0.045	0.049
E	1.150	1.250	0.045	0.049
E1	0.750	0.850	0.030	0.033
е	0.80	0.800TYP.		1TYP.
θ	7° F	REF.	7° F	REF.


# SOT-723 SUGGESTED PAD LAYOUT



- 1. Controlling dimension in millimeters.
- 2. General tolerance: ±0.05mm.
- 3. The pad layout is for reference purpose only.

# SOT-723 TAPE AND REEL

#### SOT-723 Embossed Carrier Tape




Packaging Description:


SOT-723 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 8,000 units per 7" or 17.8cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

Dimensions are in millimeter										
Pkg type	A	В	С	d	E	F	P0	Р	P1	W
SOT-723	1.33	1.45	0.61	Ø1.50	1.75	3.50	4.00	2.00	2.00	8.00

#### SOT-723 Tape Leader and Trailer




SOT-723 Reel





Dimensions are in millimeter									
Reel Option	D	D1	D2	G	н	1	W1	W2	
7"Dla	Ø178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50	12.30	

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)	G.W.(kg)
8000 pcs	7 inch	120,000 pcs	203×203×195	480,000 pcs	438×438×220	

#### www.jscj-elec.com SOT-523 PACKAGE OUTLINE DIMENSIONS








Symbol	Dimensions	In Millimeters	Dimension	s In Inches
Symbol	Min.	Max.	Min.	Max.
A	0.700	0.900	0.028	0.035
A1	0.000	0.100	0.000	0.004
A2	0.700	0.800	0.028	0.031
b1	0.150	0.250	0.006	0.010
b2	0.250	0.350	0.010	0.014
С	0.100	0.200	0.004	0.008
D	1.500	1.700	0.059	0.067
E	0.700	0.900	0.028	0.035
E1	1.450	1.750	0.057	0.069
e	0.500	TYP.	0.020	TYP.
e1	0.900	1.100	0.035	0.043
L	0.400	REF.	0.016	REF.
L1	0.260	0.460	0.010	0.018
θ	0°	8°	0°	8°


# SOT-523 SUGGESTED PAD LAYOUT



- 1. Controlling dimension in millimeters.
- 2. General tolerance: ±0.05mm.
- 3. The pad layout is for reference purpose only.

### SOT-523 TAPE AND REEL

#### SOT-523 Embossed Carrier Tape




#### Packaging Description:


SOT-523 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 3,000 units per 7" or 17.8cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

Dimensions are in millimeter										
Pkg type	A	В	С	d	E	F	P0	Р	P1	W
SOT-523	1.85	1.85	0.875	Ø1.50	1.75	3.50	4.00	4.00	2.00	8.00

#### SOT-523 Tape Leader and Trailer




SOT-523 Reel





Dimensions are in millimeter									
Reel Option	D	D1	D2	G	н	L	W1	W2	
7"Dia	Ø178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50	12.30	

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)	G.W.(kg)
3000 pcs	7 inch	45,000 pcs	203×203×195	180,000 pcs	438×438×220	

# www.jscj-elec.com SOT-323 PACKAGE OUTLINE DIMENSIONS








Symbol	Dimensions	In Millimeters	Dimension	s In Inches
Symbol	Min	Max	Min	Max
A	0.900	1.100	0.035	0.043
A1	0.000	0.100	0.000	0.004
A2	0.900	1.000	0.035	0.039
b	0.200	0.400	0.008	0.016
С	0.080	0.150	0.003	0.006
D	2.000	2.200	0.079	0.087
E	1.150	1.350	0.045	0.053
E1	2.150	2.450	0.085	0.096
е	0.650	) TYP	0.026	TYP
e1	1.200	1.400	0.047	0.055
L	0.525	REF	0.021	REF
L1	0.260	0.460	0.010	0.018
θ	0°	8°	0°	8°


# SOT-323 SUGGESTED PAD LAYOUT



- 1. Controlling dimension in millimeters.
- 2. General tolerance: ±0.05mm.
- 3. The pad layout is for reference purpose only.

## SOT-323 TAPE AND REEL

#### SOT-323 Embossed Carrier Tape




#### Packaging Description:


SOT-323 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 3,000 units per 7" or 17.8cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

				Dimensions a	ire in millime	ter				
Pkg type	A	В	С	d	E	F	P0	Р	P1	W
SOT-323	2.25	2.55	1.19	Ø1.55	1.75	3.50	4.00	4.00	2.00	8.00

A-A

#### SOT-323 Tape Leader and Trailer








			Dimensio	ons are in millime	ter	V.2.4	1.2	
Reel Option	D	D1	D2	G	н	L	W1	W2
7"Dia	Ø178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50	12.30

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)	G.W.(kg)
3000 pcs	7 inch	45,000 pcs	203×203×195	180,000 pcs	438×438×220	

# SOT-23-3L PACKAGE OUTLINE DIMENSIONS








Symbol	<b>Dimensions</b> In	n Millimeters	Dimension	s In Inches
Symbol	Min.	Max.	Min.	Max.
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
С	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E1	1.500	1.700	0.059	0.067
E	2.650	2.950	0.104	0.116
е	0.950(	BSC)	0.037	(BSC)
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°


# SOT-23-3L SUGGESTED PAD LAYOUT



- 1. Controlling dimension in millimeters.
- 2. General tolerance: ±0.05mm.
- 3. The pad layout is for reference purpose only.

# SOT-23-3L TAPE AND REEL

#### SOT-23-3L Embossed Carrier Tape




Packaging Description:


SOT-23-3L parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 3,000 units per 7" or 18.0cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

				Dimensions a	are in millime	ter				
Pkg type	Pkg type A B C d E F P0 P P1 W									
SOT-23-3L	3.18	3.28	1.32	Ø1.50	1.75	3.50	4.00	4.00	2.00	8.00

# SOT-23-3L Tape Leader and Trailer




SOT-23-3L Reel





		1.0	Dimensio	ons are in millime	ter			(0)
Reel Option	D	D1	D2	G	н	1	W1	W2
7"Dia	Ø180.00	60.00	13.00	R78.00	R25.60	R6.50	9.50	13.10

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)	G.W.(kg)
3000 pcs	7 inch	30,000 pcs	203×203×195	120,000 pcs	438×438×220	

# www.jscj-elec.com SOT-23 PACKAGE OUTLINE DIMENSIONS








Symbol	Dimensions	In Millimeters	Dimension	s In Inches
Symbol	Min	Max	Min	Max
Α	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
С	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
е	0.950	TYP	0.037	' TYP
e1	1.800	2.000	0.071	0.079
L	0.550	REF	0.022	REF
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	<mark>8</mark> °


# SOT-23 SUGGESTED PAD LAYOUT



- 1. Controlling dimension in millimeters.
- 2. General tolerance: ±0.05mm.
- 3. The pad layout is for reference purpose only.

# SOT-23 TAPE AND REEL

#### SOT-23 Embossed Carrier Tape




#### Packaging Description:


SOT-23 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 3,000 units per 7" or 17.8cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

	-			Dimensions a	re in millime	ter				
Pkg type	А	В	С	d	E	F	P0	Р	P1	W
SOT-23	3.15	2.77	1.22	Ø1.50	1.75	3.50	4.00	4.00	2.00	8.00

#### SOT-23 Tape Leader and Trailer



SOT-23 Reel





			Dimensio	ns are in millimet	ter				
Reel Option	Reel Option         D         D1         D2         G         H         I         W1         W2								
7"Dia	Ø178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50	12.30	

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)	G.W.(kg)
3000 pcs	7 inch	45,000 pcs	203×203×195	180,000 pcs	438×438×220	

#### www.jscj-elec.com


# **TO-92S PACKAGE OUTLINE DIMENSIONS**






Cumhal	Dimensions	In Millimeters	Dimension	s In Inches
Symbol	Min.	Max.	Min.	Max.
A	1.420	1.620	0.056	0.064
A1	0.660	0.860	0.026	0.034
b	0.330	0.480	0.013	0.019
b1	0.400	0.510	0.016	0.020
С	0.330	0.510	0.013	0.020
D	3.900	4.100	0.154	0.161
D1	2.280	2.680	0.090	0.106
E	3.050	3.250	0.120	0.128
е	1.27	0 TYP.	0.050	TYP.
e1	2.440	2.640	0.096	0.104
L	15.100	15.500	0.594	0.610
θ	45°	TYP.	45°	TYP.

# **TO-92S SUGGESTED PAD LAYOUT**




- 1. Controlling dimension in millimeters.
- 2. General tolerance: ±0.05mm.
- 3. The pad layout is for reference purpose only.

# **TO-92S PACKAGE TAPING DIMENSION**



	Dimiensions are in millimeter									
A1	A	Т	Р	P0	P2	F1	F2	W		
4.0	3.15	1.52	12.7	12.7	6.35	2.5	2.5	18.0		
W0	W1	W2	Н	H0	D0	t1	t2	ΔΡ		
6.0	9.0	1.0	19.0	16.0	4.0	0.4	0.2	0		



Package	Box	Box Size(mm)	Carton	Carton Size(mm)	
TO-92S	3000 pcs	333×162×43	30,000 pcs	350×340×250	

# PUBLISHED BY

# JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD. 13th Floor, C Block, Tengfei Building, Yan Chuang Yuan, Nanjing Jiangbei New Area, China

# LEGAL DISCLAIMER

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples, hints or typical values stated herein and/or any information regarding the application of the device, JSCJ hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of JSCJ in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

#### INFORMATION

For further information on technology, delivery terms and conditions as well as prices, please contact your nearest JSCJ office (<u>www.jscj-elec.com</u>).

# WARNINGS

Due to technical requirements, products may contain dangerous substances. For information on the types in question, please contact your nearest JSCJ office.

Except as otherwise explicitly approved by JSCJ in a written document signed by authorized representatives of JSCJ, JSCJ's products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.