AUTOMOTIVE

RoHS

COMPLIANT

HALOGEN FREE



www.vishay.com

Vishay General Semiconductor

Surface-Mount Ultrafast Plastic Rectifier



SMC (DO-214AB)



LINKS TO ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS					
I _{F(AV)}	3.0 A				
V _{RRM}	300 V, 400 V				
I _{FSM}	100 A				
t _{rr}	35 ns				
V _F at I _F	1.1 V				
T _J max.	150 °C				
Package	SMC (DO-214AB)				
Circuit configuration	Single				

FEATURES

- Glass passivated pellet chip junction
- Ideal for automated placement
- · Ultrafast reverse recovery time
- · Low switching losses, high efficiency
- High forward surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified available
 - Automotive ordering code: base P/NHE3 or P/NHM3
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

TYPICAL APPLICATIONS

For use in high frequency rectification and freewheeling application in switching mode converters and inverters for consumer, computer, and telecommunication.

MECHANICAL DATA

Case: SMC (DO-214AB)

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade

Base P/N-M3 - haloge-free, RoHS-compliant, and commercial grade

Base P/NHE3_X - RoHS-compliant, AEC-Q101 qualified Base P/NHM3_X - halogen-free, RoHS-compliant, and AEC-Q101 qualified

("_X" denotes revision code e.g. A, B,)

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3, M3, HE3, and HM3 suffix meet JESD 201 class 2 whisker test

Polarity: color band denotes cathode end

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	ES3F	ES3G	UNIT	
Device marking code		EF	EG		
Maximum repetitive peak reverse voltage	V_{RRM}	300	400	V	
Working peak reverse voltage	V_{RWM}	225	300	V	
Maximum RMS voltage	V _{RMS}	210	280	V	
Maximum average forward rectified current at T _L = 110 °C	I _{F(AV)}	3.0		А	
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	100		А	
Operating junction and storage temperature range	T _{J,} T _{STG}	-55 to +150		°C	



Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)						
PARAMETER	TEST CONDITIONS		SYMBOL	ES3F	ES3G	UNIT
Maximum instantaneous forward voltage	3.0 A		V _F ⁽¹⁾	1.1		V
Maximum DC reverse current at working peak reverse voltage		T _A = 25 °C T _A = 100 °C	I _R		0 50	μΑ
Maximum reverse recovery time	I _F = 0.5 A, I _R = 1.0 A, I _{rr} = 0.25 A		t _{rr}	35		ns
Maximum reverse recovery time	$I_F = 1.0 \text{ A}, \text{ dI/dt} = 100 \text{ A/}\mu\text{s}, \\ V_R = 30 \text{ V}, I_{rr} = 0.1 I_{RM}$		t _{rr}	50		ns
Maximum reverse recovery current	$I_F = 1.0 \text{ A}, \text{ dI/dt} = 100 \text{ A/}\mu\text{s}, \\ V_R = 30 \text{ V}, I_{rr} = 0.1 I_{RM}$		I _{RM}	3.0		А
Maximum stored charge	$I_F = 1.0 \text{ A}, \text{ dI/dt} = 100 \text{ A/}\mu\text{s}, \\ V_R = 30 \text{ V}, I_{rr} = 0.1 I_{RM}$		Q _{rr}	50		nC
Typical junction capacitance	4.0 V, 1 MHz		CJ	30		pF

Note

⁽¹⁾ Pulse test: 300 µs pulse width, 1 % duty cycle

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	ES3F	ES3G	UNIT	
Typical thermal resistance	R _{0JA} (1)	50		- °C/W	
Typical thermal resistance	R _{θJL} ⁽¹⁾	15			

Note

⁽¹⁾ Units mounted on PCB 5.0 mm x 5.0 mm (0.013 mm thick) land areas

ORDERING INFORMATION (Example)					
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE	
ES3G-E3/57T	0.211	57T	850	7" diameter plastic tape and reel	
ES3G-E3/9AT	0.211	9AT	3500	13" diameter plastic tape and reel	
ES3GHE3_A/H (1)	0.211	Н	850	7" diameter plastic tape and reel	
ES3GHE3_A/I (1)	0.211	I	3500	13" diameter plastic tape and reel	
ES3G-M3/57T	0.211	57T	850	7" diameter plastic tape and reel	
ES3G-M3/9AT	0.211	9AT	3500	13" diameter plastic tape and reel	
ES3GHM3_A/H (1)	0.211	Н	850	7" diameter plastic tape and reel	
ES3GHM3_A/I (1)	0.211	I	3500	13" diameter plastic tape and reel	

Note

(1) AEC-Q101 qualified



Vishay General Semiconductor

RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)




Fig. 1 - Maximum Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 4 - Typical Reverse Leakage Characteristics




Fig. 5 - Reverse Switching Characteristics




Fig. 6 - Typical Junction Capacitance



Vishay General Semiconductor






Fig. 7 - Forward Power Loss Characteristics

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

SMC (DO-214AB)



Mounting Pad Layout





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.