


www.vishay.com

Vishay Semiconductors

Standard 7-Segment Display 13 mm



DESCRIPTION

The TDS.51.. series are 13 mm character seven segment LED displays in a very compact package.

The displays are designed for a viewing distance up to 7 m and available in four bright colors. The grey package surface and the evenly lighted untinted segments provide an optimum on-off contrast.

All displays are categorized in luminous intensity groups. That allows users to assemble displays with uniform appearence. Typical applications include instruments, panel meters, point-of-sale terminals and household equipment.

Due to the design of 13 mm displays, a certain amount of cross-talk between segments is unavoidable. This light leakage becomes more noticeable as the brightness of the operated segments increases. However, higher environmental illumination, or a partially transparent cover, may reduce this effect. Therefore, it's important to consider this phenomenon during design-in and to validate suitability for the particular application and all its operation modes.

FEATURES

- Evenly lighted segments
- · Grey package surface
- · Untinted segments
- · Luminous intensity categorized
- · Yellow and green categorized for color
- · Wide viewing angle
- · Suitable for DC and high peak current
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



- Panel meters
- Test- and measure-equipment
- · Point-of-sale terminals
- Control units
- TV sets

PRODUCT GROUP AND PACKAGE DATA

Product group: DisplayPackage: 13 mm

Product series: Standard
Angle of half intensity: ± 50°

PARTS TABLE															
PART	COLOR	LUMINOUS INTENSITY (µcd)		at I _F (mA)	WAVELENGTH (nm)		at I _F (mA)	FORWARD VOLTAGE (V)		at I _F (mA)	CIRCUITRY				
		MIN.	TYP.	MAX.		MIN.	TYP.	MAX.		MIN. TYP. MAX.		MAX.			
TDSO5150	Orange red	700	5000	-	10	612	-	625	10	-	2	3	20	Common anode	
TDSO5150-LM	Orange red	2800	-	9000	10	612	-	625	10	-	2	3	20	Common anode	
TDSO5160	Orange red	700	5000	-	10	612	-	625	10	-	2	3	20	Common cathode	
TDSO5160-LM	Orange red	2800	-	9000	10	612	-	625	10	-	2	3	20	Common cathode	
TDSY5150 (1)	Yellow	700	4200	-	10	581	-	594	10	-	2.4	3	20	Common anode	
TDSG5150	Green	700	9500	-	10	562	-	575	10	-	2.4	3	20	Common anode	
TDSG5150-MN	Green	4500	-	14 000	10	562	-	575	10	-	2.4	3	20	Common anode	
TDSG5150-N	Green	7000	-	14 000	10	562	-	575	10	-	2.4	3	20	Common anode	
TDSG5160	Green	700	9500	-	10	562	-	575	10	-	2.4	3	20	Common cathode	
TDSG5160-MN	Green	4500	-	14 000	10	562	-	575	10	-	2.4	3	20	Common cathode	
TDSG5160-N	Green	7000	-	14 000	10	562	-	575	10	-	2.4	3	20	Common cathode	

Note

(1) Not for new designs



www.vishay.com

Vishay Semiconductors

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified) TDSO5150, TDSO5160, TDSY5150, TDSG5150, TDSG5160										
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT						
Reverse voltage per segment or DP		V_R	6	V						
DC forward current per segment or DP		I _F	25	mA						
Surge forward current per segment or DP	$t_p \le 10 \mu s$ (non repetitive)	I _{FSM}	0.15	Α						
Power dissipation	T _{amb} ≤ 45 °C	P _V	550	mW						
Junction temperature		T _j	100	°C						
Operating temperature range		T _{amb}	-40 to +85	°C						
Storage temperature range		T _{stg}	-40 to +85	°C						
Soldering temperature	$t \le 3 \text{ s}, 2 \text{ mm below seating plane}$	T _{sd}	260	°C						
Thermal resistance LED junction to ambient		R _{thJA}	100	K/W						

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_{amb} = 25$ °C, unless otherwise specified) TDSO5150, TDSO5150-LM, TDSO5160, TDSO5160-LM, ORANGE RED										
PARAMETER TEST CONDITION PART SYMBOL MIN. TYP. MAX. UNIT										
		TDSO5150		700	5000	-				
Luminous intensity per segment	I _E = 10 mA	TDSO5150-LM		2800	-	9000	uad			
(digit average) (1)	TDSO5160		ΙV	700	5000	-	μcd			
		TDSO5160-LM		2800	-	9000				
Dominant wavelength	I _F = 10 mA		λ_{d}	612	-	625	nm			
Peak wavelength	I _F = 10 mA	TDSO5150,	λρ	-	630	-	nm			
Angle of half intensity	I _F = 10 mA	TDSO5150-LM, TDSO5160.	j	-	± 50	-	0			
Forward voltage per segment or DP	I _F = 20 mA	TDSO5160-LM	V _F	-	2	3	V			
Reverse voltage per segment or DP	I _R = 10 μA		V_R	6	15	-	V			

Note

⁽¹⁾ I_{Vmin.} and I_V groups are mean values of all segments (a to g, D1 to D4), matching factor within segments is ≥ 0.5, excluding decimal points and colon

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_{amb} = 25 ^{\circ}$ C, unless otherwise specified) TDSY5150, YELLOW, NOT FOR NEW DESIGNS									
PARAMETER TEST CONDITION PART SYMBOL MIN. TYP. MAX. UNIT									
Luminous intensity per segment (digit average) (1)	I _F = 10 mA	TDSY5150	I _V	700	4200	-	μcd		
Dominant wavelength	I _F = 10 mA		λ_{d}	581	-	594	nm		
Peak wavelength	I _F = 10 mA		λ_{p}	-	585	-	nm		
Angle of half intensity	I _F = 10 mA	TDSY5150	j	-	± 50	-	0		
Forward voltage per segment or DP $I_F = 20 \text{ mA}$ V_F - 2.4 3 V_F									
Reverse voltage per segment or DP	I _R = 10 μA		V _R	6	15	-	V		

Note

⁽¹⁾ I_{Vmin.} and I_V groups are mean values of all segments (a to g, D1 to D4), matching factor within segments is ≥ 0.5, excluding decimal points and colon



www.vishay.com

Vishay Semiconductors

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_{amb} = 25$ °C, unless otherwise specified) TDSG5150, TDSG5150-MN, TDSG5150-N, TDSG5160-MN, TDSG5160-N, GREEN										
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT			
		TDSG5150		700	9500	-				
		TDSG5150-MN		4500	-	14 000				
Luminous intensity per segment	1 10 1	TDSG5150-N		7000	-	14 000				
(digit average) (1)	I _F = 10 mA	TDSG5160		700	9500	-	μcd			
		TDSG5160-MN		4500	-	14 000				
		TDSG5160-N		7000	-	14 000				
Dominant wavelength	I _F = 10 mA	TDSG5150,	λ_{d}	562	-	575	nm			
Peak wavelength	I _F = 10 mA	TDSG5150-MN, TDSG5150-N. TDSG5160, TDSG5160-MN,	λρ	-	565	-	nm			
Angle of half intensity	I _F = 10 mA		j	-	± 50	-	0			
Forward voltage per segment or DP	I _F = 20 mA		V _F	-	2.4	3	V			
Reverse voltage per segment or DP	I _R = 10 μA	TDSG5160-N	V_R	6	15		V			

Note

⁽¹⁾ I_{Vmin}, and I_V groups are mean values of all segments (a to g, D1 to D4), matching factor within segments is ≥ 0.5, excluding decimal points and colon

LUMINOUS INTENSITY CLASSIFICATION								
GROUP	LIGHT INTENSITY (µcd)							
STANDARD	MIN.	MAX.						
E	180	360						
F	280	560						
G	450	900						
Н	700	1400						
1	1100	2200						
K	1800	3600						
L	2800	5600						
М	4500	9000						
N	7000	14 000						

Note

 The above type numbers represent the order groups which include only a few brightness groups. Only one group will be shipped in one tube (there will be no mixing of two groups in one tube).

In order to ensure availability, single brightness groups will not be orderable

COLOR CLASSIFICATION									
GROUP	ORANG	E RED	YELI	LOW	GREEN				
GROUP	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.			
1	612	617	581	584	-	-			
2	616	621	583	586	-	-			
3	620	625	585	588	562	565			
4	-	-	587	590	564	567			
5	-	-	589	592	566	569			
6	-	-	591	594	568	571			
7	-	-	-	-	570	573			
8	-	-	-	-	572	575			

Note

 Wavelengths are tested at a current pulse duration of 25 ms and an accuracy of ± 1 nm

Vishay Semiconductors

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Forward Current vs. Ambient Temperature




Fig. 4 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 2 - Relative Luminous Intensity vs. Angular Displacement




Fig. 5 - Relative Luminous Intensity vs. Forward Current/Duty Cycle




Fig. 3 - Forward Current vs. Forward Voltage




Fig. 6 - Relative Luminous Intensity vs. Forward Current

www.vishay.com

Vishay Semiconductors




Fig. 7 - Relative Intensity vs. Wavelength




Fig. 8 - Forward Current vs. Forward Voltage




Fig. 9 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 10 - Relative Luminous Intensity vs. Forward Current/Duty Cycle




Fig. 11 - Relative Luminous Intensity vs. Forward Current




Fig. 12 - Relative Intensity vs. Wavelength

www.vishay.com

Vishay Semiconductors




Fig. 13 - Forward Current vs. Forward Voltage




Fig. 14 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 15 - Specific Luminous Intensity vs. Forward Current




Fig. 16 - Relative Luminous Intensity vs. Forward Current




Fig. 17 - Relative Intensity vs. Wavelength





Fig. 18 - TDS.51..




www.vishay.com

Vishay Semiconductors

PACKAGE DIMENSIONS FOR TDS.51.. in millimeters







Drawing-No.: 6.544-5150.01-4


Issue: 1; 21.11.95


95 11344

Vishay Semiconductors

Display-13 mm

Package Dimensions in mm







95 11344

Display-13 mm

Vishay Semiconductors



Ozone Depleting Substances Policy Statement

It is the policy of Vishay Semiconductor GmbH to

- 1. Meet all present and future national and international statutory requirements.
- 2. Regularly and continuously improve the performance of our products, processes, distribution and operatingsystems with respect to their impact on the health and safety of our employees and the public, as well as their impact on the environment.

It is particular concern to control or eliminate releases of those substances into the atmosphere which are known as ozone depleting substances (ODSs).

The Montreal Protocol (1987) and its London Amendments (1990) intend to severely restrict the use of ODSs and forbid their use within the next ten years. Various national and international initiatives are pressing for an earlier ban on these substances.

Vishay Semiconductor GmbH has been able to use its policy of continuous improvements to eliminate the use of ODSs listed in the following documents.

- 1. Annex A, B and list of transitional substances of the Montreal Protocol and the London Amendments respectively
- 2. Class I and II ozone depleting substances in the Clean Air Act Amendments of 1990 by the Environmental Protection Agency (EPA) in the USA
- 3. Council Decision 88/540/EEC and 91/690/EEC Annex A, B and C (transitional substances) respectively.

Vishay Semiconductor GmbH can certify that our semiconductors are not manufactured with ozone depleting substances and do not contain such substances.

We reserve the right to make changes to improve technical design and may do so without further notice.

Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer. Should the buyer use Vishay Semiconductors products for any unintended or unauthorized application, the buyer shall indemnify Vishay Semiconductors against all claims, costs, damages, and expenses, arising out of, directly or indirectly, any claim of personal damage, injury or death associated with such unintended or unauthorized use.

> Vishay Semiconductor GmbH, P.O.B. 3535, D-74025 Heilbronn, Germany Telephone: 49 (0)7131 67 2831, Fax number: 49 (0)7131 67 2423


www.vishay.com Rev. 1.1, 25-Mar-04





Vishay Semiconductors

Pin Connections 13 mm



Pin Connections 13 mm

Vishay Semiconductors



Ozone Depleting Substances Policy Statement

It is the policy of Vishay Semiconductor GmbH to

- 1. Meet all present and future national and international statutory requirements.
- 2. Regularly and continuously improve the performance of our products, processes, distribution and operatingsystems with respect to their impact on the health and safety of our employees and the public, as well as their impact on the environment.

It is particular concern to control or eliminate releases of those substances into the atmosphere which are known as ozone depleting substances (ODSs).

The Montreal Protocol (1987) and its London Amendments (1990) intend to severely restrict the use of ODSs and forbid their use within the next ten years. Various national and international initiatives are pressing for an earlier ban on these substances.

Vishay Semiconductor GmbH has been able to use its policy of continuous improvements to eliminate the use of ODSs listed in the following documents.

- 1. Annex A, B and list of transitional substances of the Montreal Protocol and the London Amendments respectively
- 2. Class I and II ozone depleting substances in the Clean Air Act Amendments of 1990 by the Environmental Protection Agency (EPA) in the USA
- 3. Council Decision 88/540/EEC and 91/690/EEC Annex A, B and C (transitional substances) respectively.

Vishay Semiconductor GmbH can certify that our semiconductors are not manufactured with ozone depleting substances and do not contain such substances.

We reserve the right to make changes to improve technical design and may do so without further notice.

Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer. Should the buyer use Vishay Semiconductors products for any unintended or unauthorized application, the buyer shall indemnify Vishay Semiconductors against all claims, costs, damages, and expenses, arising out of, directly or indirectly, any claim of personal damage, injury or death associated with such unintended or unauthorized use.

> Vishay Semiconductor GmbH, P.O.B. 3535, D-74025 Heilbronn, Germany Telephone: 49 (0)7131 67 2831, Fax number: 49 (0)7131 67 2423

www.vishay.com Rev. 1.1, 07-Jul-04



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.