




Poles	Dimensions(mm)		
	A	B	C
02	1.25	5.75	4.95
03	2.50	7.00	6.20
04	3.75	8.25	7.45
05	5.00	9.50	8.70
06	6.25	10.75	9.95
07	7.50	12.00	11.20
08	8.75	13.25	12.45
09	10.00	14.50	13.70
10	11.25	15.75	14.95
11	12.50	17.00	16.20
12	13.75	18.25	17.45



PCB Layout (Pattern side)



NOTE:
 Voltage rating: 50V AC/DC
 Current rating: 1A AC / DC
 Withstanding voltage: 500V AC/minute
 Temperature range: $-40^{\circ}\text{C} \sim +110^{\circ}\text{C}$
 Insulation resistance: $\geq 100\text{M}\Omega$
 Contact resistance: $\leq 20\text{m}\Omega$
 After environmental test: $\leq 50\text{m}\Omega$

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

APPROVALS		DATE
DRAWN	G.M.Chen	2015/5/22
CHECKED		
APPROVALS		

TOLERANCES ARE	ANGLE	UNIT: mm	SCALE: 1:1	SHEET 1 OF 1
30° ±0.10	$\pm 2^{\circ}$	mm	1:1	1 OF 1
10° ±0.20				
5° ±0.15				
~ 5 ±0.10				

DEALON 德之隆®		ELECTRONICS CO.,LTD	
TITLE: Connector		PART NO. L125WS-XPFW	
DRAWING NO.		PROJ.	