



孔位	孔位	DIM A	DIM B	DIM C	DIM D
16	30.00	36.00	32.80	28.90	
15	28.00	34.00	30.80	26.90	
14	26.00	32.00	28.80	24.90	
13	24.00	30.00	26.80	22.90	
12	22.00	28.00	24.80	20.90	
11	20.00	26.00	22.80	18.90	
10	18.00	24.00	20.80	16.90	
9	16.00	22.00	18.80	14.90	
8	14.00	20.00	16.80	12.90	
7	12.00	18.00	14.80	10.90	
6	10.00	16.00	12.80	8.90	
5	8.00	14.00	10.80	6.90	
4	6.00	12.00	8.80	4.90	
3	4.00	10.00	6.80	2.90	
2	2.00	8.00	4.80	2.70	

技术要求Notes:
1.外观质量 Appearance quality:
 a. 金属表面镀层不能有明显损伤;
 Coating on metal surface can not be damaged obviously;
 b. 塑壳表面不能有明显的变形或开裂;
 No obvious deformation or cracking can be observed on the surface of the Housing;
 c. 产品表面应保持清洁;
 Product surface should be kept clean;
 2. 工作温度 Working temperature: -25℃~+105℃;
 3. 额定电压 Voltage Rating : Max 250V (AC/Effective value rms)/DCI;
 4. 额定电流 Current Rating: Max 2A (AC/Effective value rms)/DCI;
 5. 接触电阻 Contact resistance: Max 20 mΩ
 6. 绝缘电阻 Insulation resistance: Min 1000MΩ;
 7. 耐压 Withstanding voltage: 1000V AC(50 Hz, Effective value: 1 min);
 8. 环保要求应符合RoHS标准
 Environmental requirements should meet RoHS standards.

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

APPROVALS	DATE	TOLERANCES ARE	ANGLE	PART NO.	SCALE:	SHEET
DRAWN G.M.Chen	2015/7/17	30 ^{±0.15} 10 ^{±0.10} 5 ^{±0.10}	±2°	L200HY-XXPWB	1:1	1 OF 1
CHECKED						
APPROVALS						
TITLE: CONNECTOR		DRAWING NO.		PROJ.		
DEALON 德之隆® ELECTRONICS CO.,LTD						