



孔位 OKT NO.	DIM A	DIM B	DIM C	DIM D
16	30.00	36.00	32.80	28.90
15	28.00	34.00	30.80	26.90
14	26.00	32.00	28.80	24.90
13	24.00	30.00	26.80	22.90
12	22.00	28.00	24.80	20.90
11	20.00	26.00	22.80	18.90
10	18.00	24.00	20.80	16.90
9	16.00	22.00	18.80	14.90
8	14.00	20.00	16.80	12.90
7	12.00	18.00	14.80	10.90
6	10.00	16.00	12.80	8.90
5	8.00	14.00	10.80	6.90
4	6.00	12.00	8.80	4.90
3	4.00	10.00	6.80	2.90
2	2.00	8.00	4.80	2.70

**技术要求Notes:**

- 外观质量 Appearance quality:
  - 金属表面镀层不能有明显损伤: Coating on metal surface can not be damaged obviously;
  - 塑料表面不能有明显的变形或开裂: No obvious deformation or cracking can be observed on the surface of the Housing;
- 产品表面应保持清洁: Product surface should be kept clean;
- 工作温度 Working temperature:  $-25^{\circ}C \sim +105^{\circ}C$ ;
- 额定电压 Voltage Rating: Max 250V (AC/Effective value rms)/DCI;
- 额定电流 Current Rating: Max 2A (AC/Effective value rms)/DCI;
- 接触电阻 Contact resistance: Max 20 mΩ;
- 绝缘电阻 Insulation resistance: Min 1000MΩ;
- 耐压 Withstanding voltage: 1000V AC(50 Hz, Effective value: 1 min);
- 环保要求应符合RoHS标准 Environmental requirements should meet RoHS standards.

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

  

APPROVALS		DATE		TITLE: CONNECTOR
DRAWN	G.M.Chen	2015/7/17		
CHECKED				
PART NO.		L200HY-XXPWB	SCALE: 1:1	
TOLERANCES ARE		30 <sup>±0.15</sup>	±0.30	ANGLE
		10 <sup>±0.10</sup>	±0.20	UNIT: mm
		5 <sup>±0.05</sup>	±0.15	DRAWING NO.
			±2'	SHEET 1 OF 1
				PROJ.