

PRODUCT-DETAILS

AX40-30-10-80

AX40-30-10-80 220-230V50Hz/230-240V60Hz

Contactors



General Information

Extended Product Type	AX40-30-10-80
Product ID	1SBL321074R8010
EAN	3471522401809
Catalog Description	AX40-30-10-80 220-230V50Hz/230-240V60Hz Contactor
Long Description	AX32, AX40 contactors are mainly used for controlling 3-phase motors and power circuits up to 690 V AC. These contactors are of the block type design with: – 3 main poles and 1 built-in auxiliary contact – control circuit: AC operated – add-on auxiliary contact blocks for front or side mounting and a wide range of accessories.

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Popular Downloads

Instructions and Manuals	9AKK107492A7057
--------------------------	-----------------

Dimensions

Product Net Width	54 mm
Product Net Depth / Length	90 mm
Product Net Height	108.3 mm
Product Net Weight	0.667 kg

Technical

Number of Main Contacts NO	3
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	1
Number of Auxiliary Contacts NC	0
Rated Operational Voltage	Auxiliary Circuit 690 V Main Circuit 690 V
Rated Frequency (f)	Auxiliary Circuit 50 / 60 Hz Main Circuit 50 / 60 Hz
Conventional Free-air Thermal Current (I_{th})	acc. to IEC 60947-4-1, Open Contactors $q = 40$ °C 65 A acc. to IEC 60947-5-1, $q = 40$ °C 16 A
Rated Operational Current AC-1 (I_e)	(220 / 240 V) 55 °C 60 A (690 V) 40 °C 60 A (690 V) 70 °C 42 A
Rated Operational Current AC-3 (I_e)	(415 V) 55 °C 40 A (440 V) 55 °C 37 A (500 V) 55 °C 33 A (690 V) 55 °C 25 A (380 / 400 V) 55 °C 40 A (220 / 230 / 240 V) 55 °C 40 A
Rated Operational Power AC-3 (P_e)	(415 V) 18.5 kW (440 V) 22 kW (500 V) 22 kW (690 V) 22 kW (380 / 400 V) 18.5 kW (220 / 230 / 240 V) 11 kW
Rated Operational Current AC-15 (I_e)	(500 V) NC 2 (500 V) 2 A (690 V) 2 A (24 / 127 V) 6 A (220 / 240 V) 4 A (380 / 400 V) 3 A (400 / 440 V) 2 A
Rated Short-time Withstand Current Low Voltage (I_{cw})	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 400 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 65 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 150 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 600 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 225 A for 0.1 s 140 A for 1 s 100 A
Maximum Breaking Capacity	$\cos \phi = 0.45$ ($\cos \phi = 0.35$ for $I_e > 100$ A) at 440 V 820 A $\cos \phi = 0.45$ ($\cos \phi = 0.35$ for $I_e > 100$ A) at 690 V 340 A
Maximum Electrical Switching Frequency	(AC-1) 600 cycles per hour (AC-15) 1200 cycles per hour (AC-3) 1200 cycles per hour (DC-13) 900 cycles per hour
Rated Operational Current DC-13 (I_e)	(24 V) 6 A / 144 W (110 V) 1.1 A / 121 W (125 V) 1.1 A / 138 W

	(220 V) 0.55 A / 121 W (250 V) 0.55 A / 138 W (400 V) 2.8 A / 134 W (500 V) 2 A / 144 W
Rated Insulation Voltage (U _i)	acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 690 V
Rated Impulse Withstand Voltage (U _{imp})	Auxiliary Circuit 6 kV
Maximum Mechanical Switching Frequency	3600 cycles per hour
Rated Control Circuit Voltage (U _c)	50 Hz 220 ... 230 V 60 Hz 230 ... 240 V
Operate Time	Between Coil De-energization and NC Contact Closing 7 ... 14 ms Between Coil De-energization and NO Contact Opening 4 ... 11 ms Between Coil Energization and NC Contact Opening 6 ... 18 ms Between Coil Energization and NO Contact Closing 8 ... 21 ms
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20 IP20
Terminal Type	Screw Terminals

Technical UL/CSA

General Use Rating UL/CSA	(600 V AC) 60 A
Horsepower Rating UL/CSA	(120 V AC) Single Phase 3 hp (200 ... 208 V AC) Three Phase 10 hp (220 ... 240 V AC) Three Phase 15 hp (240 V AC) Single Phase 7.5 hp (440 ... 480 V AC) Three Phase 30 hp (550 ... 600 V AC) Three Phase 40 hp
Tightening Torque UL/CSA	Auxiliary Circuit 9 in-lb Control Circuit 9 in-lb Main Circuit 20 in-lb

Environmental

Ambient Air Temperature	Close to Contactor Fitted with Thermal O/L Relay -25 ... 55 °C Close to Contactor without Thermal O/L Relay -40 ... 70 °C Close to Contactor for Storage -60 ... +80 °C Near Contactor for Operation in Free Air -40 ... 70 °C
Climatic Withstand	acc. to IEC 60068-2-30 and 60068-2-11 - UTE C 63-100 specification II
Maximum Operating Altitude Permissible	3000 m
RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

CB Certificate	9AKK107492A7073
CCC Certificate	9AKK107492A7090
CCS Certificate	9AKK107492A7096
CQC Certificate	CQC2013010304647116
Declaration of Conformity - CCC	2020980304001065
Declaration of Conformity	1SBD250011U1000

- CE

Instructions and Manuals	9AKK107492A7057
RoHS Information	1SBD251301E1000

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	65 mm
Package Level 1 Depth / Length	101 mm
Package Level 1 Height	115 mm
Package Level 1 Gross Weight	0.71 kg
Package Level 1 EAN	3471522401809
Package Level 2 Units	12 piece
Package Level 2 Width	240 mm
Package Level 2 Depth / Length	295 mm
Package Level 2 Height	145 mm
Package Level 2 Gross Weight	8.52 kg

Classifications

Object Classification Code	Q
ETIM 6	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
UNSPSC	39121529
IDEA Granular Category Code (IGCC)	4755 >> Contactors
E-Number (Finland)	3707349

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors

