

SEP ELECTRONIC CORP.

SURFACE MOUNT GLASS PASSIVATED BRIDEG RECTIFIERS

REVERSE VOLTAGE - 50 to 1000 Volts FORWARD CURRENT - 1.5 Amperes


FEATURES

- ●Rating to 1000V PRV
- ●Ideal for printed circuit board
- Low forward voltage drop, high current capability
- Reliable low cost construction utilizing molded plastic technique results in inexpensive product
- ●Lead tin Pb/Sn copper
- The plastic material has UL flammability classification 94V-0

MECHANICAL DATA

Polarit: As marked on BodyWeight: 0.02 ounces,0.38 gras

Mounting position: Any



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave ,60Hz, resistive or inductive load.

For capacitive load, derate current by 20%

CHARACTERISTICS	SYMBOL	DB151	DB152	DB153	DB156	DB157	DB158	DF1510	UNIT
	STIVIBOL	וטוטט	DB 132	DB 133	DB 130	וטוטט		DF 1310	
Maximum Recurrent Peak Reverse Voltage	VRRM	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	VRMS	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	VDC	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current @Ta=40℃	I(AV)	1.5							Α
Peak Forward Surage Current 8.3ms Single Half Sine-Wave Super Imposed on Rated Load (JEDEC .Method)	IFSМ	60							А
Maximum Forward Voltage at 2.0A DC	VF	1.1							V
Maximum DC Reverse Current @TJ=25℃ at Rated DC Blocking Voltage @TJ=125℃	lR	10 500							uA
I ² t Rating for Fusing (t<8.3ms)	l ² t	10.4							A^2s
Typical Junction capacitance Per Element(Note1)	CJ	25							pF
Typical Thermal Resistance (Note2)	Rejc	40							°C/W
Operating Temperature Range	TJ	-55 to +150							$^{\circ}$
Storage Temperature Range	Tstg	-55 to +150							$^{\circ}$

Note:1.Measured at 1.0MHz and applied reverse voltage of 4.0V DC

2.Thermal resistance from junction to ambient mounted on P.C.B with 0.5*0.5"(13*13mm) copper pads.

RATING AND CHARACTERISTIC CURVES DF1501 thru DF1510

