

isc Silicon NPN Power Transistor

2N3055

DESCRIPTION

- Excellent Safe Operating Area
- DC Current Gain- $h_{FE}=20-70@I_C = 4A$
- Collector-Emitter Saturation Voltage-
: $V_{CE(sat)}= 1.1 V(Max)@ I_C = 4A$
- Complement to Type MJ2955
- Minimum Lot-to-Lot variations for robust device performance and reliable operation

APPLICATIONS



- Designed for general-purpose switching and amplifier applications

ABSOLUTE MAXIMUM RATINGS($T_a=25^{\circ}C$)

SYMBOL	PARAMETER	VALUE	UNIT
V_{CBO}	Collector-Base Voltage	100	V
V_{CER}	Collector-Emitter Voltage	70	V
V_{CEO}	Collector-Emitter Voltage	60	V
V_{EBO}	Emitter-Base Voltage	7	V
I_C	Collector Current-Continuous	15	A
I_B	Base Current	7	A
P_C	Collector Power Dissipation@ $T_C=25^{\circ}C$	115	W
T_J, T_{stg}	Operating and Storage Junction Temperature Range	-65~+150	$^{\circ}C$

THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	MAX	UNIT
$R_{th\ j-c}$	Thermal Resistance, Junction to Case	1.52	$^{\circ}C/W$



isc Silicon NPN Power Transistors

2N3055

ELECTRICAL CHARACTERISTICS

 $T_C=25^{\circ}\text{C}$ unless otherwise specified

SYMBOL	PARAMETER	CONDITIONS	MIN	MAX	UNIT
$V_{CE0(SUS)}$	Collector-Emitter Sustaining Voltage	$I_C=30\text{mA}$; $I_B=0$	60		V
$V_{CE(sat)-1}$	Collector-Emitter Saturation Voltage	$I_C= 4\text{A}$; $I_B= 0.4\text{A}$		1.1	V
$V_{CE(sat)-2}$	Collector-Emitter Saturation Voltage	$I_C= 10\text{A}$; $I_B= 3.3\text{A}$		3.0	V
$V_{BE(on)}$	Base-Emitter On Voltage	$I_C= 4\text{A}$; $V_{CE}= 4\text{V}$		1.5	V
I_{CEO}	Collector Cutoff Current	$V_{CE}= 30\text{V}$; $I_B=0$		0.7	mA
I_{EBO}	Emitter Cutoff Current	$V_{EB}= 7.0\text{V}$; $I_C=0$		5.0	mA
h_{FE-1}	DC Current Gain	$I_C= 4\text{A}$; $V_{CE}= 4\text{V}$	20	70	
h_{FE-2}	DC Current Gain	$I_C= 10\text{A}$; $V_{CE}= 4\text{V}$	5.0		
$I_{s/b}$	Second Breakdown Collector Current with Base Forward Biased	$V_{CE}= 40\text{V}$, $t= 1.0\text{s}$, Nonrepetitive	2.87		A
f_T	Current Gain-Bandwidth Product	$I_C= 0.5\text{A}$; $V_{CE}= 10\text{V}$; $f=1.0\text{MHz}$	2.5		MHz

**Notice:**

ISC reserves the rights to make changes of the content herein the datasheet at any time without notification. The information contained herein is presented only as a guide for the applications of our products.

ISC products are intended for usage in general electronic equipment. The products are not designed for use in equipment which require specialized quality and/or reliability, or in equipment which could have applications in hazardous environments, aerospace industry, or medical field. Please contact us if you intend our products to be used in these special applications.

ISC makes no warranty or guarantee regarding the suitability of its products for any particular purpose, nor does ISC assume any liability arising from the application or use of any products, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.