

NCU18XH103E6SRB

目前生产


推荐

AEC-Q200

RoHS

REACH

外观&形状



特点

1. Excellent solderability and high stability in environment
2. Excellent long time aging stability
3. High accuracy in resistance and B-constant
4. Flow / Reflow soldering possible
5. Same B-Constant in the same resistance in the three sizes (0805 size / 0603 size / 0402 size)
Easy to use smaller size in the circuits
6. Lead is not contained in the product.
7. UL/cULcertified product.(UL1434, File No. E137188)

用途

限定用途	车载用途
------	------

包装信息

包装	规格	标准包装数量
RB	180mm纸带	4000

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，请核准其规格或者办理产品规格表。

NCU18XH103E6SRB



规格


电阻值(25°C)	10kΩ
电阻值(25°C)允许差	±3%
B常数(25/50°C)	3380K
B常数(25/50°C)允许差	±1%
B常数(25/80°C)(标准值)	3428K
B常数(25/85°C)(标准值)	3434K
B常数(25/100°C)(标准值)	3455K
最大电压	5V
最大工作电流(25°C)	0.1mA
散热常数(25°C)	1mW/°C
工作温度范围	-40°C to 150°C
Size Code (in inch)	0.6x0.3inch
形状	SMD
质量	0.0047g
MSL	1

注意


1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，请核准其规格或者办理产品规格表。

NCU18XH103E6SRB


产品数据



电阻-温度特性



最大工作电压降低特性



温度误差特性

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，请核准其规格或者办理产品规格表。