



孔位	孔位	DIM A	DIM B	DIM C	DIM D
16	30.00	36.00	32.80	28.90	
15	28.00	34.00	30.80	26.90	
14	26.00	32.00	28.80	24.90	
13	24.00	30.00	26.80	22.90	
12	22.00	28.00	24.80	20.90	
11	20.00	26.00	22.80	18.90	
10	18.00	24.00	20.80	16.90	
9	16.00	22.00	18.80	14.90	
8	14.00	20.00	16.80	12.90	
7	12.00	18.00	14.80	10.90	
6	10.00	16.00	12.80	8.90	
5	8.00	14.00	10.80	6.90	
4	6.00	12.00	8.80	4.90	
3	4.00	10.00	6.80	2.90	
2	2.00	8.00	4.80	2.70	

**技术要求Notes:**  
**1.外观质量Appearance quality:**  
 a.金属表面镀层不能有明显损伤;  
 Coating on metal surface can not be damaged obviously;  
 b.塑壳表面不能有明显的变形或开裂;  
 No obvious deformation or cracking can be observed on the surface of the Housing;  
 c.产品表面应保持清洁;  
**Product surface should be kept clean;**  
 2.工作温度 Working temperature: -25℃~+105℃;  
 3.额定电压 Voltage Rating : Max 250V (AC/Effective value rms)/DCI;  
 4.额定电流 Current Rating: Max 2A (AC/Effective value rms)/DCI;  
 5.接触电阻 Contact resistance: Max 20 mΩ  
 6.绝缘电阻 Insulation resistance: Min 1000MΩ;  
 7.耐压 Withstanding voltage: 1000V AC(50 Hz, Effective value: 1 min);  
 8.环保要求应符合RoHS标准  
 Environmental requirements should meet RoHS standards.

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

  

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/7/17	L200HY-XXPWB	
CHECKED			ELECTRONICS CO.,LTD	
TOLERANCES ARE		ANGLE	SCALE:	SHEET
30 <sup>±0.15</sup>	±0.30	±2°	1:1	1 OF 1
10 <sup>±0.10</sup>	±0.20			
5 <sup>±0.05</sup>	±0.15			