



Pin	A	B	C
2	3.96	9.9	11.88
3	7.92	13.86	15.84
4	11.88	17.82	19.80
5	15.84	21.78	23.76
6	19.80	25.74	27.72
7	23.76	29.70	31.68
8	27.72	33.66	35.64
9	31.68	37.62	39.60
10	35.64	41.58	43.56
10	39.60	45.54	47.52
12	43.56	49.50	51.48

**SPECIFICATIONS**

1. Voltage rating: 250V AC, DC
2. Current rating: 7A, AC, DC
3. Withstanding Voltage: 1500V AC/minute
4. Insulation resistance: 1000MΩ min
5. Temperature range: -25°C~+85°C
6. Contact resistance: 10mΩ max

WAFER  
 Housing Material: LCP UL 94V0  
 Pin Material: Phosphor Bronze or Brass  
 Contact Area Plating: Plated Tin or Plated Gold

PCB Layout(Pattern side)

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

  

APPROVALS		DATE
DRAWN	G.M.Chen	2015/5/29
CHECKED		
APPROVALS		

  

TOLERANCES ARE	ANGLE	UNIT: mm	SCALE: 1:1	SHEET 1 OF 1
30 <sup>±0.15</sup>	±2°			
10 <sup>±0.10</sup>				
5 <sup>±0.05</sup>				

  

DRAWING NO.		PART NO.		TITLE:	
L396VII-XXPW		CONNECTOR		EPCALON 德之隆® ELECTRONICS CO.,LTD	