

### **Description**

The CLAMP0504S is an ultra low capacitance TVS array, utilizing leading monolithic silicon technology to provide fast response time and low ESD clamping voltage, making this device an ideal solution for protecting voltage sensitive high-speed data lines. The CLAMP0504S has an ultra-low capacitance with a typical value at 0.3pF, and complies with the IEC 61000-4-2 (ESD) standard with ±25kV air and ±20kV contact discharge. It is assembled into a 6-pin lead-free SOT-563package. The combination of small size, ultra low capacitance, and high ESD surge capability make it ideal for use in applications such as USB 3.0, multimedia, and other high speed ports.

### **Features**

■ Ultra low capacitance: 0.3pF typical (I/O to I/O)

■ Ultra low leakage: nA level

■ Working voltage: 5V

Low clamping voltage

■ Up to 4 data lines and one power line protects

Complies with following standards:


- IEC 61000-4-2 (ESD) immunity test

Air discharge: ±25kV Contact discharge: ±20kV

– IEC61000-4-5 (Lightning) 5A (8/20µs)

■ RoHS Compliant

### **Dimensions & Symbol** (Unit: mm Max)



Circuit Diagram & Pin Schematic

#### **Mechanical Characteristics**

Package: SOT-563Lead Finish: Matte Tin

Case Material: "Green" Molding Compound.
Moisture Sensitivity: Level 3 per J-STD-020
Terminal Connections: See Diagram Below

Marking Information: See Below

## **Applications**

- USB 2.0 and USB 3.0 Ports
- USB OTG
- Digital Video Interface (DVI)
- Monitor and Flat Panel Displays
- PCI Express and Serial SATA Ports
- Gigabit Ethernet
- IEEE 1394 Firewire Ports
- Consumer products (STB, DVD, DSC, DVC...)

#### **Marking information**



Dot denotes Pin1

Details marking code reference customer approval list

### **Ordering Information**

Part Number	Packaging	Reel Size	
CLAMP0504S	3000/Tape & Reel	7 inch	

Rev.A\_Aug,2016 - 1 - www.wpmtek.com



# Absolute Maximum Ratings (T<sub>A</sub>=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20µs)	Ppk	100	W
Peak Pulse Current (8/20µs)	Ipp	5	Α
ESD per IEC 61000-4-2 (Air)		±25	
ESD per IEC 61000-4-2 (Contact)	VESD	±20	kV
Operating Temperature Range	TJ	-55 to +125	°C
Storage Temperature Range	Tstg	-55 to +150	°C


# Electrical Characteristics (T<sub>A</sub>=25°C unless otherwise specified)


Parameter	Symbol	Min	Тур	Max	Unit	Test Condition
Reverse Working Voltage	VRWM			5	V	
Breakdown Voltage	VBR	6			V	IT = 1mA
Reverse Leakage Current	I <sub>R</sub>			0.5	μA	VRWM = 5.0V
Clamping Voltage	Vc			15	V	IPP = 1A (8 x 20µs pulse)
Clamping Voltage	Vc			20	V	IPP = 5A (8 x 20μs pulse)
Junction Capacitance	Сл		0.3	0.4	pF	Between I/O pins VR=0V, f=1MHZ
Junction Capacitance	CJ			0.8	pF	Any I/O pins to Ground VR=0V, f=1MHZ

Rev.A\_Aug,2016 - 2 - www.wpmtek.com



### Typical Performance Characteristics (T<sub>A</sub>=25°C unless otherwise Specified)






2


3


5


6

0










ESD Clamping Voltage 8 kV Contact per IEC61000-4-2



# **Soldering parameters**


Reflow Condition		Pb-Free assembly (see FIG.2)		
	-Temperature Min (T <sub>s(min)</sub> )	+150℃		
Pre Heat	-Temperature Max(T <sub>s(max)</sub> )	+200℃		
	-Time (Min to Max) (ts)	60-180 secs.		
Average ramp	up rate (Liquid us Temp (T <sub>L</sub> ) to peak)	3°C/sec. Max		
T <sub>s(max)</sub> to T <sub>L</sub> - R	lamp-up Rate	3℃/sec. Max		
Deflow	-Temperature(T <sub>L</sub> ) (Liquid us)	+217℃		
Reflow	-Temperature(t <sub>L</sub> )	60-150 secs.		
Peak Temp (Tp	b)	+260(+0/-5)°C		
Time within 5°	C of actual Peak Temp (tp)	30 secs. Max		
Ramp-down R	ate	6℃/sec. Max		
Time 25°C to F	Peak Temp (T <sub>P</sub> )	8 min. Max		
Do not exceed		+260°C		



Rev.A\_Aug,2016 - 4 - www.wpmtek.com




### Package mechanical data



	MILLIMETERS			INCHES			
DIM	MIN	MOM	MAX	MIN	NOM	MAX	
A	0.50	0.55	0.60	0.020	0.021	0.023	
b	0.17	0.22	0.27	0.007	0.009	0.011	
C	0.08	0.12	0.18	0.003	0.005	0.007	
D	1.50	1.60	1.70	0.059	0.062	0.066	
E	1.10	1.20	1.30	0.043	0.047	0.051	
е	0.5 BSC			0.02 BSC			
L	0.10	0.20	0.30	0.004	0.008	0.012	
HE	1.50	1.60	1.70	0.059	0.062	0.066	

### **Suggested Land Pattern**



#### **Contact information**

WPMTEK Incorporated Limited

Floor 1 Building 4#, Binxianghua Industry Park, No.7,

Huada Road, Hualian Community, Longhua New District, Shenzhen

wpmtek Incorporated Limited (WPM) reserves the right to make changes to the product specification and data in this document without notice. WPM makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does WPM assume any liability arising from the application or use of any products or circuits, and specifically dis- claims any and all liability, including without limitation special, consequential or incidental damages.

Rev.A\_Aug,2016 - 5 - www.wpmtek.com