





PRODUCT NO.	DSDA02LHGETR
RoHS compliant	

REV.	ECN NO.	DR	DATE



P.C.B LAYOUT


注意:

1. 波峰焊: 推荐焊锡温度在270°C±5°C, 浸锡时间为5~6秒钟。
2. 手工焊: 使用30瓦烙铁控制温度在320°C, 焊接时间大约2~3秒钟。
3. 拨柄位置: 产品焊接时, 请将产品的拨柄置于OFF端, 能给予产品更好的接触性能。
4. 清洗过程: 清洗使用超音波方式, 能给予更好的效果。

Note:

1. All dimensions are in millimeters.
2. General tolerance: ±0.2mm.
3. Material:
 - Base: UL94V-0 PBT Thermoplastic (Black).
 - Cover: UL94V-0 PBT Thermoplastic (Black/Red/Blue).
 - Actuators: UL94V-0 PBT Thermoplastic (White).
 - Contact plating: Gold plating over nickel.
 - Pitting material: Epoxy.
4. Electrical
 - Electrical: 2000 Operations per switch 24/VDC, 25mA.
 - Non-Switching Rating: 100mA, 50/VDC.
 - Switching Rating: 25mA, 24/VDC.
 - Contact Resistance: 100 mΩ Max. at initial.
5. Mechanical
 - Mechanical life: 2000 Operations per switch.
 - Stroke: 2.0mm.
 - Operation Temp: -20°C to 70°C.
 - Storage Temp: -40°C to 85°C.

6. PART NUMBER DESCRIPTION:



TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY			
LINER	ANGLES	PROJECTION	TITLE		
.0 ± 0.40	0. ± 1'		BY DSDA SERIES PITCH 2.54mm		
.00 ± 0.30	.0 ± 0.5'		PRODUCT FAMILY DSDA SERIES		
.000± 0.20	.00±		PART NO. DSDA02LHGETR		
DESIGN LU ER XIN	2013/01/08		FILE NO. DSDA02LHGETR-A		
DRAWING			SIZE	UNIT	SCALE
CHECK			A4	mm	FIT
APPD.					1 OF 1
					A