


Dual high slew rate, low noise operational amplifier


The HT4582A are low-noise dual operational amplifiers designed especially for applications involving high-grade audio equipment. Since they feature low noise, a wide band width, and high power output, these products can also be used in measuring instruments and control circuits.

● Features


- 1) High output current capacity.
- 2) High slew rate.
- 3) Low noise.



● Block diagram



● Internal circuit configuration


● Absolute maximum ratings ($T_a = 25^\circ\text{C}$)

Parameter	Symbol	Limits			Unit
		HT4582AN	HT4582AR	HT4582AI	
Power supply voltage	Vcc	± 21	± 21	± 21	V
Power dissipation	Pd	800*	550*	900*	mW
Differential input voltage	Vid	± 0.5	± 0.5	± 0.5	V
Common-mode input voltage	Vi	$-V_{cc} \sim V_{cc}$	$-V_{cc} \sim V_{cc}$	$-V_{cc} \sim V_{cc}$	V
Operating temperature	Topr	$-20 \sim +75$	$-20 \sim +75$	$-20 \sim +75$	$^\circ\text{C}$
Storage temperature	Tstg	$-55 \sim +125$	$-55 \sim +125$	$-55 \sim +125$	$^\circ\text{C}$

* Refer to Pd characteristics diagram.

The values for the BA15532F are those when it is mounted on a glass epoxy board (50mm × 50mm × 1.6mm).

● Electrical characteristics (unless otherwise noted, $T_a = 25^\circ\text{C}$, $V_{cc} = +15\text{V}$, $V_{ee} = -15\text{V}$)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions
Input offset voltage	V_{io}	—	0.5	4	mV	$R_s = 50\Omega$, $R_L \leq 10k\Omega$
Input offset current	I_{io}	—	10	150	nA	$R_L \leq 10k\Omega$
Input bias current	I_B	—	200	800	nA	$R_L \leq 10k\Omega$
High-amplitude voltage gain	A_v	80	94	—	dB	$R_L \leq 600\Omega$, $V_o = \pm 10\text{V}$
Common-mode input voltage	V_{icm}	± 12	± 13	—	V	$R_L \leq 10k\Omega$
Maximum output voltage	V_{om}	± 12	± 13	—	V	$R_L \leq 600\Omega$
Maximum output voltage	V_{om}	± 15	± 16	—	V	$R_L \leq 600\Omega$, $V_{cc} = 18\text{V}$, $V_{ee} = -18\text{V}$
Common-mode rejection ratio	CMRR	70	100	—	dB	$R_L \leq 10k\Omega$
Power supply voltage rejection ratio	PSRR	80	100	—	dB	$R_s = 50\Omega$, $R_L \leq 10k\Omega$
Quiescent current	I_Q	—	5	12	mA	$R_L = \infty$, on All Op - Amps
Output short-circuit current	I_{os}	—	38	—	mA	
Slew rate	S. R.	—	8	—	V / μs	$A_v = 1$, $R_L = 600\Omega$, $C_L = 100\text{pF}$
Voltage gain band width	GBW	—	20	—	MHz	$C_L = 100\text{pF}$, $R_L = 600\Omega$, $f = 10\text{kHz}$
Maximum frequency	f_T	—	7	—	MHz	
Input conversion noise voltage	V_n	—	0.7	1.5	μV	RIAA, $R_s = 100\Omega$, $BW = 20\text{Hz} \sim 30\text{kHz}$
Channel separation	CS	—	110	—	dB	RIAA, $f = 1\text{kHz}$



● Electrical characteristic curves









Fig.1 Power dissipation vs.
ambient temperatureFig.2 Quiescent current vs.
power supply voltageFig.3 Open loop voltage gain vs.
frequencyFig.4 Maximum output voltage vs.
frequencyFig.5 Input bias current vs.
ambient temperatureFig.6 Input bias current vs.
power supply voltage

Fig.7 Output response characteristics

Fig.8 Common mode input voltage vs.
power supply voltage

● Operation notes

(1) Handling unused circuits

If there are any circuits which are not being used, we recommend making connections as shown in Figure 9, with the non-inverted input pin connected to the potential within the in-phase input voltage range (V_{ICM}).





Fig.9 Unused circuit connections


● External dimensions (Units: mm)

HT4580ANZ




DIP8

HT4582ARZ



SOP8

HT4582AIZ



SIP8



DUB8 (7.5*6.5) package information

