



RoHS Compliant  
Directive 2011/65/EU

## REFERENCE SPECIFICATION

Customer: \_\_\_\_\_

Item: Simple Packaged Crystal Oscillator  
(SPXO)

Type: NZ2520SH

Nominal Frequency: 48 MHz

Customer's Spec. No.: ---

NDK Spec. No.: ERG5048A

For your reference we submit this specification.  
Please study and keep in your related document file.

### Revision Record

Rev.	Date	Items	Contents	Approved	Checked	Drawn
---	26.May.2016	Issue	---	Y.Akasaka	---	C.Sakurai

- 1. Customer's Spec. No. : ---
- 2. NDK Spec. No. : ERG5048A
- 3. Type : NZ2520SH

4. Maximum Ratings


	Item	Ratings			Notes
		min	max	Units	
1	Supply Voltage	-0.3	4.0	V	
2	Storage Temperature Range	-55	+125	°C	

5. Electrical Specifications

(Unless otherwise noted, TA=-40 to +85 °C, V<sub>CC</sub>=1.8 V, Load=15 pF)


	Parameters	SYM	Electrical Spec.				Notes
			min	typ	max	Units	
1	Nominal Frequency	f <sub>nom</sub>		48		MHz	
2	Supply Voltage	V <sub>CC</sub>	1.62	1.8	1.98	V	
3	Current Consumption (Operating)	I <sub>CC</sub>			5	mA	at 25 °C
4	Current Consumption (Stand-by)	I <sub>ST</sub>			20	μA	at 25 °C
5	Output Level	-	C-MOS				
6	Load Capacitance	C <sub>L</sub>			15	pF	
7	Operating Temperature Range	T <sub>opr</sub>	-40		+85	°C	
8	Overall Frequency Tolerance	Δf/f <sub>nom</sub>	-50		+50	ppm	*1
9	Output Voltage	V <sub>OL</sub>			0.1 V <sub>CC</sub>	V	
		V <sub>OH</sub>	0.9 V <sub>CC</sub>			V	
10	Rise Time(t <sub>r</sub> ), Fall Time(t <sub>f</sub> )	t <sub>r</sub> /t <sub>f</sub>			6	ns	0.1 V <sub>CC</sub> to 0.9 V <sub>CC</sub>
11	Symmetry	SYM	45		55	%	at 1/2 V <sub>CC</sub>
12	Start-up Time	t <sub>su</sub>			4	ms	
13	Output Wave Form	-	Rectangular				
14	Stand-by Function						
	#1 PAD input			# 3 PAD output			
	H level (0.7 V <sub>CC</sub> to V <sub>CC</sub> ) or open			Operating			
	L level (0.3 V <sub>CC</sub> max)			High impedance			

\*1 Inclusive of Freq. tolerance (at 25 °C), frequency/temperature characteristics, frequency/voltage coefficient.



Symmetry = t / T × 100 ( % )

## 6. Measuring circuits



CL ; 15pF MAX including input capacity of oscilloscope

Cby ; Bypass capacitor (0.01uF)

## 7. Test data will not be submitted.

## 8. Application drawing

## 8.1 Dimension drawing

EKD14B-00027

## 8.2 Marking drawing

EKH11B-00052

## 8.3 Reliability assurance Item

EKS30B-00092

## 8.4 Taping &amp; Reel drawing

EKK17B-00032

EEK17B-00015

## 9. Instruction Notice

## 9.1 Noise

When the NZ2520 series are used, the 0.01  $\mu$ F capacitor should be connected between  $V_{CC}$  and GND line. (Closer to the product terminal is desirable.)

## 9.2 Resistance to dropping

The NZ2520 series is designed to be impactproof so that no damage occurs when dropped a height(75 cm) three times. However, if dropped from a desk etc., it is advisable to check their performance or contact us to check it.

## 9.3 Electrostatic protection

The NZ2520 series employ C-MOS ICs for the active element. Please use them in static-free environments.

## 9.4 High temperature

Normal operation cannot be guaranteed for the NZ2520 series at +125  $^{\circ}$ C (for 24 hours). Be sure that the units are kept within the specified temperature range.

## 9.5 Cleaning

Basically, the NZ2520 series are applicable for ultrasonic wave cleaning. However, in some case, during ultrasonic wave cleanings, internal design may get damage. Please check condition carefully beforehand.

## 9.6 Other

The NZ2520 series are C-MOS applied products. And careful handling(same as with C-MOS IC) are needed to avoid electrostatic problems.


Incorrect PAD connection is cause of trouble. Please make sure to connect correctly as below.

#2 terminal  $\rightarrow$  GND


#4 terminal  $\rightarrow$   $V_{CC}$


## 10. Order items are manufactured according to specification. As to conditions, which are not indicated in this specification and unpredictable such as applied condition and oscillation margin, please check them beforehand.

\*Example For Soldering Conditions (The below graph corresponds to Pb free solder)




\* Recommended footprint [mm]





	Date of Revise	Charge	Approved	Reason	
C	2.Aug.2012	Y.Oishi	C.Ishimaru	Change V <sub>DD</sub> →V <sub>CC</sub> , PAD CONNECTIONS→Terminal land connections	
	Date	Name	Third Angle Projection	Tolerance	
Drawn	23.Oct.2003	M.Yamaguchi	Dimension : mm	-----	
Designed	27.Jun.2003	M.Yamaguchi	Title	Drawing No.	
Checked	-----	-----			
Approved	23.Oct.2003	H.Omata			
			<b>NZ2520S</b> <b>Dimension of External</b>	<b>EKD14B-00027</b>	Rev. C

**NIHON DEMPA KOGYO CO., LTD.**



**\*1 [FREQUENCY]**

Digits are five and 6TH digit will be omitted.  
 MHz unit sign is not marked.  
 ex, ) 28.63636MHz → 28.636 [Unit sign not marked]


**\*2 [MODEL MARK]**

A last digit of model is marked. →

[MODEL MARK]	
NZ2520SA	→ Space
NZ2520SB	→ B
NZ2520SC	→ C
NZ2520SD	→ D
NZ2520SEA	→ E
NZ2520SF	→ F
NZ2520SG	→ G
NZ2520SH	→ H
NZ2520SJ	→ J

**\*3 [WEEK CODE (Digit are three)]**

ex1,) In case of 7TH week of 2006



ex2,) In case of 31<sup>TH</sup> week of 2006





6 3 1

**\*4 [Trace code]**


Trace code consists of four digits number or letter.  
 This code indicates production date and production line number.

Date of Revise	Charge	Approved	Reason		
H	12.Mar.2014	Y.Oishi	Y.Akasaka	Model mark addition.(NZ2520SJ)	
Drawn	Date	Name	Third Angle Projection	Tolerance	Scale
Y.Oishi	27.Jan.2006	Y.Oishi	mm	-----	-----
Designed	Date	Name	Title	Drawing No.	Rev.
Y.Okajima	27.Jan.2006	C.Ishimaru			
C.Ishimaru	27.Jan.2006	H.Omata			
Approved			NZ2520S Marking	<b>EKH11B-00052</b>	H

Environmental Test Conditions	Specification
1. Pre- and Post-Stress Electrical Test Refer to AEC-Q200-REV.D TABLE.11 NO.1	*1
2. High Temperature Exposure (Storage) Refer to AEC-Q200-REV.D TABLE.11 NO.3	*3
3. Temperature Cycling Refer to AEC-Q200-REV.D TABLE.11 NO.4	*3
4. Moisture Resistance Refer to AEC-Q200-REV.D TABLE.11 NO.6	*2
5. Biased Humidity Refer to AEC-Q200-REV.D TABLE.11 NO.7	*2
6. Operational Life Refer to AEC-Q200-REV.D TABLE.11 NO.8	*3
7. External Visual Refer to AEC-Q200-REV.D TABLE.11 NO.9	*4
8. Physical Dimension Refer to AEC-Q200-REV.D TABLE.11 NO.10	*5
9. Resistance to Solvents Refer to AEC-Q200-REV.D TABLE.11 NO.12	*2, *4
10. Mechanical Shock Refer to AEC-Q200-REV.D TABLE.11 NO.13	*2
11. Vibration Refer to AEC-Q200-REV.D TABLE.11 NO.14	*2
12. Resistance to Soldering Heat Refer to AEC-Q200-REV.D TABLE.11 NO.15	*2
13. Solderability Refer to AEC-Q200-REV.D TABLE.11 NO.18	*6
14. Electrical Characterization Refer to AEC-Q200-REV.D TABLE.11 NO.19	*2
15. Board Flex Refer to AEC-Q200-REV.D TABLE.11 NO.21	*7
16. Terminal Strength Refer to AEC-Q200-REV.D TABLE.11 NO.22	*7
<p>*1 After the test mentioned above, the electrical specifications are satisfied.</p> <p>*2 Frequency deviation before and after test should be <math>\Delta F/F \leq \pm 10 \times 10^{-6}</math>, Current consumption deviation before and after test should be <math>\Delta F/F \leq \pm 10\%</math>.</p> <p>*3 Frequency deviation before and after test should be <math>\Delta F/F \leq \pm 20 \times 10^{-6}</math>, Current consumption deviation before and after test should be <math>\Delta F/F \leq \pm 10\%</math>.</p> <p>*4 Inspect device construction, marking, and workmanship.</p> <p>*5 External is satisfied.</p> <p>*6 95% min. covered by new solder.</p> <p>*7 Visual inspection to confirm no cracking of materials and no break of sealing.</p> <p>The electrical specifications are <math>I_{CC}</math>, Tr/Tf, <math>V_{OL}/V_{OH}</math>, duty cycle, stand-by current consumption.</p>	



Reel material: Conductive PS  
EIAJ standard reel




3000pcs MAX-Product Tape

	Date of Revise	Charge	Approved	Reason	
C	5.Sep.2012	Y.Oishi	C.Ishimaru	3000pcs-Product Tape→3000pcs MAX-Product Tape.	
	Date	Name	Third Angle Projection	Tolerance	
Drawn	7.Oct.2003	Y.Okajima	Dimension:mm	Scale /	
Designed	7.Oct.2003	Y.Okajima	Title <b>NZ2520 Taping and Reel Spec.</b>	Drawing No.	
Checked				<b>EKK17B-00032</b>	Rev.
Approved	7.Oct.2003	H.Omata			C

**NIHON DEMPA KOGYO CO., LTD.**





	Date of Revise	Charge	Approved	Reason	
C	4 Jul. 2012	H. Ohkubo	K. Oguri	Addition of condition when reels are 1 to 4.	
	Date	Name	Third Angle Projection	Tolerance	Scale
Drawn	26 Feb. 2010	H. Ohkubo	Dimension:mm	-----	-----
Designed	26 Feb. 2010	K. Oguri	Title <b>180 dia. Reel package</b>	Drawing No. <b>EEK17B-00015</b>	Rev.
Checked	26 Feb. 2010	K. Oguri			C
Approved	26 Feb. 2010	J. Nakamura			

**NIHON DEMPA KOGYO CO., LTD.**