

Vishay BCcomponents

## EMI Suppression Safety Capacitor, Ceramic Disc, Class X1, 440 V<sub>AC</sub>, Class Y2, 300 V<sub>AC</sub>



### LINKS TO ADDITIONAL RESOURCES

30 Models

SPICE Models

QUICK REFERENCE DATA					
DESCRIPTION	VALUE				
Ceramic Class	-	1 5		2	
Ceramic Dielectric	U2J		Y5S, Y5U, Y5V		
Voltage (V <sub>AC</sub> )	300 440		300	440	
Min. Capacitance (pF)	10		68		
Max. Capacitance (pF)	47 10 000		000		
Mounting	Radial				

### **OPERATING TEMPERATURE RANGE**

-40 °C to +125 °C

#### **TEMPERATURE CHARACTERISTICS**

Class 1: U2J Class 2: Y5S, Y5U, Y5V

#### SECTIONAL SPECIFICATIONS

Climatic category (according to EN 60058-1) Class 1 and class 2: 40 / 125 / 21

#### COATING

According to UL 94 V-0 Epoxy resin, isolating, flame retardant

#### **APPROVALS**

IEC 60384-14 UL 60384-14 DIN EN 60384-14 CSA E60384-1:03, CSA E60384-14:09 CQC11-471112

#### PACKAGING

Bulk, tape and reel, taped ammopack

### FEATURES

- Complying with IEC 60384-14
- High reliability
- Vertical (inline) kinked or straight leads
- · Singlelayer AC disc safety capacitors
- Material categorization: for definitions of compliance ple
- for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

#### APPLICATIONS

- X1, Y2 according to IEC 60384-14
- Line-to-line filtering (Class X)
- Line-to-ground filtering (Class Y)
- Primary and secondary coupling (SMPS)
- EMI / RFI suppression and filtering

#### DESIGN

The capacitor consists of a ceramic disc which is silver plated on both sides. Connection leads are made of tin plated copper-clad steel having a diameter of 0.6 mm.

The capacitors may be supplied with vertical (inline) kinked leads having a lead spacing of 5.0 mm, 7.5 mm, 10.0 mm, or 12.5 mm. Encapsulation is made of flame retardant epoxy resin in accordance with UL 94 V-0.

#### **CAPACITANCE RANGE**

10 pF to 0.01 µF

#### RATED VOLTAGE UR

IEC 60384-14: (X1): 440 V<sub>AC</sub>, 50 Hz (Y2): 300 V<sub>AC</sub>, 50 Hz 1000 V<sub>DC</sub>

#### TEST VOLTAGE

Component test (100 %): 2600  $V_{AC}$ , 50 Hz, 2 s (2600  $V_{AC}$  for LS 7.5 mm and above) (2200  $V_{AC}$  for LS 5.0 mm) Random sampling test (destructive test): 2600  $V_{AC}$ , 50 Hz, 60 s Voltage proof of coating (destructive test): 2600  $V_{AC}$ , 50 Hz, 60 s

#### **INSULATION RESISTANCE**

 $\geq$  10 000 M $\Omega$ 

CAPACITANCE TOLERANCE

± 20 % (code M); ± 10 % (code K)

#### **DISSIPATION FACTOR**

Class 1: max. 0.5 % (1 MHz) Class 2: max. 2.5 % (1 kHz)

Revision: 28-Jan-2022

1 For technical questions, contact: <u>cdc@vishay.com</u> Document Number: 28535

(FQ) (e3)

> COMPLIANT HALOGEN FREE <u>GREEN</u> (5-2008)


RoHS

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishav.com/doc?91000</u>

www.vishay.com

SHA

Vishay BCcomponents



	CAPACITANCE	BODY	BODY		PART NUMBER			
CAPACITANCE C (pF)	TOLERANCE (%)	DIAMETER D <sub>max.</sub> (mm)	THICKNESS T <sub>max.</sub> (mm)	LEAD SPACING <sup>(1)</sup> F (mm) ± 1 mm	MISSING DIGITS SEE ORDERING CODE BELOW			
U2J		•	•	· · ·				
10					VY2100K29U2JS6###			
15					VY2150K29U2JS6###			
22	± 10	7.5	5.0	5.0, 7.5, 10.0, or 12.5	VY2220K29U2JS6###			
33					VY2330K29U2JS6###			
47					VY2470K29U2JS6###			
Y5S								
68					VY2680K29Y5SS6###			
100					VY2101K29Y5SS6###			
150	10	7.5	5.0	50.75.400405	VY2151K29Y5SS6###			
220	± 10	7.5 5.0	5.0	5.0, 7.5, 10.0, or 12.5	VY2221K29Y5SS6###			
330					VY2331K29Y5SS6###			
470					VY2471K29Y5SS6###			
Y5U								
680		7.5			VY2681M29Y5US6###			
1000		7.5	7.5	7.5	7.5			VY2102M29Y5US6###
1500		8.0			VY2152M31Y5US6###			
2200		9.0		5.0, 7.5, 10.0, or 12.5	VY2222M35Y5US6###			
3300	± 20	10.5	5.0		VY2332M41Y5US6###			
3900		11.0			VY2392M43Y5US6###			
4700		12.5			VY2472M49Y5US6###			
6800		14.5		7.5, 10.0, or 12.5	VY2682M59Y5US63##			
10 000		16.0			VY2103M63Y5US63##			
Y5V MINI SIZE SE	RIES	•	•	· · ·				
1000		7.5			VY2102M29Y5VS6###			
1500		7.5	1		VY2152M29Y5VS6###			
2200		8.0	1		VY2222M31Y5VS6###			
3300	. 00	9.0		5.0, 7.5, 10.0,	VY2332M35Y5VS6###			
3900	± 20	10.0	5.0	or 12.5	VY2392M39Y5VS6###			
4700		10.5	1		VY2472M41Y5VS6###			
6800		12.0	1		VY2682M47Y5VS6###			
10 000		15.0	1		VY2103M59Y5VS6###			

#### Note

<sup>(1)</sup> Straight leads are available on request

2

Revision: 28-Jan-2022

3

### Vishay BCcomponents


ORDERING CODE										
###	15 <sup>th</sup> to 1	7 <sup>th</sup> digit	Lead config	guration		Available o	configuratio	ns see below		
Example	VY2	221	к	29	Y5S	S	6	U	v	7
	Series	Capacitance value	Tolerance code	Size code	Temperature coefficient	Rated voltage	Lead wire diameter	Packaging / lead length	Lead style	Lead spacing
						S = X1/Y2 300 V (AC)		3 = bulk T = tape and reel U = ammopack	L = straight V = inline kinked	5 = 5.0 7 = 7.5 0 = 10.0 X = 12.5

PACKAGING						
LEAD SPACING	CAPACITANCE VALUE	BODY DIAMETER	PACK	TAPING FIGURE		
(mm)		D <sub>max.</sub> (mm)	BULK	REEL	AMMO	TAPING FIGURE
5.0	10 pF to 4700 pF	11.0	1000	1000	1000	Fig. 1
7.5	10 pF to 6800 pF	14.0	1000	1000	1000	Fig. 1
7.5	6800 pF to 10 000 pF	16.0	500	500	500	Fig. 2
10.0 / 12.5	10 pF to 6800 pF	14.0	1000	500	750	Fig. 2
10.07 12.5	6800 pF to 10 000 pF	16.0	500	500	750	Fig. 2


#### Note

• The capacitors are supplied in bulk packaging (cardboard boxes), in tape on reel, or in ammopack

#### STRAIGHT LEADS










Fig. 1 - The hole pitch 12.7 mm for lead spacing 5 mm (0.2") and 15.0 mm for lead spacing 7.5 mm (0.3")




Fig. 2 - The hole pitch 12.7 mm for lead spacing 10.0 mm (0.40") and 12.5 mm (0.50")

DIMENSION OF TAPE						
SYMBOL	PARAMETER		DIMENSIONS (mm)			
STMBOL	FARAMETER	FIG. 1 (5 mm)	FIG. 1 (7.5 mm)	FIG. 2 (10 mm)		
D <sup>(1)</sup>	Body diameter	11.0 max.	14.0 max.	16.0 max.		
d	Lead diameter	$0.6 \pm 0.05$	$0.6 \pm 0.05$	$0.6 \pm 0.05$		
Р	Pitch of component	12.7 ± 1	15.0 ± 1	25.4 ± 1		
P <sub>0</sub> <sup>(2)</sup>	Pitch of sprocket hole	12.7 ± 0.3	15.0 ± 0.3	12.7 ± 0.3		
P <sub>1</sub> <sup>(3)</sup>	Distance, hole center to lead	$3.85 \pm 0.7$	3.75 ± 0.7	7.7 ± 1.0		
P <sub>2</sub> <sup>(3)</sup>	Distance, hole to center of component	6.35 ± 1.3	7.5 ± 1.5	12.7 ± 1.5		
F	Lead spacing	5.0 (+ 0.6 / - 0.4)	7.5 (+ 0.6 / - 0.4)	10.0 (+ 0.6 / - 0.4)		
Δh	Average deviation across tape	± 1.0 max.	± 1.0 max.	± 1.0 max.		
ΔP	Average deviation in direction of reeling	± 1.0 max.	± 1.0 max.	± 1.0 max.		
W	Carrier tape width	18.0 + 1 / - 0.5	18.0 + 1/- 0.5	18.0 + 1 / - 0.5		
W <sub>0</sub>	Hold-down tape width	5.0 min.	5.0 min.	5.0 min.		
W <sub>1</sub>	Position of sprocket hole	9.0 + 0.75 / - 0.5	9.0 + 0.75 / - 0.5	9.0 + 0.75 / - 0.5		
W <sub>2</sub>	Distance of hold-down tape	3.0 max.	3.0 max.	3.0 max.		
H <sub>1</sub>	Maximum component height	32	40	40		
H <sub>0</sub>	Height to seating plane (for kinked leads)	$16.0 \pm 0.5$	16.0 ± 0.5	16.0 ± 0.5		
H <sub>0</sub>	Height to seating plane (for straight leads)	$20.0 \pm 0.5$	$20.0 \pm 0.5$	$20.0 \pm 0.5$		
L	Length of cut leads	11.0 max.	11.0 max.	11.0 max.		
L <sub>1</sub>	Length of lead protrusion	1.0 max.	1.0 max.	1.0 max.		
D <sub>0</sub>	Diameter of sprocket hole	4.0 ± 0.2	$4.0 \pm 0.2$	$4.0 \pm 0.2$		
t	Total tape thickness	0.9 max.	0.9 max.	0.9 max.		
t <sub>1</sub>	Maximum thickness of tape and wires	1.5 max.	1.5 max.	1.5 max.		

#### Notes


<sup>(1)</sup> See "Technical Data" table

(2) Cumulative pitch error:  $\pm \le 1$  mm/20 pitches (3) Obliquity maximum 3°

Revision: 28-Jan-2022


SHA


www.vishay.com





#### **REEL AND TAPE DATA** in millimeters






APPROVALS				
IEC 60384-14 - Safety tests This approval together with CB test certificate	substitutes all national approvals.			
CB Certificate				$\frown$
Y2-capacitor: CB test certificate:	US-26163-UL	10 pF to 10 nF	300 V <sub>AC</sub>	(Ui )
X1-capacitor: CB test certificate:	US-26163-UL	10 pF to 10 nF	$440 V_{AC}$	
VDE				$\wedge$
Y2-capacitor: VDE marks approval:	40009669	10 pF to 10 nF	300 V <sub>AC</sub>	
X1-capacitor: VDE marks approval:	40009669	10 pF to 10 nF	440 V <sub>AC</sub>	
DIN EN 60384-14 VDE 0565-1-1:2006-04 - Sat	fety tests			
Underwriters Laboratories Inc. / Canadian S	Standards Association			
Y2-capacitor: UL-test certificate:	E183844	10 pF to 10 nF	300 V <sub>AC</sub>	®
X1-capacitor: UL-test certificate:	E183844	10 pF to 10 nF	440 V <sub>AC</sub>	c <b>T</b> us
UL 60384-14.1, CSA E60384-1:03 2 <sup>nd</sup> edition,	CSA E60384-14:09 2 <sup>nd</sup> edition			
Across-the-line, antenna-coupling, and line-by	-pass component			
CQC				$\frown$
Y2-capacitor: CQC test certificate:	CQC05001012316	10 pF to 10 nF	300 V <sub>AC</sub>	$( \cap \cap )$
X1-capacitor: CQC test certificate:	CQC05001012316	10 pF to 10 nF	440 V <sub>AC</sub>	

www.vishay.com

SHAY

# Vishay BCcomponents



PERFORM	PERFORMANCE					
TEST	TEST CONDITION	TEST LIMITS				
Visual and mechanical inspection	Optical inspection, dimensions measured with caliper	No visible damage, marking legible				
Capacitance (C)	25 °C ± 3 °C, relative humidity (RH) ≤ 75 %,	Capacitance within specified tolerance				
Dissipation factor (DF)	1.0 $V_{\text{RMS}}$ $\pm$ 0.2 $V_{\text{RMS}}$ at 1 kHz for Y5U and Y5S, and 1 MHz for U2J	DF $\leq$ 0.3 % for U2J and DF $\leq$ 2.5 % for Y5S and Y5U				
Insulation resistance (IR)	Measured within 60 s $\pm$ 5 s after charging at 500 $V_{\text{DC}}$	10 000 MΩ min.				
Dielectric strength	2600 $V_{\text{AC}}$ at 50 Hz / 60 Hz for 1 min, 50 mA max.	No failure				
Temperature characteristic	RH $\leq$ 75 %, 1.0 V_{RMS} $\pm$ 0.2 V_{RMS} at 1 kHz for Y5U and Y5S, and 1 MHz for U2J	U2J: -750 ppm ± 120 ppm Y5S: ± 22 % Y5U: +22 % / -56 %				
Impulse voltage	3 pulses of 5 kV	No failure				
Life test	1000 h at 125 °C $\pm$ 2 °C, 550 V <sub>AC</sub> /50 Hz; once every hour 1000 V <sub>AC</sub> for 0.1 s	External appearance: no visible damage $\Delta C/C \le \pm 15 \%$ DF $\le 0.5 \%$ for U2J and $\le 5 \%$ for Y5S and Y5U IR $\ge 3000 M\Omega$ Dielectric strength: no failure				
Humidity test	500 h at 440 V <sub>AC</sub> , 50 Hz and 500 h unloaded 40 °C, RH = 90 % to 95 %	External appearance: no visible damage $\Delta C/C \le \pm 10$ % for U2J and $\le \pm 15$ % for Y5S and Y5U DF $\le 0.5$ % for U2J and $\le 5$ % for Y5S and Y5U IR $\ge 3000$ M $\Omega$ Dielectric strength: no failure				
Robustness of termination	Pull test: 0.5 kg tensile weight in radial direction for 10 s $\pm$ 1 s Bending strength: capacitor body rotated by 90° in both directions	No damage to capacitor body and lead wire				
Soldering effect	Immersion of lead wires into 260 °C $\pm$ 5 °C solder for 10 s $\pm$ 2 s; min. distance from body: 1.5 mm Hand soldering at 400 °C $\pm$ 10 °C for 3 s to 4 s; min. distance from body: 1.5 mm	External appearance: no visible damage $\Delta C/C \le \pm 5$ % for U2J and $\le \pm 10$ % for Y5S and Y5U Dielectric strength: no failure				
Vibration test	Resin (adhesive) Solder the capacitor onto test jig (glass epoxy body) and use resin (adhesive) to stick the body to the test jig. The capacitor must be soldered firmly to the supporting lead wire. Vibration change from 10 Hz to 2000 Hz and back to 10 Hz; Total amplitude: 1.5 mm; Acceleration: 100 m/s <sup>2</sup> ; Sweep rate: 1 oct/min, each axis 2 h (6 h in total)	External appearance: no visible damage Capacitance within specified tolerance DF $\leq$ 0.3 % for U2J and $\leq$ 2.5 % for Y5S and Y5U IR $\geq$ 10 000 G $\Omega$				

Revision: 28-Jan-2022


6 For technical questions, contact: <u>cdc@vishay.com</u> Document Number: 28535

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



### Vishay BCcomponents

LEAKAGE CURRENT VS. VOLTAGE (Typical)



#### Note

• The capacitors meet the essential requirements of EIA 198. Unless stated otherwise all electrical values apply at an ambient temperature of 25 °C ± 3 °C, at normal atmospheric conditions

RELATED DOCUMENTS				
General Information	www.vishay.com/doc?28536			
CB Test Certificate	www.vishay.com/doc?22254			
VDE Marks Approval	www.vishay.com/doc?22256			
UL Test Certificate	www.vishay.com/doc?22253			
CQC Test Certificate	www.vishay.com/doc?22255			
LTspice <sup>®</sup> Models	www.vishay.com/doc?28568			

SAMPLE KITS			
Part Number (VY2 Sample Kit)	VY21-KIT-HF		
Link (VY2 Sample Kit)	www.vishay.com/doc?28554		
Part Number (VY2Y5V Sample Kit)	VY2-KIT-MS		
Link (VY2Y5V Sample Kit)	www.vishay.com/doc?28562		



Vishay

## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.