

## P-Channel 30-V (D-S) MOSFET

### GENERAL DESCRIPTION

The ME4835 is the P-Channel logic enhancement mode power field effect transistors are produced using high cell density , DMOS trench technology. This high density process is especially tailored to minimize on-state resistance. These devices are particularly suited for low voltage application such as cellular phone and notebook computer power management and other battery powered circuits where high-side switching and low in-line power loss are needed in a very small outline surface mount package.



### FEATURES

- $R_{DS(ON)} \leq 20m\Omega @ V_{GS} = -10V$
- $R_{DS(ON)} \leq 35m\Omega @ V_{GS} = -4.5V$
- Super high density cell design for extremely low  $R_{DS(ON)}$
- Exceptional on-resistance and maximum DC current capability

### APPLICATIONS

- Power Management in Note book
- Portable Equipment
- Battery Powered System
- DC/DC Converter
- Load Switch
- DSC
- LCD Display inverter

### PIN CONFIGURATION



P-Channel MOSFET

### Absolute Maximum Ratings ( $T_A = 25^\circ C$ Unless Otherwise Noted)

Parameter	Symbol	10 secs	Steady State	Unit	
Drain-Source Voltage	$V_{DSS}$		-30	V	
Gate-Source Voltage	$V_{GSS}$		$\pm 20$	V	
Continuous Drain Current ( $T_j = 150^\circ C$ )	$I_D$	$T_A = 25^\circ C$	-9.1	-7	A
		$T_A = 70^\circ C$	-7.3	-5.6	
Pulsed Drain Current	$I_{DM}$		-30	A	
Avalanche Energy with Single Pulse ( $L = 0.1mH$ )	EAS		50	mJ	
Continuous Source Current (Diode Conduction)	$I_S$	-2.1	-1.25	A	
Maximum Power Dissipation	$P_D$	$T_A = 25^\circ C$	2.5	1.5	W
		$T_A = 70^\circ C$	1.6	0.9	
Operating Junction Temperature	$T_J$	-55 to 150		$^\circ C$	
Thermal Resistance-Junction to Ambient*	$R_{\theta JA}$	$T \leq 10 \text{ sec}$	30	$^\circ C/W$	
		Steady State	62		
Thermal Resistance-Junction to Case	$R_{\theta JC}$	38		$^\circ C/W$	

\*The device mounted on  $1in^2$  FR4 board with 2 oz copper

## P-Channel 30-V (D-S) MOSFET







Electrical Characteristics (T<sub>A</sub>=25°C Unless Otherwise Specified)

Symbol	Parameter	Limit	Min	Typ	Max	Unit
<b>STATIC</b>						
V <sub>GS(th)</sub>	Gate Threshold Voltage	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =-250 μA	-1	-1.4	-3	V
I <sub>GSS</sub>	Gate Leakage Current	V <sub>DS</sub> =0V, V <sub>GS</sub> =±20V			±100	nA
I <sub>DSS</sub>	Zero Gate Voltage Drain Current	V <sub>DS</sub> =-30V, V <sub>GS</sub> =0V			-1	μA
		V <sub>DS</sub> =-30V, V <sub>GS</sub> =0V T <sub>J</sub> =55°C			-25	
I <sub>D(ON)</sub>	On-State Drain Current <sup>a</sup>	V <sub>DS</sub> =-5V, V <sub>GS</sub> =-10V	-30			A
R <sub>DS(ON)</sub>	Drain-Source On-State Resistance <sup>a</sup>	V <sub>GS</sub> =-10V, I <sub>D</sub> =-9.1A		15	20	mΩ
		V <sub>GS</sub> =-4.5V, I <sub>D</sub> =-6.9A		25	35	
V <sub>SD</sub>	Diode Forward Voltage	I <sub>S</sub> =-2.1A, V <sub>GS</sub> =0V		-0.8	-1.2	V
<b>DYNAMIC</b>						
Q <sub>g</sub>	Total Gate Charge	V <sub>DS</sub> =-15V, V <sub>GS</sub> =-10V, I <sub>D</sub> =-9.1A		38	45	nC
Q <sub>gs</sub>	Gate-Source Charge			7.7		
Q <sub>gd</sub>	Gate-Drain Charge			9		
R <sub>g</sub>	Gate Resistance	V <sub>GS</sub> =0V, V <sub>DS</sub> =0V, f=1MHz		5.5		Ω
C <sub>iss</sub>	Input capacitance	V <sub>DS</sub> =-15V, V <sub>GS</sub> =0V, f=1MHz		1730	1900	pF
C <sub>oss</sub>	Output Capacitance			240		
C <sub>rss</sub>	Reverse Transfer Capacitance			70		
t <sub>d(on)</sub>	Turn-On Delay Time	V <sub>DD</sub> =-15V, R <sub>L</sub> =15Ω I <sub>D</sub> =-1A, V <sub>GEN</sub> =-10V R <sub>G</sub> =6Ω		41	50	ns
t <sub>r</sub>	Turn-On Rise Time			19	23	
t <sub>d(off)</sub>	Turn-Off Delay Time			105	120	
t <sub>f</sub>	Turn-On Fall Time			17	20	






Notes: a. Pulse test; pulse width ≤ 300us, duty cycle ≤ 2%

## P-Channel 30-V (D-S) MOSFET




### Typical Characteristics (T<sub>J</sub> = 25°C Noted)



### Typical Characteristics (T<sub>J</sub> = 25°C Noted)



### SOP-8 Package Outline



DIM	MILLIMETERS (mm)	
	MIN	MAX
A	1.35	1.75
A1	0.10	0.25
B	0.35	0.49
C	0.18	0.25
D	4.80	5.00
E	3.80	4.00
e	1.27 BSC	
H	5.80	6.20
L	0.40	1.25
$\theta$	0°	7°

Note: 1. Refer to JEDEC MS-012AA.

2. Dimension "D" does not include mold flash, protrusions or gate burrs . Mold flash, protrusions or gate burrs shall not exceed 0.15 mm per side.