

1. Description

KCX3406A is an N-channel enhancement mode power MOS field effect transistor which is produced using KIA's LVMOS technology. The improved process and cell structure have been especially tailored to minimize on-state resistance, provide superior switching performance.

This device is widely used in Secondary synchronous rectifier, Power Management for Inverter Systems.

2. Features

- 80A,60V, $R_{DS(ON)}(typ.)=8.5m\Omega$ @ $V_{GS}=10V$
- SGT MOSFET
- Low Gate Charge
- Low Crss
- Fast switching
- Improved dv/dt capability

3. Pin configuration



Pin	Function
1,2,3	Source
4	Gate
5,6,7,8	Drain

4. Ordering Information

Part Number	Package	Brand
KCY3406A	DFN5*6	KIA

5. Absolute maximum ratings

TC=25°C unless otherwise specified

Parameter		Symbol	Ratings	Unit
Drain-to-Source Voltage		V _{DSS}	60	V
Gate-to-Source Voltage		V _{GSS}	±20	V
Continuous Drain Current	T _C =25°C	I _D	80	A
	T _C =100°C		48	A
Pulsed Drain Current at VGS=10V		I _{DM}	240	A
Power Dissipation (T _C =25°C)		P _D	63	W
Derating Factor above 25°C			0.5	W/°C
Single Pulsed Avalanche Energy(Note 1)		EAS	81	mJ
Operation Junction Temperature Range		T _J	-55 to 150	°C
Storage Temperature Range		T _{STG}	-55 to 150	°C

6. Thermal characteristics

Parameter	Symbol	Ratings	Unit
Thermal Resistance, Junction-to-Case	R _{θJC}	2.0	°C/W
Thermal Resistance, Junction-to-Ambient	R _{θJA}	62	°C/W

7. Electrical characteristics

($T_J=25^\circ\text{C}$,unless otherwise notes)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Drain-to-Source Breakdown Voltage	BV_{DSS}	$V_{\text{GS}}=0\text{V}, I_{\text{D}}=250\mu\text{A}$	60	--	--	V
Drain-to-Source Leakage Current	I_{DSS}	$V_{\text{DS}}=60\text{V}, V_{\text{GS}}=0\text{V}$	--	--	1	μA
Gate-to-Source Leakage Current	I_{GSS}	$V_{\text{GS}}=\pm 20\text{V}, V_{\text{DS}}=0\text{V}$	--	--	± 100	nA
Gate Threshold Voltage	$V_{\text{GS}(\text{TH})}$	$V_{\text{DS}}=V_{\text{GS}}, I_{\text{D}}=250\mu\text{A}$	1.0	2.0	3.0	V
Static Drain-to-Source On-Resistance	$R_{\text{DS}(\text{ON})}$	$V_{\text{GS}}=10\text{V}, I_{\text{D}}=13.5\text{A}$	--	8.5	9.5	$\text{m}\Omega$
		$V_{\text{GS}}=4.5\text{V}, I_{\text{D}}=11.5\text{A}$	--	13	15	$\text{m}\Omega$
Gate Resistance	R_{G}	$F=1\text{MHz}$ $F=1.0\text{MHz}, V_{\text{GS}}=0\text{V}, V_{\text{DS}}=30\text{V}$	--	1.8	--	Ω
Input Capacitance	C_{iss}		--	1065	--	pF
Output Capacitance	C_{oss}		--	430	--	pF
Reverse Transfer Capacitance	C_{rss}		--	22	--	pF
Turn-on Delay Time	$t_{\text{d}(\text{ON})}$		--	8	--	nS
Rise Time	t_{rise}	$V_{\text{DD}}=30\text{V}, V_{\text{GS}}=10\text{V}, R_{\text{G}}=3\Omega, I_{\text{D}}=13.5\text{A}$ (Note2,3)	--	54	--	nS
Turn-Off Delay Time	$t_{\text{d}(\text{OFF})}$		--	19	--	nS
Fall Time	$t_{\text{f,all}}$		--	8.8	--	nS
Total Gate Charge	Q_{g}		--	16.8	--	nC
Gate-to-Source Charge	Q_{gs}	$V_{\text{DD}}=48\text{V}, V_{\text{GS}}=10\text{V}, I_{\text{D}}=13.5\text{A}$ (Note2,3)	--	5.9	--	nC
Gate-to-Drain (Miller) Charge	Q_{gd}		--	2.7	--	nC
Continuous Source Current ^[2]	I_{SD}		--	--	80	A
Pulsed Source Current ^[2]	I_{SM}	Integral Reverse P-N Junction Diode in the MOSFET	--	--	240	A
Diode Forward Voltage	V_{SD}		--	--	1.4	V
Reverse Recovery Time	t_{rr}	$I_{\text{s}}=13.5\text{A}, V_{\text{GS}}=0\text{V}, \frac{dI}{dt}=100\text{A}/\mu\text{s}$ (Note2)	--	52	--	ns
Reverse Recovery Charge	Q_{rr}		--	0.05	--	nC

Notes:

1. $L=0.5\text{mH}, V_{\text{DD}}=50\text{V}, R_{\text{G}}=10\Omega$,starting $T_J=25^\circ\text{C}$;

2.Pulse Test : Pulse width $\leq 300\mu\text{s}$,Duty cycle $\leq 2\%$;

3.Essentially independent of operating temperature.

8. Typical Characteristics

Figure 1. Output Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-resistance vs. Drain Current




Figure 4. Body Diode Forward Voltage Variation vs. Source Current and Temperature




Figure 5. Capacitance Characteristics










Figure 6. Gate Charge







9. Test Circuits and Waveforms

Gate Charge Test Circuit & Waveform



Resistive Switching Test Circuit & Waveform



Unclamped Inductive Switching Test Circuit & Waveform

