



Specifications:

规格:
 Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
 Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Withstanding voltage:1000V AC/minute
 耐受电压: 1000V AC/分钟
 Temperature range:-25℃~+85℃
 温度范围: -25℃~+85℃
 Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance:≤10mΩ
 接触电阻: ≤10mΩ
 After environmental testing:≤20mΩ
 环境测试后: ≤20兆欧





Poles	Dimension(mm)			
	A	B	C	D
10	12.00	8.00	10.60	5.10
12	14.00	10.00	12.60	6.80
14	16.00	12.00	14.60	6.80
16	18.00	14.00	16.60	6.80
18	20.00	16.00	18.60	6.80
20	22.00	18.00	20.60	6.80
22	24.00	20.00	22.60	6.80
24	26.00	22.00	24.60	6.80
26	28.00	24.00	26.60	6.80
28	30.00	26.00	28.60	6.80
30	32.00	28.00	30.60	6.80
32	34.00	30.00	32.60	6.80
34	36.00	32.00	34.60	6.80
36	38.00	34.00	36.60	6.80
38	40.00	36.00	38.60	6.80
40	42.00	38.00	40.60	6.80

X2081 H-2xXX-N0

① ② ③ ④

- 1.Series No
- 2.Category:H-HSG
- 3.Row No-Pin No:2xXX-2x05P~2x20P
- 5.Material:N0-PA66 94V-0



截面 B-B

X2081H-2xXX-N0	Nylon 66 UL 94V-0	X2081W	X2081T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	2.00mm Crimp Style Connectors
APPD		DATE		SIZE: A4	DWG NO.:
					X2081H-2xXX-N0
XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	SHEET
				1.0g	1/1
					REVISION
					A0

MARK	DESCRIPTION	DATE	REVISED	APPROVED	units:	mm
					tolerance:	
ΔX					X.X	±0.2mm
ΔX					X.XX	±0.1mm
ΔX					X.XXX	±0.05mm
					UNSPECIFIED TOLERANCES	
REVISIONS						
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn						