





| | |
|--------------|----------------|
| PRODUCT NO. | RoHS compliant |
| DSDA05LHGETR | |

| | | | |
|------|---------|----|------|
| REV. | ECN NO. | DR | DATE |
| | | | |



P.C.B LAYOUT


注意:

- 波峰焊: 推荐焊锡温度在270℃±5℃, 浸锡时间为5~6秒钟。
- 手工焊: 使用30瓦烙铁控制温度在320℃, 焊接时间大约2~3秒钟。
- 拨柄位置: 产品焊接时, 请将产品的拨柄置于OFF端, 能给予产品更好的接触性能。
- 清洗过程: 清洗使用超声波方式, 能给予更好的效果。

Note:

- All dimensions are in millimeters.
- General tolerance: ±0.2mm.
- Material:
 - Base: UL94V-0 PBT Thermoplastic (Black).
 - Cover: UL94V-0 PBT Thermoplastic (Black/Red/Blue).
 - Actuators: UL94V-0 PBT Thermoplastic (White).
 - Contact plating: Gold plating over nickel.
 - Pitting material: Epoxy.
- Electrical
 - Electrical: 2000 Operations per switch 24/VDC, 25mA.
 - Non-Switching Rating: 100mA, 50/VDC.
 - Switching Rating: 25mA, 24/VDC.
 - Contact Resistance: 100 mΩ Max. at initial.
- Mechanical
 - Mechanical life: 2000 Operations per switch.
 - Stroke: 2.0mm.
 - Operation Temp: -20℃ to 70℃.
 - Storage Temp: -40℃ to 85℃.

6. PART NUMBER DESCRIPTION:



| TOLERANCE UNLESS OTHERWISE SPECIFIED | |
|--------------------------------------|-----------|
| LINER | ANGLES |
| .0 ± 0.40 | 0. ± 1' |
| .00 ± 0.30 | .0 ± 0.5' |
| .000± 0.20 | .00± |
| DESIGN | LU ER XIN |
| DRAWING | |
| CHECK | |
| APPD. | |

| | |
|------------|------------|
| INSPECTION | COPY |
| PROJECTION | |
| DESIGN | 2013/01/08 |

| | | | | |
|-----------------------------|------|----------------|--------|------|
| | | | | |
| TITLE | | | | |
| BY DSDA SERIES PITCH 2.54mm | | | | |
| PRODUCT FAMILY | | DSDA SERIES | | |
| PART NO. | | DSDA05LHGETR | | |
| FILE NO. | | DSDA05LHGETR-A | | |
| SIZE | UNIT | SCALE | SHEET | REV. |
| A4 | mm | FIT | 1 OF 1 | A |