

# **Quadruple Operational Amplifiers**

### **DESCRIPTION**

The LM324 consists of four independent, high gain, internally frequency compensated operational amplifiers which were designed specifically to operate from a single power supply over a wide range of voltages. Operation from split power supplies is also possible and the low power supply current drain is independent of the magnitude of the power supply voltage.

Application areas include transducer amplifiers, DC gain blocks and all the conventional op amp circuits.


## **FEATURES**

- Wide range of supply voltages
- Low supply current drain independent of supply voltage
- Low input biasing current
- Low input offset voltage and offset current
- Input common-mode voltage range includes ground
- Differential input voltage range equal to the power supply voltage
- DC voltage gain 100 V/ mV Typ
- Internally frequency compensation

## ORDERING INFORMATION

DEVICE	Package Type	MARKING	Packing	Packing Qty
LM324N	DIP14	LM324	TUBE	1000pcs/Box
LM324M/TR	SOP14	LM324	REEL	2500pcs/Reel
LM324MT/TR	TSSOP14	LM324	REEL	2500pcs/Reel

#### PACKAGE INFORMATION



DIP14/SOP14/TSSOP14



# **ELECTRICAL CHARACTERISTICS**

at specified free-air temperature, VCC = 5V (unless otherwise noted)

DADAMETED	TEOT CONS	LN	LINUT				
PARAMETER	TEST CONE	JITIONS*	MIN	TYP	MAX	UNIT	
VIO	Vcc =5V to MAX,	25°C		3	7		
Input offset voltage	VIC=VICRmin,	Full temperature			9	mV	
input onset voltage	VO=1.4V	range			9		
αVIO		Full temperature					
Average temperature coefficient		range		7		μV/°C	
of input offset voltage		Tunge					
IIO		25°C		2	50		
Input offset current	Vo=1.4V	Full temperature			150	nA	
		range					
αΙΙΟ		Full temperature					
Average temperature coefficient of		range		10		pA/°C	
input offset current		-					
IIB		25°C	los de la constante de la cons	-20	-250		
Input bias current	Vo=1.4V	Full temperature	111010		-500	nA	
<u>.                                    </u>		range	gu				
VICR		25°C	0 to Vcc-1.5			V	
Common-mode input voltage range	Vcc = 5V to MAX	Full temperature	0 to Vcc - 2				
, ,		range					
	RL = 2 k	25°C	Vcc-1.5				
VOH	Vcc = MAX,	Full temperature	26				
High-level output voltage	RL =2k	range				V	
	Vcc = MAX,	Full temperature	27	28			
VO	RL = 10 k	range					
VOL	RL = 10 k	Full temperature		5	20	mV	
Low-level output voltage	V 45.V	range	0.5	400			
AVD	Vcc = 15 V, Vo=1V to 11 V,	25°C	25	100		\	
Large-signal differential voltage amplification	V0=1V t0 11 V,   RL≥2 k	Full temperature	15			V/mV	
CMRR	Vcc = 5V to MAX,	range					
Common-mode rejection ratio	VIC = VICR min	25°C	65	80		dB	
kSVR Supply voltage rejection ratio	VIC - VICK IIIII						
(ΔVcc/ΔVIO)	Vcc = 5V to MAX	25°C	65	100		dB	
Vo1/Vo2 Crosstalk attenuation	f=1kHz to 20 kHz	25°C		120		dB	
vo i, voz orossian attenuation	I INIZ IO ZO NIZ	25°C	-20	-30		GD.	
	Vcc = 15 V,	Full temperature	-20	-30			
Ю	VID=1V,Vo= 0	range	-10				
Output current		25°C	10	20		mA	
	Vcc = 15 V,	Full temperature	10	20			
	VID= -1V, Vo=15V						



	VID= -1V, Vo = 200 mV	25°C	12	30		μA
los Short-circuit output current	Vcc at 5 V, GND at -5V,Vo=0	25°C		±40	±60	mA
Icc	Vo = 2.5 V, No load	Full temperature range		1.5	2.4	
Supply current (four amplifiers)	Vcc = MAX, Vo = 0.5Vcc, No load	Full temperature range		1.1	3	mA

<sup>\*</sup> All characteristics are measured under open loop conditions with zero common-mode input voltage unless otherwise specified.


<sup>&</sup>quot;MAX" Vcc for testing purposes is 30 V. Operating temperature -40 ÷ 85° C, MAX Junction temperature + 125°C.






# **Physical Dimensions**


# DIP14





Dimensions In Millimeters(DIP14)										
Symbol:	Α	В	D	D1	Е	L	L1	а	С	d
Min:	6.10	18.94	8.40	7.42	3.10	0.50	3.00	1.50	0.40	2.54 BSC
Max:	6.68	19.56	9.00	7.82	3.55	0.70	3.60	1.55	0.50	2.54 BSC


# SOP14



Dimensions In Millimeters(SOP14)										
Symbol:	Α	A1	В	С	C1	D	Q	а	b	
Min:	1.35	0.05	8.55	5.80	3.80	0.40	0°	0.35	1.27 BSC	
Max:	1.55	0.20	8.75	6.20	4.00	0.80	8°	0.45		



### TSSOP14



Dimensions In Millimeters(TSSOP14)										
Symbol:	Α	A1	В	С	C1	D	Q	а	b	
Min:	0.85	0.05	4.90	6.20	4.30	0.40	0°	0.20	0.65 BSC	
Max:	0.95	0.20	5.10	6.60	4.50	0.80	8°	0.25	0.05 BSC	





#### **IMPORTANT STATEMENT:**

Huaguan Semiconductor Co,Ltd. reserves the right to change the products and services provided without notice. Customers should obtain the latest relevant information before ordering, and verify the timeliness and accuracy of this information.

Customers are responsible for complying with safety standards and taking safety measures when using our products for system design and machine manufacturing to avoid potential risks that may result in personal injury or property damage.

Our products are not licensed for applications in life support, military, aerospace, etc., so we do not bear the onsequences of the application of these products in these fields.

Huaguan Semiconductor Co,Ltd. the performance of the semiconductor products produced by the company can reach the performance indicators that can be applied at the time of sales. The use of testing and other quality control technologies is limite d to the quality assurance scope of Huaguan semiconductor. Not all parameters of each device need to be tested. The above documents are for reference only, and all are subject to the physical parameters.

Our documentation is only permitted to be copied without any tampering with the content, so we do not accept any responsibility or liability for the altered documents.

