




PRODUCT NO.	RoHS compliant
DSDP07LHGETB	


REV.	ECN NO.	DR	DATE



**P.C.B LAYOUT**

- Note:**
- All dimensions are in millimeters.
  - General tolerance:  $\pm 0.2\text{mm}$ .
  - Material:
    - Base: UL94V-0 PBT Thermoplastic (Black).
    - Cover: UL94V-0 PBT Thermoplastic (Black/Red/Blue).
    - Actuators: UL94V-0 PBT Thermoplastic (White).
    - Contact plating: Gold plating over nickel.
    - Pitting material: Epoxy.
  - Electrical
    - Electrical: 2000 Operations per switch 24/VDC, 25mA.
    - Non-Switching Rating: 100mA, 50/VDC.
    - Switching Rating: 25mA, 24/VDC
    - Contact Resistance: 100 m $\Omega$  Max. at initial.
  - Mechanical
    - Mechanical life: 2000 Operations per switch.
    - Stroke: 30°.
    - Operation Temp: -20°C to 70°C.
    - Storage Temp: -40°C to 85°C.

**6. PART NUMBER DESCRIPTION:**



- 注意:**
- 波峰焊: 推荐焊锡温度在  $270^{\circ}\text{C} \pm 5^{\circ}\text{C}$ , 浸锡时间为 5~6 秒钟。
  - 手工焊: 使用 30 瓦烙铁控制温度在  $320^{\circ}\text{C}$ , 焊接时间大约 2~3 秒钟。
  - 拨柄位置: 产品焊接时, 请将产品的拨柄置于 OFF 端, 能给予产品更好的接触性能。
  - 清洗过程: 清洗使用超声波方式, 能给予更好的效果。

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	东莞市广普实业有限公司 DongGuan Kingtek Industrial Co., Ltd.
LINER	ANGLES		
.0 $\pm$ 0.40	0. $\pm$ 1'	PROJECTION	TITLE
.00 $\pm$ 0.30	.0 $\pm$ 0.5'		BY DSDP SERIES PITCH 2.54mm
.000 $\pm$ 0.20	.00 $\pm$		PRODUCT FAMILY DSDP SERIES
DESIGN LU ER XIN	2013/01/08		PRAT NO. DSDP07LHGETB
DRAWING		FILE NO. DSDP07LHGETB-A	
CHECK		SIZE UNIT SCALE SHEET REV.	
APPD.		A4 mm FIT 1 OF 1 A	