

TOSHIBA CMOS Digital Integrated Circuit Silicon Monolithic

TC74VHC4040F, TC74VHC4040FK

12-Stage Ripple Carry Binary Counter

The TC74VHC4040 is an advanced high speed CMOS 12-STAGE BINARY COUNTER/DIVIDER fabricated with silicon gate C^2MOS technology.

It achieves the high speed operation similar to equivalent Bipolar Schottky TTL while maintaining the CMOS low power dissipation.

Setting CLR to high resets the counter to low.


A negative transition on the $\overline{\mbox{CK}}$ input brings one increment into the counter.

This counter provides all divided output stages, and at Q12, a 1/4096 divided frequency will be output.

An input protection circuit ensures that 0 to 5.5 V can be applied to the input pins without regard to the supply voltage. This device can be used to interface 5 V to 3 V systems and two supply systems such as battery back up. This circuit prevents device destruction due to mismatched supply and input voltages.

Features

- High speed: fmax = 210 MHz (typ.) at VCC = 5 V
- Low power dissipation: ICC = 4 μA (max) at Ta = 25°C
- High noise immunity: VNIH = VNIL = 28% VCC (min)
- Power down protection is provided on all inputs.
- Balanced propagation delays: tpLH ≃ tpHL
- Wide operating voltage range: VCC (opr) = 2 V to 5.5 V
- Low noise: VOLP = 1.5 V (max)
- Pin and function compatible with 74HC4040




Weight

SOP16-P-300-1.27A : 0.18 g (typ.) VSSOP16-P-0030-0.50 : 0.02 g (typ.)


Start of commercial production 1992-05



Pin Assignment



IEC Logic Symbol



Truth Table


СК	CLR	Output State
Х	Н	All Outputs = "L"
	L	No Change
$\overline{}$	L	Advance to Next State

X: Don't care

2



System Diagram



Absolute Maximum Ratings (Note)

Characteristics	Symbol	Rating	Unit
Supply voltage range	Vcc	-0.5 to 7.0	V
DC input voltage	VIN	-0.5 to 7.0	V
DC output voltage	Vout	-0.5 to V _{CC} + 0.5	V
Input diode current	lıĸ	-20	mA
Output diode current	Іок	±20	mA
DC output current	lout	±25	mA
DC V _{CC} /ground current	Icc	±100	mA
Power dissipation	PD	180	mW
Storage temperature	T _{stg}	−65 to 150	°C

Note: Exceeding any of the absolute maximum ratings, even briefly, lead to deterioration in IC performance or even destruction.

Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings and the operating ranges.

Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc).



Operating Ranges (Note)

Characteristics	Symbol	Rating	Unit
Supply voltage	Vcc	2.0 to 5.5	V
Input voltage	VIN	0 to 5.5	V
Output voltage	Vout	0 to Vcc	V
Operating temperature	Topr	−40 to 85	°C
Input rise and fall time	dt/dv	0 to 100 (V _{CC} = 3.3 ± 0.3 V) 0 to 20 (V _{CC} = 5 ± 0.5 V)	ns/V

Note: The operating ranges must be maintained to ensure the normal operation of the device. Unused inputs must be tied to either VCC or GND.

Electrical Characteristics

DC Characteristics

Characteristics	Symbol	Test Condition		Ta = 25°C			Ta = −40 to 85°C		Unit	
				Vcc (V)	Min	Тур.	Max	Min	Max	
High-level input voltage	ViH	_		2.0 3.0 to 5.5	1.50 VCC × 0.7	1 1		1.50 V _{CC} × 0.7		٧
Low-level input voltage	V _{IL}	_		2.0 3.0 to 5.5	_ _		0.50 VCC × 0.3	_ _	0.50 VCC × 0.3	٧
High-level output VOH	VIN = VIH or VIL	I _{OH} = -50 μA	2.0 3.0 4.5	1.9 2.9 4.4 2.58	2.0 3.0 4.5	_ _ _	1.9 2.9 4.4 2.48	_ _ _	V	
			I _{OH} = -8 mA	4.5	3.94	_	_	3.80	_	
Low-level output voltage	VoL	VIN = VIH or VIL	I _{OL} = 50 μA	2.0 3.0 4.5	_ _ _	0.0 0.0 0.0	0.1 0.1 0.1	_ _ _	0.1 0.1 0.1	V
			I _{OL} = 4 mA I _{OL} = 8 mA	3.0 4.5	_		0.36 0.36	_	0.44 0.44	
Input leakage current	I _{IN}	V _{IN} = 5.5 V or GND		0 to 5.5		_	±0.1	_	±1.0	μΑ
Quiescent supply current	Icc	V _{IN} = V _{CC} or GND		5.5	_	_	4.0	_	40.0	μΑ



Timing Requirements (input: tr = tf = 3 ns)

Characteristics	Symbol	Test Condition		Ta = 25°C		Ta = −40 to 85°C	Unit	
			V _{CC} (V)	Тур.	Limit	Limit		
Minimum pulse width (\overline{CK})	tw (L) tw (H)	_	3.3 ± 0.3 5.0 ± 0.5	_ _	5.0 5.0	5.0 5.0	ns	
Minimum pulse width (CLR)	tw (H)	_	3.3 ± 0.3 5.0 ± 0.5	_ _	5.0 5.0	5.0 5.0	ns	
Minimum removal time	t _{rem}	_	3.3 ± 0.3 5.0 ± 0.5		5.0 5.0	5.0 5.0	ns	

AC Characteristics (input: tr = tf = 3 ns)

Characteristics	Symbol	Te	Test Condition		Ta = 25°C			Ta = -40 to 85°C		Unit		
	Cymbol		Vcc (V)	C _L (pF)	Min	Тур.	Max	Min	Max	J		
			22.02	15	_	7.5	11.9	1.0	14.0			
Propagation delay time	t _{pLH}		3.3 ± 0.3	50	_	10.0	15.4	1.0	17.5			
(CK -Q1)	t _{pHL}	_	5.0 ± 0.5	15	_	4.8	7.3	1.0	8.5	ns		
			5.0 ± 0.5	50	_	6.3	9.3	1.0	10.5			
Propagation delay			3.3 ± 0.3	50	_	2.4	4.4	_	5.0			
time (Q_n-Q_n+1)	Δt _{pd}	Δt_{pd}	Δt _{pd}	_	5.0 ± 0.5	50	_	1.6	3.1	_	3.5	ns
			3.3 ± 0.3	15	_	8.3	12.8	1.0	15.0	ns ns		
Propagation delay time				50	_	10.8	16.3	1.0	18.5			
(CLR-Q)	t _{pHL}	_	5.0 ± 0.5	15	_	5.6	8.6	1.0	10.0			
(= ==,				50	_	7.1	10.6	1.0	12.0			
	f _{max}		3.3 ± 0.3	15	75	140	_	75	_			
Maximum clock				50	55	80	_	50	_	- MHz		
frequency		_	5.0 ± 0.5	15	150	210	_	125	_			
			5.0 ± 0.5	50	95	125	_	80	_			
Input capacitance	CIN		_		_	4	10	_	10	pF		
Power dissipation capacitance	CPD			(Note)	_	21	_	_	_	pF		

Note: CPD is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load.

Average operating current can be obtained by the equation:


 $ICC (opr) = CPD \cdot VCC \cdot fIN + ICC$



Noise Characteristics (input: tr = tf = 3 ns)

Characteristics	Symbol	Test Condition		Ta = 25°C		Unit
	,		Vcc (V)	Тур.	Limit	
Quiet output maximum dynamic V _{OL}	VOLP	C _L = 50 pF	5.0	1.2	1.5	V
Quiet output minimum dynamic V _{OL}	V _{OLV}	C _L = 50 pF	5.0	-1.2	-1.5	V
Minimum high level dynamic input voltage	VIHD	C _L = 50 pF	5.0	_	3.5	V
Maximum low level dynamic input voltage	VILD	C _L = 50 pF	5.0	_	1.5	V


Input Equivalent Circuit





Package Dimensions

SOP16-P-300-1.27A Unit: mm




Weight: 0.18 g (typ.)



Package Dimensions

VSSOP16-P-0030-0.50 Unit: mm



Weight: 0.02 g (typ.)



RESTRICTIONS ON PRODUCT USE

Toshiba Corporation and its subsidiaries and affiliates are collectively referred to as "TOSHIBA". Hardware, software and systems described in this document are collectively referred to as "Product".

- TOSHIBA reserves the right to make changes to the information in this document and related Product without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.
- PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE
 EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH MAY
 CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT
 ("UNINTENDED USE"). Except for specific applications as expressly stated in this document, Unintended Use includes, without limitation,
 equipment used in nuclear facilities, equipment used in the aerospace industry, lifesaving and/or life supporting medical equipment,
 equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or
 explosions, safety devices, elevators and escalators, and devices related to power plant. IF YOU USE PRODUCT FOR UNINTENDED USE,
 TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT. For details, please contact your TOSHIBA sales representative or contact us via our
 website.
- Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any
 applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR
 PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER,
 INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING
 WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2)
 DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR
 INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE,
 ACCURACY OF INFORMATION, OR NONINFRINGEMENT.
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please
 use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including
 without limitation, the EU RoHS Directive. TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES OCCURRING AS A RESULT
 OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.

TOSHIBA ELECTRONIC DEVICES & STORAGE CORPORATION

https://toshiba.semicon-storage.com/