



**N-channel Enhanced mode TO-252 MOSFET****Features**

- High ruggedness
- Low  $R_{DS(ON)}$  (Typ 5.8mΩ)@ $V_{GS}=10V$
- Low Gate Charge (Typ 102nC)
- Improved dv/dt Capability
- 100% Avalanche Tested
- Application:Synchronous Rectification, Li Battery Protect Board, Inverter



**BV<sub>DSS</sub> : 68V**  
**I<sub>D</sub> : 100A**  
**R<sub>DS(ON)</sub> : 5.8mΩ**

**General Description**

This power MOSFET is produced with advanced technology of SAMWIN. This technology enable the power MOSFET to have better characteristics, including fast switching time, low on resistance, low gate charge and especially excellent avalanche characteristics.

**Order Codes**

Item	Sales Type	Marking	Package	Packaging
1	SW D 056R68E7T	SW056R68E7T	TO-252	REEL

**Absolute maximum ratings**

Symbol	Parameter	Value	Unit
$V_{DSS}$	Drain to source voltage	68	V
$I_D$	Continuous drain current (@ $T_C=25^\circ C$ )	100*	A
	Continuous drain current (@ $T_C=100^\circ C$ )	79*	A
$I_{DM}$	Drain current pulsed (note 1)	400	A
$V_{GS}$	Gate to source voltage	$\pm 20$	V
$E_{AS}$	Single pulsed avalanche energy (note 2)	289	mJ
$E_{AR}$	Repetitive avalanche energy (note 1)	28	mJ
dv/dt	Peak diode recovery dv/dt (note 3)	5	V/ns
$P_D$	Total power dissipation (@ $T_C=25^\circ C$ )	178.6	W
	Derating factor above 25°C	1.4	W/°C
$T_{STG}, T_J$	Operating junction temperature & storage temperature	-55 ~ + 150	°C

\*. Drain current is limited by junction temperature.

**Thermal characteristics**

Symbol	Parameter	Value	Unit
$R_{thjc}$	Thermal resistance, Junction to case	0.7	°C/W

### Electrical characteristic ( $T_J = 25^\circ\text{C}$ unless otherwise specified )

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
<b>Off characteristics</b>						
$\text{BV}_{\text{DSS}}$	Drain to source breakdown voltage	$V_{\text{GS}}=0\text{V}$ , $I_D=250\mu\text{A}$	68			V
$\Delta \text{BV}_{\text{DSS}} / \Delta T_J$	Breakdown voltage temperature coefficient	$I_D=250\mu\text{A}$ , referenced to $25^\circ\text{C}$		0.05		$^\circ\text{C}$
$I_{\text{DSS}}$	Drain to source leakage current	$V_{\text{DS}}=68\text{V}$ , $V_{\text{GS}}=0\text{V}$		1		$\mu\text{A}$
		$V_{\text{DS}}=54\text{V}$ , $T_J=125^\circ\text{C}$		50		$\mu\text{A}$
$I_{\text{GSS}}$	Gate to source leakage current, forward	$V_{\text{GS}}=20\text{V}$ , $V_{\text{DS}}=0\text{V}$		100		nA
	Gate to source leakage current, reverse	$V_{\text{GS}}=-20\text{V}$ , $V_{\text{DS}}=0\text{V}$		-100		nA
<b>On characteristics</b>						
$V_{\text{GS(TH)}}$	Gate threshold voltage	$V_{\text{DS}}=V_{\text{GS}}$ , $I_D=250\mu\text{A}$	2		4	V
$R_{\text{DS(ON)}}$	Drain to source on state resistance	$V_{\text{GS}}=10\text{V}$ , $I_D=30\text{A}$ , $T_J=25^\circ\text{C}$		5.8	7.1	$\text{m}\Omega$
		$V_{\text{GS}}=10\text{V}$ , $I_D=30\text{A}$ , $T_J=125^\circ\text{C}$		9.6		$\text{m}\Omega$
$G_{\text{fs}}$	Forward transconductance	$V_{\text{DS}}=10\text{V}$ , $I_D=30\text{A}$		45		S
<b>Dynamic characteristics</b>						
$C_{\text{iss}}$	Input capacitance	$V_{\text{GS}}=0\text{V}$ , $V_{\text{DS}}=34\text{V}$ , $f=1\text{MHz}$		5178		pF
$C_{\text{oss}}$	Output capacitance			357		
$C_{\text{rss}}$	Reverse transfer capacitance			320		
$t_{\text{d(on)}}$	Turn on delay time	$V_{\text{DS}}=34\text{V}$ , $I_D=30\text{A}$ , $R_G=4.7\Omega$ , $V_{\text{GS}}=10\text{V}$ (note 4,5)		39		ns
$t_r$	Rising time			80		
$t_{\text{d(off)}}$	Turn off delay time			95		
$t_f$	Fall time			35		
$Q_g$	Total gate charge	$V_{\text{DS}}=54\text{V}$ , $V_{\text{GS}}=10\text{V}$ , $I_D=30\text{A}$ , $I_G=3\text{mA}$ (note 4,5)		102		nC
$Q_{\text{gs}}$	Gate-source charge			28		
$Q_{\text{gd}}$	Gate-drain charge			37		
$R_g$	Gate resistance	$V_{\text{DS}}=0\text{V}$ , Scan F mode		3.3		$\Omega$


### Source to drain diode ratings characteristics

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$I_s$	Continuous source current	Integral reverse p-n Junction diode in the MOSFET			100	A
$I_{\text{SM}}$	Pulsed source current				400	A
$V_{\text{SD}}$	Diode forward voltage drop.	$I_s=50\text{A}$ , $V_{\text{GS}}=0\text{V}$			1.4	V
$t_{\text{rr}}$	Reverse recovery time	$I_s=30\text{A}$ , $V_{\text{GS}}=0\text{V}$ , $dI_F/dt=100\text{A}/\mu\text{s}$		31		ns
$Q_{\text{rr}}$	Reverse recovery charge			28		nC


#### ※ Notes

- Repetitive rating : pulse width limited by junction temperature.
- $L = 0.5\text{mH}$ ,  $I_{\text{AS}} = 34\text{A}$ ,  $V_{\text{DD}} = 40\text{V}$ ,  $R_G = 25\Omega$ , Starting  $T_J = 25^\circ\text{C}$
- $I_{\text{SD}} \leq 30\text{A}$ ,  $di/dt = 100\text{A}/\mu\text{s}$ ,  $V_{\text{DD}} \leq \text{BV}_{\text{DSS}}$ , Starting  $T_J = 25^\circ\text{C}$
- Pulse Test : Pulse Width  $\leq 300\mu\text{s}$ , duty cycle  $\leq 2\%$ .
- Essentially independent of operating temperature.


**Fig. 1. On-state characteristics**




**Fig. 2. Transfer Characteristics**




**Fig. 3. On-resistance variation vs. drain current and gate voltage**



**Fig. 4. On-state current vs. diode forward voltage**



**Fig 5. Breakdown voltage variation vs. junction temperature**



**Fig. 6. On-resistance variation vs. junction temperature**




Fig. 7. Gate charge characteristics




Fig. 8. Capacitance Characteristics




Fig. 9. Maximum safe operating area




Fig. 10. Maximum drain current vs. case temperature




Fig. 11. Transient thermal response curve




Fig. 12. Gate charge test circuit & waveform




Fig. 13. Switching time test circuit & waveform





Fig. 14. Unclamped Inductive switching test circuit & waveform






Fig. 15. Peak diode recovery dv/dt test circuit & waveform



## DISCLAIMER

- \* All the data & curve in this document was tested in SEMIPOWER TESTING & APPLICATION CENTER.
- \* This product has passed the PCT, TC, HTRB, HTGB, HAST, PC and Solderdunk reliability testing.
- \* Qualification standards can also be found on the Web site (<http://www.semipower.com.cn>)
- \* Suggestions for improvement are appreciated, Please send your suggestions to [samwin@samwinsemi.com](mailto:samwin@samwinsemi.com)