

Product Summary

| $V_{(BR)DSS}$ | $R_{DS(on)TYP}$ | I_D |
|---------------|-----------------|-------|
| 20V | 190mΩ@4.5V | 0.75A |
| | 260mΩ@2.5V | |
| | 390mΩ@1.8V | |


Feature

- Lead Free Product is Acquired
- Surface Mount Package
- N-Channel Switch with Low $R_{DS(on)}$
- Operated at Low Logic Level Gate Drive

Application


- Load/Power Switching
- Interfacing Switching
- Battery Management for Ultra Small Portable Electronics
- Logic Level Shift

MARKING:



ABSOLUTE MAXIMUM RATINGS ($T_a=25^\circ\text{C}$ unless otherwise noted)

| Parameter | Symbol | Value | Unit |
|---|-----------------|----------|------|
| Drain-Source Voltage | V_{DS} | 20 | V |
| Gate-Source Voltage | V_{GS} | ± 12 | V |
| Continuous Drain Current ⁽¹⁾ | I_D | 0.75 | A |
| Pulsed Drain Current($t_p=10\mu\text{s}$) | I_{DM} | 1.8 | A |
| Power Dissipation ⁽¹⁾ | P_D | 150 | mW |
| Thermal Resistance from Junction to Ambient ⁽¹⁾ | $R_{\theta JA}$ | 833 | °C/W |
| Junction Temperature | T_J | 150 | °C |
| Storage Temperature | T_{STG} | -55~+150 | °C |
| Lead Temperature for Soldering Purposes(1/8" from case for 10s) | T_L | 260 | °C |









MOSFET ELECTRICAL CHARACTERISTICS($T_a=25^\circ\text{C}$ unless otherwise noted)

| Parameter | Symbol | Test Condition | Min | Type | Max | Unit |
|--|-----------------------------|---|------|------|----------|------------------|
| Static Characteristics | | | | | | |
| Drain-source breakdown voltage | $V_{(\text{BR})\text{DSS}}$ | $V_{\text{GS}} = 0\text{V}, I_D = 250\mu\text{A}$ | 20 | | | V |
| Zero gate voltage drain current | I_{DSS} | $V_{\text{DS}} = 20\text{V}, V_{\text{GS}} = 0\text{V}$ | | | 1 | μA |
| Gate-body leakage current | I_{GSS} | $V_{\text{GS}} = \pm 10\text{V}, V_{\text{DS}} = 0\text{V}$ | | | ± 20 | μA |
| Gate threshold voltage ⁽²⁾ | $V_{\text{GS}(\text{th})}$ | $V_{\text{DS}} = V_{\text{GS}}, I_D = 250\mu\text{A}$ | 0.35 | 0.75 | 1.1 | V |
| Drain-source on-resistance ⁽²⁾ | $R_{\text{DS}(\text{on})}$ | $V_{\text{GS}} = 4.5\text{V}, I_D = 650\text{mA}$ | | 190 | 260 | $\text{m}\Omega$ |
| | | $V_{\text{GS}} = 2.5\text{V}, I_D = 550\text{mA}$ | | 260 | 360 | |
| | | $V_{\text{GS}} = 1.8\text{V}, I_D = 450\text{mA}$ | | 390 | 590 | |
| Forward transconductance | g_{FS} | $V_{\text{DS}} = 10\text{V}, I_D = 800\text{mA}$ | | 1.6 | | S |
| Dynamic characteristics⁽⁴⁾ | | | | | | |
| Input Capacitance | C_{iss} | $V_{\text{DS}} = 16\text{V}, V_{\text{GS}} = 0\text{V}, f = 1\text{MHz}$ | | 79 | 120 | pF |
| Output Capacitance | C_{oss} | | | 13 | 20 | |
| Reverse Transfer Capacitance | C_{rss} | | | 9 | 15 | |
| Switching Characteristics⁽⁴⁾ | | | | | | |
| Turn-on delay time ⁽³⁾ | $t_{\text{d}(\text{on})}$ | $V_{\text{DS}} = 10\text{V}, I_D = 500\text{mA}, V_{\text{GS}} = 4.5\text{V}, R_G = 10\Omega$ | | 6.7 | | ns |
| Turn-on rise time ⁽³⁾ | t_r | | | 4.8 | | ns |
| Turn-off delay time ⁽³⁾ | $t_{\text{d}(\text{off})}$ | | | 17.3 | | ns |
| Turn-off fall time ⁽³⁾ | t_f | | | 7.4 | | ns |
| Source-Drain Diode characteristics | | | | | | |
| Diode Forward voltage ⁽³⁾ | V_{DS} | $I_S = 0.15\text{A}, V_{\text{GS}} = 0\text{V}$ | | | 1.2 | V |

Notes:

1. Surface mounted on FR4 board using the minimum recommended pad size.
2. Pulse Test : Pulse Width=300 μs , Duty Cycle=2%.
3. Switching characteristics are independent of operating junction temperatures.
4. Guaranteed by design, not subject to producting.

Typical Electrical and Thermal Characteristics








SALLTECH

SR3134K

SOT-723 Package Information




| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|-------|----------------------|-------|
| | Min. | Max. | Min. | Max. |
| A | 0.430 | 0.500 | 0.017 | 0.020 |
| A1 | 0.000 | 0.050 | 0.000 | 0.002 |
| b | 0.170 | 0.270 | 0.007 | 0.011 |
| b1 | 0.270 | 0.370 | 0.011 | 0.015 |
| c | 0.080 | 0.150 | 0.003 | 0.006 |
| D | 1.150 | 1.250 | 0.045 | 0.049 |
| E | 1.150 | 1.250 | 0.045 | 0.049 |
| E1 | 0.750 | 0.850 | 0.030 | 0.033 |
| e | 0.800TYP. | | 0.031TYP. | |
| θ | 7° REF. | | 7° REF. | |





SALLTECH

SR3134K

SOT-723 Tape and Reel**SOT-723 Tape and reel****SOT-723 Embossed Carrier Tape**

| Dimensions are in millimeter | | | | | | | | | | |
|------------------------------|------|------|------|-------|------|------|------|------|------|------|
| Pkg type | A | B | C | d | E | F | P0 | P | P1 | W |
| SOT-723 | 1.33 | 1.45 | 0.61 | Ø1.50 | 1.75 | 3.50 | 4.00 | 4.00 | 2.00 | 8.00 |

SOT-723 Tape Leader and Trailer**SOT-723 Reel**

| Dimensions are in millimeter | | | | | | | | |
|------------------------------|---------|-------|-------|--------|--------|-------|------|-------|
| Reel Option | D | D1 | D2 | G | H | I | W1 | W2 |
| 7" Dia | Ø178.00 | 54.40 | 13.00 | R78.00 | R25.60 | R6.50 | 9.50 | 12.30 |

| REEL | Reel Size | Box | Box Size(mm) | Carton | Carton Size(mm) | G.W.(kg) |
|----------|-----------|------------|--------------|-------------|-----------------|----------|
| 8000 pcs | 7 inch | 80,000 pcs | 203×203×195 | 320,000 pcs | 438×438×220 | |