Specification of MEMS Microphone

(RoHS Compliance & Halogen Free)

Customer Name : Customer Model : GoerTek Model : S170T421-038

Goertek			CUSTOMER APPROVAL
DESIGN	Jasen	2018.10.19	
CHKD	Samual	2018.10.19	
STANDARD	Sweety	2018.10.19	
APVD	Daniel	2018.10.19	

Tel : + 86 536 3051234 E- Mail : <u>goertek@goertek.com</u> Website: <u>http://www.goertek.com</u> Address: No.268 Dongfang Road, High-Tech Industry Development District, Weifang, Shandong, P.R.C.

Restricted

1 Security Warning

The information contained in this document is the exclusive property of GoerTek Inc. and should not be disclosed to any third party without the written consent of GoerTek Inc. -

2 Publication History

Version	Description	Date	Author	Approved
1.0	New Design	2018.10.19	Jasen	Daniel

Contents

1		4
2	Test Condition	4
3	Acoustic and Electrical Characteristics — — — — — — — — — — — — — — — — — — —	4
4	Frequency Response Curve and Frequency Response Limits	4
5	Measurement Circuit ————————————————————————————————————	5
6	Test Setup Drawing	5
7	Mechanical Characteristics	6
	7.1 Appearance Drawing	
8	Reliability Test	7
9	Package — — — — — — — — — — — — — — — — — — —	8
	9.1 Tape Specification	8 9 9 10
10	Storage and Transportion	10
11	Land Pattern Recommendation — — — — — — — — — — — — — — — — — — —	11
	11.1 The Pattern of MIC Pad –	11 11
12	Soldering Recommendation	12
	12.1 Soldering Machine Condition	12 12 13
13	Cautions 13.1 Board Wash Restrictions 13.2 Nozzle Restrictions	14 14 14
14	Output Inspection Standard	14

1 Introduction:

MEMS MIC which is able to endure reflow temperature up to 260 $^\circ\!C$ for 50 seconds can be used in SMT process. It is widely used in telecommunication and electronics device such as mobile phone, MP3, PDAs etc.


2 Test Condition (Vs=2.0V, L=50cm)

StandardConditions (As IEC 60268-4)	Temperature	Humidity	Air pressure	
Environment Conditions	+15℃~+35℃	25%RH~75%RH	86kPa \sim 106kPa	
Basic Test Conditions	+20℃± 2℃	60%RH~70%RH	86kPa \sim 106kPa	

3 Acoustic and Electrical Characteristics


Item	Symbol	Test Conditions	Min	Тур	Max	Unit
Sensitivity	S	f=1kHz, Pin=1Pa	-43	-42	-41	dBV/Pa
Directivity	D(0)		Omnidirectional		1	
Output Impedance	Zout	f=1kHz, Pin=1Pa	-	-	300	Ω
Operating Voltage Range	Vs		1.5	2.0	3.6	V
Current Consumption	I		-	-	200	μA
Decreasing Voltage Characteristic	∆S	f=1kHz, Pin=1Pa Vs =3.3 → 1.5V	No Change dBV/Pa		dBV/Pa	
S/N Ratio	S/N(A)	f=1kHz, Pin=1Pa (A-weighted)	56	59	-	dB
Total Harmonic Distortion	THD	110dB SPL@1 kHz	-	-	1	%
Acoustic Overload Point	AOP	10% THD @1 kHz	-	130	-	dB SPL

4 Frequency Response Curve and Limits






5 Measurement Circuit




6 Test Setup Drawing



7 Mechanical Characteristics

7.1 Appearance Drawing (Unit: mm)



7.2 Weight


The weight of the MIC is Less than 0.04g.


8 Reliability Condition

8.1 Vibration Test	To be no interference in operation after vibrations, 4 cycles, from 20 to 2,000Hz in each direction(X,Y,Z), 48 minutes, using peak acceleration of 20g, sensitivity should vary within ±3dB from initial sensitivity. (Normal Condition) (The measurement to be done after 2 hours of conditioning at +15 $^{\circ}$ C ~+35 $^{\circ}$ C, R.H 25% ~75%)
8.2	a)To be no interference in operation after dropped to 1.0cm steel plate 20 times from 1.5 meter height in state of JIG, JIG weight of 100g, sensitivity should vary within ±3dB from initial sensitivity. (Normal Condition)
Drop Test	b)To be no interference in operation after dropped to 1.0cm steel plate 30 times from 1.5 meter height in state of JIG, JIG weight of 100g, sensitivity should vary within ±3dB from initial sensitivity (Limit Condition) (The measurement to be done after 2 hours of conditioning at +15 °C ~+35°C, R.H.25% ~75%)
8.3	a)To be no interference in operation after dropped 150times at 10 rotate/minute rotation speed from 1 meter height on to Steel Base, Steel thickness of 3mm, sensitivity should vary within ±3dB from initial sensitivity. (Normal Condition)
Tumble Test	b)To be no interference in operation after dropped 300times at 10 rotate/minute from 1 meter height on to Steel Base, Steel thickness of 3mm, sensitivity should vary within ±3dB from initial sensitivity. (Limit Condition) (The measurement to be done after 2 hours of conditioning at +15 ℃~+35℃, R.H.25%~75%)
8.4	a) After exposure at +125 ℃ for 200 hours, sensitivity should vary within ±3dB from initial sensitivity. (Normal Condition) (The measurement to be done after 2 hours of conditioning at +15 ℃~+35℃, R.H 25%~75%)
Temperature Test	b) After exposure at -40 $^{\circ}$ C for 200 hours, sensitivity should vary within ±3dB from initial sensitivity. (Normal Condition) (The measurement to be done after 2 hours of conditioning at +15 $^{\circ}$ C ~+35 $^{\circ}$ C, R.H 25% ~75%)
	a)After exposure at +85 °C and 85% relative humidity for 200 hours, sensitivity should vary within ±3dB from initial sensitivity. (Normal Condition)
8.5 Humidity	b)After exposure at +80 $^\circ\!\!C$ and 80% relative humidity for 96 hours with 2.75V DC Bias, sensitivity should vary within ±3dB from initial sensitivity. (Limit Condition)
Test	c)After exposure at +60 $^{\circ}$ C and 90% relative humidity for 96 hours with 2.75V DC Bias, sensitivity should vary within ±3dB from initial sensitivity. (Limit Condition) (The measurement to be done after 2 hours of conditioning at +15 $^{\circ}$ C +35 $^{\circ}$ C, R.H 25% ~75%)
8.6	 a) The subject samples to three one-half sine shock pulses (3000 g for 0.3 milliseconds) in each direction (for six axes in total) along each of the three mutually perpendicular axes for a total of 18 shocks, sensitivity should vary within ±3dB from initial sensitivity. (Normal Condition) (The measurement to be done after 2 hours of conditioning at +15 °C ~+35°C, R.H 25% ~75%)
Mechanical Shock Test	b) The subject samples to three one-half sine shock pulses (10000 g for 0.1 milliseconds) in each direction (for six axes in total) along each of the three mutually perpendicular axes for a total of 30 shocks with 2.75V DC Bias, sensitivity should vary within ±3dB from initial sensitivity. (Limit Condition) (The measurement to be done after 2 hours of conditioning at +15 $^{\circ}C$ +35 $^{\circ}C$, R.H 25% ~75%)
8.7 Thermal Shock Test	After exposure at -40 $^{\circ}$ C for 30 minutes, at +125 $^{\circ}$ C for 30 minutes (change time 20 seconds) 32 cycles, sensitivity should vary within ±3dB from initial sensitivity. (Normal Condition) (The measurement to be done after 2 hours of conditioning at +15 $^{\circ}$ C ~+35 $^{\circ}$ C, R.H 25% ~75%)
8.8 Reflow Test	Adopt the reflow curve of item 12.3, after five reflows, sensitivity should vary within ±2dB from initial sensitivity. (Normal Condition) (The measurement to be done after 2 hours of conditioning at +15 °C ~+35°C, R.H 25% ~75%)
8.9 Electrostatic Discharge Test	C=150pF,R=330ohm,Test to ±8KV contact the case,10times ,without grounding; contact discharge ±2KV to I/O terminals,10times, case grounding. (Normal Condition) (The measurement to be done after 2 hours of conditioning at +15 $^{\circ}$ C ~+35 $^{\circ}$ C, R.H 25% ~75%)


9 Package

9.1 Tape Specification





A-A





The Dimensions as Follows:


ITEM	W	E	F	ØD0	ØD1
DIM(mm)	12.0±0.30	1.75±0.10	5.50±0.05	1.50 ^{+0.10}	1.50 MIN
ITEM	P0	10P0	P1	A0	B0
DIM(mm)	4.00±0.10	40.0±0.20	8.00±0.10	3.40±0.10	2.80±0.10
ITEM	K0	P2	Т	ØD2	
DIM(mm)	1.30±0.10	2.00±0.05	0.30±0.05	1.00 MIN	

9.2 Reel Dimension

7" reel for sample stage

13" reel will be provided for the mass production stage


The following is 13" reel dimensions (unit:mm)




9.3 The Content of Box(13" reel)




Packing (5,000PCS)




Antistatic bag (5,000PCS)



Inner Box(5,000PCS)




Five Inner Box(25,000PCS)



Outer Box(25,000PCS) (335mm×335mm×160mm)



9.4 Packing Explain




10 Storage and Transportation


- 10.1 Keep MEMS MIC in warehouse with less than 75% humidity and without sudden temperature change, acid air, any other harmful air or strong magnetic field.
- 10.2 The MEMS MIC with normal pack can be transported by ordinary conveyances. Please protect products against moist, shock, sunburn and pressure during transportation.
- 10.3 Storage Temperature Range : -40 °C ~+100 °C
- 10.4 Operating Temperature Range : -40 $^\circ\!\mathrm{C}\!\sim\!+100\,^\circ\!\mathrm{C}$

11 Land Pattern Recommendation

11.1 The Pattern of MIC Pad(Unit:mm)



11.2 Recommended Soldering Surface Land Pattern(Unit:mm)




1.0

12 Soldering Recommendation

12.1 Soldering Machine Condition


Temperature Control	8 zones	
Heater Type	Hot Air	
Solder Type	Lead-free	

12.2 The Drawing and Dimension of Nozzle



Please don't vacuum over the acoustic port directly, The recommendation is for reference.

12.3 Reflow Profile



Key Features of The Profile:

Average Ramp-up rate(T_{smax} to T_p)	3℃/s max.
Preheat : Temperature Min(T _{smin}) Temperature Max(T _{smax}) Time(T _{smin} to T _{smax})(t _s)	150℃ 200℃ 60~180s
Time maintained above : Tempreature(T _L) Time(t _L)	217℃ 60~150s
Peak Temperature(T _p)	260 ℃
Time within 5 $^\circ\!{\rm C}$ of actual Peak Temperature(t_p) :	30~40s
Ramp-down rate(T _p to T _{smax})	6℃/s max
Time 25 $^\circ\!\!\!\!\!^\circ \mathrm{C}$ to Peak Temperature	8min max

When MEMS MIC is soldered on PCB, the reflow profile is set according to solder paste and the thickness of PCB etc.

13 Cautions

13.1 Board Wash Restrictions

It is very important not to wash the PCBA after reflow process, otherwise this could damage the microphone.

13.2 Nozzle Restrictions

It is very important not to pull a nozzle over the port hole of the microphone. otherwise this could damage the microphone.

14 Output Inspection Standard

Output inspection standard is executed according to <<ISO2859-1:1999>>.