




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - TE CONNECTIVITY ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		T		REVISED PER ECR-20-000541	15MAY2020	PC	SW



- 1 MATERIAL: CONNECTOR - NYLON UL94V-2. (RED)
CONTACTS - 0.30[.012] THICK COPPER ALLOY
BRIGHT TIN-LEAD .00203[.000080] MIN THICKNESS
FOR 640620-2 THRU 2-640620-8.
MATTE WHISKER MITIGATED TIN .00203[.000080] MIN THICKNESS OVER
NICKEL UNDERPLATE FOR 3-640620-2 THRU 5-640620-8.
- 2 CONTACTS ACCEPT 22 AWG WIRE WITH 1.52[.060] MAX
INSULATION DIAMETER.
- 3 CONTACTS MUST ACCEPT 0.64#0.03[.025#.762]
POST AND REMAIN LOCKED IN POSITION.
- 4 IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY
NOT APPEAR ON ALL ASSEMBLIES.
- 5 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 6 HOUSING FEATURES ARE: FEED THRU WITH LOCKING
RAMP.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 8 OBSOLETE PARTS

YES	71.12[2.800]	28	5-640620-8
YES	68.58[2.700]	27	5-640620-7
YES	66.04[2.600]	26	5-640620-6
YES	63.50[2.500]	25	5-640620-5
YES	60.96[2.400]	24	5-640620-4
YES	58.42[2.300]	23	5-640620-3
YES	55.88[2.200]	22	5-640620-2
YES	53.34[2.100]	21	5-640620-1
YES	50.80[2.000]	20	5-640620-0
YES	48.26[1.900]	19	4-640620-9
YES	45.72[1.800]	18	4-640620-8
YES	43.18[1.700]	17	4-640620-7
YES	40.64[1.600]	16	4-640620-6
YES	38.10[1.500]	15	4-640620-5
YES	35.56[1.400]	14	4-640620-4
YES	33.02[1.300]	13	4-640620-3
YES	30.48[1.200]	12	4-640620-2
YES	27.94[1.100]	11	4-640620-1
YES	25.40[1.000]	10	4-640620-0
YES	22.86[.900]	9	3-640620-9
YES	20.32[.800]	8	3-640620-8
YES	17.78[.700]	7	3-640620-7
YES	15.24[.600]	6	3-640620-6
YES	12.70[.500]	5	3-640620-5
YES	10.16[.400]	4	3-640620-4
YES	7.62[.300]	3	3-640620-3
YES	5.08[.200]	2	3-640620-2

NO	71.12[2.800]	28	2-640620-8	SUPERSEDED
NO	68.58[2.700]	27	2-640620-7	
NO	66.04[2.600]	26	2-640620-6	
NO	63.50[2.500]	25	2-640620-5	
NO	60.96[2.400]	24	2-640620-4	
NO	58.42[2.300]	23	2-640620-3	
NO	55.88[2.200]	22	2-640620-2	
NO	53.34[2.100]	21	2-640620-1	
NO	50.80[2.000]	20	2-640620-0	SUPERSEDED
NO	48.26[1.900]	19	1-640620-9	
NO	45.72[1.800]	18	1-640620-8	
NO	43.18[1.700]	17	1-640620-7	
NO	40.64[1.600]	16	1-640620-6	
NO	38.10[1.500]	15	1-640620-5	
NO	35.56[1.400]	14	1-640620-4	
NO	33.02[1.300]	13	1-640620-3	
NO	30.48[1.200]	12	1-640620-2	SUPERSEDED
NO	27.94[1.100]	11	1-640620-1	
NO	25.40[1.000]	10	1-640620-0	
NO	22.86[.900]	9	640620-9	
NO	20.32[.800]	8	640620-8	
NO	17.78[.700]	7	640620-7	
NO	15.24[.600]	6	640620-6	
NO	12.70[.500]	5	640620-5	
NO	10.16[.400]	4	640620-4	SUPERSEDED
NO	7.62[.300]	3	640620-3	
NO	5.08[.200]	2	640620-2	

LEADFREE	DIM A	NO. OF CIRCUITS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER 11JUN2003		TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK D. BOSSI 11JUN2003		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. BOSSI 11JUN2003	MTA 100 CONNECTOR ASSEMBLY, 22 AWG, STANDARD		
0 PLC ± -		PRODUCT SPEC	SIZE	CAGE CODE	DRAWING NO
1 PLC ± -		APPLICATION SPEC	A2	00779	C=640620
2 PLC ± -		108-1050	RESTRICTED TO		
3 PLC ± 0.13 [.005]		114-1019	SCALE 5:1 SHEET 1 OF 1 REV T		
4 PLC ± -		WEIGHT			
ANGLES ± -		CUSTOMER DRAWING			
FINISH					