

Low VF Schottky Barrier Rectifiers


ITO-220AB

FEATURES

- Plastic package has Underwriters Laboratory Flammability Classification 94V-O.
 Flame Retardant Epoxy Molding Compound.
- · Metal silicon junction, majority carrier conduction
- · Low power loss, high efficiency.
- · High current capability
- For use in low voltage, high frequency inverters free wheeling, and polarlity protection applications.
- . Lead free in comply with EU RoHS

MECHANICAL DATA

- Case: ITO-220AB molded plastic
- Terminals: Solder plated, solderable per MIL-STD-750, Method 2026
- Polarity: As marked.
- Mounting Position: Any



Dim.	Min.	Max.			
Α	9.95	10.25			
В	2.95	3.25			
С	1.25	1.45			
D	12.95	13.25			
E	0.50	0.65			
F	3.1	3.3			
G	1.30	1.45			
Н	Typ 2.54				
1	Тур	Typ 5.08			
J	4.60	4.75			
K	2.50	2.65			
L	6.35	6.55			
М	15.4	16.0			
N	2.75	3.05			
0	0.48	0.52			
Р	0.76	0.84			

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%

Characteristics		Symbol	Value	Unit	
Maximum Repetitive Peak Reverse Voltage		V_{RRM}	100	V	
Working Peak Reverse Voltage		V_{RWM}	100	V	
Maximum DC Blocking Voltage		V_{DC}	100	V	
Maximum Average Forward Rectified Current	Per Leg	,	15	А	
	Total	I _O	30		
Peak Forward Surge Current,8.3 ms Single Half Sine-wave		I _{FSM}	220	А	
Operating Temperature Range		T _J	-50 to +150	°C	
Storage Temperature Range		T _{STG}	-50 to +150	°C	
Typical Thermal Resistance (Note1)		$R_{\theta JC}$	4	°C/W	

Note1: Thermal resistance from Junction to case per leg mounted on heatsink.




Low VF Schottky Barrier Rectifiers


ELECTRICAL CHARACTERISTICS(Ta=25°C unless otherwise noted)


Characteristics		Symbol	Va	lue	Unit
Forward Voltage Drop(Note2)			Тур.	Max.	
at I _F =5A	TA=25°C	V _F	0.50	-	
	TA=125°C		0.44	-	
at I _F =10A	TA=25°C		0.58	0.66	V
	TA=125°C		0.56	-	
at I _F =15A	TA=25°C		0.67	0.73	
	TA=125°C		0.63	-	
Maximum Reverse Current at V _R =100V	TA=25°C	l _R	10	70	μA
	TA=125°C		8	-	mA


Note2:Pulse test: 300 µs pulse width, 1 % duty cycle

RATING AND CHARACTERISTIC CURVES









INSTANTANEOUS FORWARD CURRENT (A)