



Recommended PCB Layout(Top view)  
Tolerance:±0.05mm

Specifications:  
规格:  
Voltage rating:250V AC/DC  
额定电压: 250V AC/DC  
Current rating:3A AC/DC  
额定电流: 3A AC/DC  
Withstanding voltage:800V AC/minute  
耐受电压: 800V AC/分钟  
Temperature range:-25℃~+85℃  
温度范围: -25℃~+85℃  
Insulation resistance:≥1000MΩ  
绝缘电阻: ≥1000MΩ  
Contact resistance:≤30mΩ  
接触电阻: ≤30mΩ

X8826 W V - 2xXX R - LP SN  
① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Stright 180°
- 4.Row No.Pin No:2xXX-2x02~2x12Pin
- 5.Special No:R-DIP 2.2mm
- 6.Material:LP-LCP UL94V-0 ,Natural
- 7.Plating:SN- Tin Plated

Poles	Dimensions (mm)			Poles	Dimensions (mm)		
	A	B	C		A	B	C
2x02	2.50	5.70	7.50	2x08	17.50	20.70	22.50
2x03	5.00	8.20	10.00	2x09	20.00	23.20	25.00
2x04	7.50	10.70	12.50	2x10	22.50	25.70	27.50
2x05	10.00	13.20	15.00	2x11	25.00	28.20	30.00
2x06	12.50	15.70	17.50	2x12	27.50	30.70	32.50
2x07	15.00	18.20	20.00				

X8826WV-2xXXR-LPSN	LCP	Brass	X8826H
PART NO	Material	Material(Pin)	Suitable XKB Housing

广东星坤科技股份有限公司

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
△					L ≤ 4	±0.2
△					4 < L ≤ 16	±0.3
△					16 < L ≤ 63	±0.4
					L > 63	±0.5
					UNSPECIFIED TOLERANCES	



DSND		SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connector		
DWN		VIEW:	PART NO.: X8826WV-2xXXR-LPSN		
CHKD		UNIT: mm/in	DWG NO.: X-X8826WV-2xXXR-LPSN		
APPD		SIZE: A4	WEIGHT	SHEET	REVISION
XKB INDUSTRIAL PRECISION CO., LIMITED				1/1	A0

文件工程章