

JW7726BL

Synchronous Rectifier Controller

Preliminary Specifications Subject to Change without Notice

DESCRIPTION

JW[®]7726BL is a synchronous rectifier controller, used for the secondary side rectification of isolation topologies, such as Active Clamp Flyback and CCM/QR/DCM Flyback. By driving an external MOSFET, JW7726BL is able to significantly improve the efficiency comparing with the conventional Diode rectifier.

When JW7726BL senses V_{ds} of MOSFET less than -300mV, it turns on the MOSFET. Once the V_{ds} is greater than -10mV, JW7726BL turns off the MOSFET.

JW7726BL supports multiple operation modes, such as DCM, CrCM, CCM and Quasi-Resonant. By implementing the Joulwatt proprietary technology, JW7726BL is able to handle CCM operation.

JW7726BL is available in SOT23-6 package..

Company's Logo is Protected, "JW" and "JOULWATT" are Registered Trademarks of JoulWatt technology Inc.

FEATURES

- Supports Active Clamp Flyback, DCM, Quasi-Resonant, and CCM Flyback
- Support High-side and Low-side Rectification
- Output voltage directly supply VCC
- Low quiescent current
- Fast driver capability for CCM operation
- SOT23-6 package

APPLICATIONS

- Active clamp Flyback and Flyback converters
- Adaptor
- LCD and PDP TV

TYPICAL APPLICATION




Figure A: JW7726BL Typical Application for low-side.

JW7726BL Rev.0.1 2020/06/29

JoulWatt[®] Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited. This document contains information of a product under development. Joulwatt reserves the right to change this product without notice.





Figure B: JW7726BL Typical Application for high-side.

JW7726BL Rev.0.1 2020/06/29 JoulWatt[®] Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited. This document contains information of a product under development. Joulwatt reserves the right to change this product without notice.

ORDER INFORMATION


DEVICE ¹⁾	PACKAGE	TOP MARKING ²⁾	ENVIRONMENTAL ³⁾
JW7726BLSOTB#TR	SOT23-6	JWJB 🗌 YW 🗌 🗆 🗆	Green

Notes:



3) All Joulwatt products are packaged with Pb-free and Halogen-free materials and compliant to RoHS standards.

PIN CONFIGURATION



ABSOLUTE MAXIMUM RATING¹⁾

SW PIN	1 to 150V
VO PIN	0.3 to 30V
VCC, GT PIN	0.3 to 10V
VT PIN	0.3 to 7V
Continuous Power Dissipation(T _A =+25°C) ²⁾ SOT23-6	0.6W
Junction Temperature ³	150ºC
Lead Temperature	
Storage Temperature	65ºC to150ºC
ESD Susceptibility (Human Body Model)	2kV

JW7726BL Rev.0.1 2020/06/29 JoulWatt[®] Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.

This document contains information of a product under development.

 θ_{IA}

 θ_{Jc}

RECOMMENDED OPERATING CONDITIONS

SW Pin	4.7V to 130V
VO Pin	4.7V to 27V
VCC, GT PIN	4V to 8V
Operation Junction Temp.	40°C to 125°C

THERMAL PERFORMANCE⁴⁾

Note:

- 1) Exceeding these ratings may damage the device.
- 2) TA=25 °C. The maximum allowable power dissipation is a function of the maximum junction temperature $T_J(MAX)$, the junction-to-ambient thermal resistance θ_{JA} , and the ambient temperature T_A . The maximum allowable continuous power dissipation at any ambient temperature is calculated by $P_D(MAX)=(T_J(MAX)-T_A)/\theta_{JA}$.
- 3) The JW7726BL guarantees robust performance from -40°C to 150°C junction temperature. The junction temperature range specification is assured by design, characterization and correlation with statistical process controls.
- 4) Measured on JESD51-7, 4-layer PCB.

ELECTRICAL CHARACTERISTICS

Item	Symbol	Condition	Min.	Тур.	Max.	Units
VCC Section						
VCC Voltage	VCC	SW=40V, VCC=2.2uF	7.5	8	8.5	V
VCC Startup voltage	V _{CC_Startup}			4.5		V
VCC UVLO	V _{CC_UVLO}			3.9		V
Operation Current (Switching)	I _{SW}	GT=5nF, Fsw=100KHz		3.2		mA
Operation Current (GT On)	I _{VCC}	GT=5nF,VCC=2.2uF		900		uA
Quiescent Current	lq	VCC=4.5V, VCC=2.2uF		70		uA
Gate Section						
Gate Turn on Threshold	V _{MOS_ON}			-150		mV
Gate Turn off Threshold	V_{MOS_OFF}			-10		mV
Gate Turn off Threshold in MOT	V _{GTOFF_MOT}			1		V
Gate Turn on Voltage	V _{GT}	SW=32V, VCC=2.2uF	V _{CC} -1	V _{CC}		V
Maximum Gate Pull up current	I _{GU}			0.65		А
Maximum Gate Pull down current	I _{GD}			4.7		А
Gate Minimum on Time	T _{MIN_ON}			1.1		us
Absolutely Minimum off Time	T_{MIN_OFF}			350		nS
Turn off blanking threshold	$V_{OFF_MIN_OFF}$		2	2.5	3	V
Turn-on total delay	T _{DON}	$R_{GATE}=0 \Omega$, $C_{LOAD}=4.7 nF$		50		nS
Turn-off total delay	T _{DOF}	$R_{GATE}=0 \Omega$, $C_{LOAD}=4.7 nF$		20		nS
SW and VO Section						
VCC Charge Current	I _{SW_CHG}	SW=40V, VCC=6V		80		mA
SW Regulation Voltage	V_{MOS_REG}			-40		mV
SW Control Voltage MAX	$V_{MOS_REG_MAX}$			-160		mV
VO Enable Charge Voltage	Vo_en	VCC=4V, SW=0V, rising		4.6		V
VO Disable Charge Voltage	V _{O_DIS}	VCC=4V, SW=0V, falling		4.5		V
VO Charge Current	Ivo_chg	SW=0V, VCC=6V, VO=12V		40		mA

JW7726BL Rev.0.1 2020/06/29 JoulWatt® Proprietary Information. Patent Protected.


Unauthorized Photocopy and Duplication Prohibited.

This document contains information of a product under development.

PIN DESCRIPTION

Part No.	Name	Description
5	GT	Drive the External NMOSFET.
2	GND	Ground.
4	VCC	Power supply. Bypass a Capacitor Between VCC and GND.
3	VT	Set the voltage-second product.
1	VO	Output Voltage Sensing and Charging to VCC.
6	SW	External Power MOSFET Drain Voltage Sensing. Charging to VCC.

BLOCK DIAGRAM



JW7726BL Rev.0.1 2020/06/29

JoulWatt[®] Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited. This document contains information of a product under development.

6

accument contains information of a product under development

FUNCTIONAL DESCRIPTION

Operation

JW7726BL is a synchronous rectifier controller which combined with external MOSFET can replace the Schottky Barrier Diode. It supports all operations, such as DCM, CrCM, (Quasi-Resonant) and CCM when adopted in Active Clamp Flyback and Flyback converters.

Startup

During the startup period, when the VCC is charged up by the two internal LDOs connected to SW and VO pin respectively.

When VO is lower than 4.5V (falling), JW7726BL can power itself through the internal LDO connected to SW pin during the SR turn-off period, which means primary the primary side MOSFET is turned on and SW presents a positive voltage. A capacitor between VCC and GND is required to store the energy and supply to IC during the SR turn-on period.

When VO is above 4.6V (rising), the VO pin charges VCC pin.

Once the VCC voltage exceeds $V_{CC_Startup}$, the JW7726BL exits the UVLO. If VCC is lower than V_{CC_UVLO} , the external MOSFET is turned off. The current flows though body diode before the VCC reaches to the startup voltage $V_{cc_startup}$.

Under-Voltage Lockout (UVLO)

When the VCC is below UVLO threshold, the external MOSFET is turned off and pulled low internally. Once the VCC exceeds the startup voltage Vcc_startup, the parts is activated again.

Turn On Phase

There are two conditions for the JW7726BL to turn on the SR, i.e. Vsw, voltage-second value on SW pin when primary side switch is on, and the turn on phase is shown in Fig. 1.

1) Vsw: when the synchronous MOEFET is conducting, current flows through the body diode of MOSFET, which generates a negative voltage V_{SW} across it. When V_{SW} is lower than V_{MOS_ON} , the part will pull the gate high to turn on the synchronous MOSFET after turn on delay time T_{DON} if the other condition is met.

2) Volt-second of SW: in DCM and QR operation, there are parasitic oscillations. In some applications, the drain resonant voltage may below the SR turn on threshold, especially for the first couple rings. SR could be falsely turned on, which may cause shoot through issue and result in high power loss. The volt-second value of SW pin can be used to distinguish the parasitic ring from normal primary side switch on. The threshold can be set by the resistance from at VT pin. The curve is shown in Fig. 2.




Figure. 1 Turn on delay and turn off delay

JW7726BL Rev.0.1 2020/06/29 JoulWatt[®] Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited. This document contains information of a product under development. Joulwatt reserves the right to change this product without notice. 7




Figure-3 Volt-second value vs. VT resistance

Minimum On Time (MOT)

When the synchronous MOSFET is turn on, there is a minimum on time for the SR. The V_{SW} voltage may have a parasitic ring when the synchronous MOSFET turns on. So, a minimum on time (MOT) is very important to avoid the MOSFET turn off threshold is false triggered. Minimum on time is 1.1us for high frequency applications. During the minimum time, the gate can still be turned off if V_{SW} touches a positive threshold value, +1V.

Conducting Phase

When the synchronous MOSFET is turned on, the drain source voltage V_{SW} it is determined by its on resistance and the current through it. The part adjusts the gate voltage and regulates the Vsw to a internal threshold (typical -40mV) after the synchronous MOSFET turn on. When the

 V_{SW} is lower than -40mV, the gate keep its maximum voltage. And the synchronous MOSFET is fully on.

The V_{SW} rises when the current follow through the MOSFET decreases. The gate voltage will be decreased to increase its on resistance and regulate the V_{SW} around -40mV.

It should be noted that the typical regulation threshold (-40mV) during MOSFET on time is not fixed, it can be internally changed to ensure the proper operation under CCM mode.

Turn Off Phase


After synchronous MOSFET conducting, once the voltage V_{SW} touches the MOSFET turn off threshold (-10mV), the gate is pulled to low after a turn off delay time T_{DOFF} . A 350nS blanking time is necessary to avoid error trigger. The banking time is reset once Vsw rises above 2V.

Output Voltage Detection

The JW7726BL has output voltage detection function via VO pin. VCC is charged from VO pin when VO is higher than 4.6V to save power loss caused by the LDO when charging from SW pin to VCC pin. When VO drops below 4.5V, the JW7726BL is powered from SW pin.

JW7726BL Rev.0.1 2020/06/29 JoulWatt[®] Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited. This document contains information of a product under development. Joulwatt reserves the right to change this product without notice.

PACKAGE OUTLINE



$\label{eq:source} \mbox{JoulWatt}^{\mbox{${\scriptscriptstyle \mathbb{B}}$}} \mbox{ Proprietary Information. Patent Protected.}$

Unauthorized Photocopy and Duplication Prohibited.

This document contains information of a product under development.

IMPORTANT NOTICE

- Joulwatt Technology Inc. reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein.
- Any unauthorized redistribution or copy of this document for any purpose is strictly forbidden.
- Joulwatt Technology Inc. does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

Copyright © 2020 JW7726BL Incorporated.

All rights are reserved by Joulwatt Technology Inc.

JW7726BL Rev.0.1 2020/06/29

JoulWatt[®] Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.

This document contains information of a product under development. Joulwatt reserves the right to change this product without notice.