


SCHEMATIC



SPECIFICATION

规格

1. Rating: DC 30V, 2A

额定值: 直流30V, 2A

2. Contact resistance: ≤0.02Ω

接触电阻: ≤0.02Ω

3. Insulation resistance: 100mΩ

绝缘电阻: 100mΩ

4. Withstand voltage: 250V/min

耐压: 250V/min

5. Insertion and extraction force: 3-15N

插拔力: 3-15N

6. life: 5, 000 cycles

寿命: 5, 000次循环

5	Terminal	1	Brass	Plating silvering
4	Terminal	1	Brass	Plating silvering
3	Terminal	1	Phosphor copper	Plating silvering
2	Cover	1	PBT	-
1	Plastic	1	PBT	-
LTR	PART NAME	1	MATERIAL	PLATED

广东星坤科技股份有限公司

生

日期

ΔX

敬

日期

ΔX

文件

DESIGNER

MARK

文件工程章

REVISIONS

DATE

REVISED

APPROVED

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

XKIB

DSND		SCALE: N/A	MODEL TYPE: DC POWER JACK
DWN		VIEW:	PART NO.: DC-011-2.0A-0.65
CHKD		UNIT: mm/in	DWG NO.: X-DC-011-2.0A-0.65
APPD		SIZE: A4	

XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0