



■ Specifications :

- Voltage rating: 125V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤20mΩ
- After environmental testing: ≤30mΩ

X9515 H M-XX XX-XX XX

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category: H-HSG
- ③ Appearance type: M-male HSG
- ④ Row No.-Pin No.: XX-02P~20P
- ⑤ Plug the Pin & special No.:
- ⑥ Material: N0-PA66 UL 94V-0
PT-PBT UL 94V-0
- ⑦ HF-Halogen Free



Poles	Dimensions (mm)			Poles	Dimensions (mm)		
	A	B	C		A	B	C
02	2.00	6.60	4.60	12	22.00	26.60	24.60
03	4.00	8.60	6.60	13	24.00	28.60	26.60
04	6.00	10.60	8.60	14	26.00	30.60	28.60
05	8.00	12.60	10.60	15	28.00	32.60	30.60
06	10.00	14.60	12.60	16	30.00	34.60	32.60
07	12.00	16.60	14.60	17	32.00	36.60	34.60
08	14.00	18.60	16.60	18	34.00	38.60	36.60
09	16.00	20.60	18.60	19	36.00	40.60	38.60
10	18.00	22.60	20.60	20	38.00	42.60	40.60
11	20.00	24.60	22.60				

X9515HM-XX-N0HF	PA66 UL 94V-0 Halogen Free	X9515TF	X9515HF
X9515HM-XX-PT	PBT UL 94V-0		
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
 香港星坤工業精密有限公司

△ X					ANGULAR	±5°
△ X					L ≤ 4	±0.2
△ X					4 < L ≤ 16	±0.3
△ X					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5

DSND		DATE		SCALE: N/A	MODEL TYPE: X9515HM-XXXX-XX
DWN		DATE		VIEW:	PART NO.: 2.00mm Crimp Style Connectors
CHKD		DATE		UNIT: mm	DWG NO.:
APPD		DATE		SIZE: A4	
				XKB INDUSTRIAL PRECISION CO., LIMITED	WEIGHT 1.0g
					SHEET 1/1
					REVISION A0

REVISIONS
 Authorized Signature(s)

UNSPECIFIED TOLERANCES