





PRODUCT NO.	RoHS compliant
DSDP01LHGETB	

REV.	ECN NO.	DR	DATE




P.C.B LAYOUT

Note:

- All dimensions are in millimeters.
- General tolerance: $\pm 0.2\text{mm}$.
- Material:
 - Base: UL94V-0 PBT Thermoplastic (Black).
 - Cover: UL94V-0 PBT Thermoplastic (Black/Red/Blue).
 - Actuators: UL94V-0 PBT Thermoplastic (White).
 - Contact plating: Gold plating over nickel.
 - Pitting material: Epoxy.
- Electrical
 - Electrical: 2000 Operations per switch 24/VDC, 25mA.
 - Non-Switching Rating: 100mA, 50/VDC.
 - Switching Rating: 25mA, 24/VDC.
 - Contact Resistance: 100 m Ω Max. at initial.
- Mechanical
 - Mechanical life: 2000 Operations per switch.
 - Stroke: 30°.
 - Operation Temp: -20°C to 70°C.
 - Storage Temp: -40°C to 85°C.

6. PART NUMBER DESCRIPTION:



注意:

- 波峰焊: 推荐焊锡温度在 270°C \pm 5°C, 浸锡时间为 5~6 秒钟。
- 手工焊: 使用 30 瓦烙铁控制温度在 320°C, 焊接时间大约 2~3 秒钟。
- 拨柄位置: 产品焊接时, 请将产品的拨柄置于 OFF 端, 能给予产品更好的接触性能。
- 清洗过程: 清洗使用超声波方式, 能给予更好的效果。

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	东莞市广普实业有限公司 DongGuan Kingtek Industrial Co., Ltd.
LINEAR	ANGLES		
.0 \pm 0.40	0. \pm 1'	PROJECTION	TITLE
.00 \pm 0.30	.0 \pm 0.5'		BY DSDP SERIES PITCH 2.54mm
.000 \pm 0.20	.00 \pm		PRODUCT FAMILY DSDP SERIES
DESIGN LU ER XIN	2013/07/08		PRAT NO. DSDP01LHGETB
DRAWING		FILE NO. DSDP01LHGETB-A	
CHECK		SIZE UNIT SCALE SHEET REV.	
APPD.		A4 mm FIT 1 OF 1 A	