



CAD FILE:



$$A = 1.27 * \frac{nP}{2} + 0.4 \pm 0.35$$

$$B = 1.27 * \frac{nP}{2} - 1.27 \pm 0.2$$

Pin Number=2~100

Technical Data

Material:

Contact material: Phosphor bronze

Plating: Gold Flash

Insulator material: Black polyester UL94V-0

Standard: PA6T+30%G.F

Electrical:

Current rating: 1.0Amps/contact max.

Contact resistance: $\leq 20m\Omega$ /contact



Insulation resistance: $\geq 1000M\Omega$ at $V=100V$

Withstanding voltage: 300V AC/minute

Mechanical:

Soldering temperature: +260°C, 4s max

UNSPECIFIED TOLERANCE: ± 0.20



PCB Layout

APPROVALS						DATE		DEALON 德之隆® ELECTRONICS CO.,LTD				
DRAWN		G.M.Chen		2015/5/22				TITLE: CONNECTOR				
CHECKED								PART NO. DW127S-22-XX-43				
APPROVALS								UNIT: mm		SCALE: 1:1		SHEET 1 OF 1
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	30~PL: ± 0.30	ANGLE	DRAWING NO.	PROJ:	
	A		NEW				10~30 ± 0.20		$\pm 2'$			
							5~10 ± 0.15					
							~ 5 ± 0.10					