

PRODUCT NO. DSIC12TSGE T	RoHS compliant
-----------------------------	----------------

REV.	ECN NO.	DR	DATE
------	---------	----	------

NOTES :




- 1.Specification:
  - 1>.Operating force:1000gf Max
  - 2>.Operating Temperature:-40° to+85°
  - 3>.Storage Temperature:.-40° to+85°
  - 4>.Mechanical Life:3000cycles minimum
  - 5>.Electrical Life:2000cycles minimum

2. PLATING:
  - GOLD FLASH 1u"~2u" SOLDER TAIL,
  - 1u"~3u" GOLD PLATING ON THE CONTACT AREA,
  - WITH 50u" NICKEL UNDERPLATING OVERALL.


3. PART NUMBER DESCRIPTION

DSIC XX T S G E T


- [包装方式: T=管装 R=Reel]
- [电镀层:E=接触部1u"~3u" /焊尾部1u"~2u"]
- [G=镀金 S=内金外镍]
- [脚型: S脚 / J脚 / H脚 / A脚 / Z脚]
- [T=低推贴胶 S=低推不贴胶 L=长推]
- [产品数: 02=2P ..... 08=8P 10=10P 12=12P]





[Schematic]



[剖面行程]



(Construction)



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)

Number	Part Name	Material	Finished	TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY
				LINER	ANGLES	
①	Actuator	UL94 V0	White	.0 ± 0.25	0. ± 2'	PROJECTION 2012/04/12
②	Cover	UL94 V0	Black	.00 ± 0.15	.0 ± 1'	
③	Movable	Copper Alloy	1u"~3u"Gold	.000± 0.10	.00± 0.5'	
④	Terminal	Brass	1u"~2u"Gold			
⑤	Base	UL94 V0	Black			
⑥	Terminal Contact	Brass	1u"~3u"Gold			
⑦	Mylar	UL94 V0	0.05mm			

**KE** 东莞市广普实业有限公司  
DongGuan Kingtek Industrial Co., Ltd.

TITLE: BY DSIC SERIES PITCH 2.54mm

PRODUCT FAMILY DSIC SERIES

PRAT NO. DSIC12TSGE T

FILE NO. DSIC12TSGE T-A

SIZE	UNIT	SCALE	SHEET	REV.
A4	mm	2 : 1	1 OF 1	A