

US1AU THRU US1MU


1.0AMP Ultra Fast Recovery Silicon Rectifier

Features

- · Low Power Loss, High Efficiency
- Ideally Suited for Automatic Assembly
- Guard Ring Die Construction
- Plastic Case Material has UL Flammability Classification Rating 94V- 0

Mechanical Data

- . Case: Molded plastic SMA
- Terminals: Plated leads solderable per MIL-STD-750,Method 2026 guaranteed
- · Polarity: Color band dentes cathode end
- Mounting Position: Any
- · Making: Type Number



Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified

Single phase, half wave, 60Hz, resistive or inductive load

For capacitive load derate current by 20%

Type Number	SYMBOL	US1AU	US1BU	US1DU	US1GU	US1JU	US1KU	US1MU	Unit
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1000	V
Average Rectified Output Current @T∟ =100°C	IF(AV)	1.0							Α
Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method)	İfsm	35							Α
Rating for fusing (t<8.3ms)	l²t	5.08						A^2s	
Forward Voltage @IF=1.0A	V _{FM}	1.0 1.3 1.7					V		
Peak Reverse Current @T _A =25 ℃	5.0								
At Rated DC Blocking Voltage @T₄ =125 °C	lR	200							uA
Maximum Reverse Recovery Time (Note 1)	Trr	50 75					ns		
Typical Junction Capacitance (Note 2)	С	20						pF	
Typical Thermal Resistance Junction to Ambient (Note 3)	Rθ JA	70						°C/W	
Operating Temperature Range	TJ	-55 to+150						$^{\circ}\!\mathbb{C}$	
Storage Temperature Range	Тѕтс	-55 to +150						$^{\circ}\!\mathbb{C}$	

Note:

- 1.Reverse Recovery Test Conditions:IF=0.5A,IR=1.0A,IRR=0.25A.
- 2. Measured at 1.0 MHz and Applied reverse Voltage of 4.0V D.C
- 3. Device mounted on FR-4 substrate, 1"*1", 2oz, single-sided, PC boards with 0.1"*0.15" copper pad.

version:05 1of3

1.0AMP Ultra Fast Recovery Silicon Rectifier

AVERGE FORWARD RECTIFIED CURRENT,(A)

FIG.1MAXIMUM AVERAGE FORWARD CURRENT DERATING





FIG.3MAXIMUM NON-REPEITIVE SURGE CURRENT






FIG.2TYPICAL FORWARD CHARACTERISTICS






FIG.4TYPICAL JUNCTION CAPACITANCE



SMA PAD LAYOUT



version:05 2of3



US1AU THRU US1MU

1.0AMP Ultra Fast Recovery Silicon Rectifier

Important Notice and Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from XINNUO
- XINNUO reserves the right to make changes to this document and its products and specifications
- XINNUO disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- XINNUO does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the here in document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications.
 - XINNUO makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown here in are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own ris k andagree to fully indemnify XINNUO for any damages resulting from such improper use or sale.
- Since XINNUO uses lot number as the tracking base, please provide the lot number for tracking when complaining.

version:05 3of3