

LIGHT EMITTING DIODE SPECIFICATION

CUSTOMER NAME:

DESCRIPTION: EL302RD

REVISION: V2.2

ISSUE DATE: 2018-07-25

Contains trade secret information which is the property of Ekinglux and shall not be made available to, or copied or used by anyone outside Ekinglux without its written authorization. Copyright © 2017 Ekinglux Optoelectronics Technology Co., Ltd. All rights reserved

<u>www.ekingluxs.com</u> <u>Sales@ekingluxs.com</u>



Features:

- Long operating life
- •Low Power Consumption
- •Low voltage DC operated
- ●RoHS Compliant

Application:

- Status indicator
- •Industrial control panel
- Sensor status indication
- Wearable and portable devices



Part Number	Dice Material	Emitted Color	Lens Color
EL302RD	AlGaInP	Red	Red Diffused

Electro-Optical Characteristics(Ta=25°C, @20mA)

Parameter	Symbol	Min.	Тур.	Max.	Unit
Luminous Intensity	IV	200	-	400	mcd
Radiation Bandwidth	Δλ	-	45	-	nm
Forward Voltage	VF	1.90	2.00	2.40	V
Peak Wavelength	λр	-	630	-	nm
Dominant Wavelength	λd	620	625	630	nm
CIE Coordinates CIE	x,y	-	-	-	-
Color Temperature	Tc	-	-	-	k
Viewing Angle	201/2	-	60	-	deg
Reverse Current	IR	-	-	10	uA

Absolute Maximum Ratings(Ta=25℃)

Parameter	Symbol	Max.	Unit
Peak Forward Current(1/10 Duty Cycle, 0.1ms Pulse Width)	IPF	100	mA
Forward Current	IF	30	mA
Reverse Voltage	VR	5	v
Electrostatic Discharge	ESD	2000	v
Operating Temperature Range	Topr	-40to+90	°C
Storage Temperature Range	Tstg	-40to+90	°C
Reflow Soldering	Tsld	sld 260°Cfor 10secs	

www.ekingluxs.com Sales@ekingluxs.com



Optical & Electrical Characteristics



550

Wavelength (nm)

600

650

700


Forward Current vs. Forward Voltage

0% 350


400

450

500




Relative Intensity vs.Forward Currenr




Forward Current vs. Ambient Temperature

750

800



Relative Intensity vs. Ambient Temperature



1.0

0° 20° -30° 30° Ta=25°c 40° -40° 50° -50 -60° 60° -70° 70° 80° -80 -90°L 90°

Radiation Pattern

Sales@ekingluxs.com www.ekingluxs.com



Bin Limits

Bin Range Of Luminous Intensity (Unit:mcd)

Bin Code	Min	Max	Condition
L1	200	400	
L2	-	-	IF=20mA
L3	-	-	

Bin Range Of Forward Voltage (Unit:V)

Bin Code	Min	Max	Condition
V1	1.9	2.0	
V2	2.0	2.1	
V3	2.1	2.2	IF=20mA
V4	2.2	2.3	
V5	2.3	2.4	

Bin Range Of Wavelength (Unit:nm)

Bin Code	Min	Max	Condition
R1	620	622	
R2	622	624	
R3	624	626	IF=20mA
R4	626	628	
R5	628	630	

Notes:

1.Tolerance of Luminous Intensity ±10%

2.Tolerance of Forward Voltage ±0.1V



Reliability Test Items And Conditions

Test Items	Reference	Test Conditions	Time	Quantity	Criterion
Thermal Shock	MIL-STD-202G	-40°C (30min) -100°C (30min)	100 Cycles	22	0/22
Temperature And Humidity Cyclic	JEITA ED-4701 200 203	-10˚C~65˚C; 0%~90%RH	10cycles	22	0/22
High Temperature Storage	JEITA ED -4071 200 201	Ta=100℃	1000H	22	0/22
Low Temperature Storage	JEITA ED -4071 200 202	Ta=-40°C	1000H	22	0/22
High Temperature High Humidity Storage	JEITA ED -4071 100 103	Ta=60˚ℂ ; RH=90%	1000H	22	0/22
High Temperature Life Test	JESD22-A108D	Ta=80°C	1000H	22	0/22
Life Test	JESD22-A108D	Ta=25 ℃ IF=20mA	1000H	22	0/22
Resistance to Sodering Heat	GB/T 4937, II , 2.2&2.3	Tsol*=(240±5) ℃10secs	2 times	22	0/22


Criteria For Judging Damage


Test Items	Symbol	Test Conditions	Criteria For Judging Damage
Forward Voltage	V_{F}	I _F =I _{FT}	Initial Data±10%
Recerse Current	I_R	V _R =5V	I _R ≤10uA
Luminous Intensity	IV	I _F =I _{FT}	Average I _V degradation≤30%; Single LED I _V degradation≤50%
Resistance to Soldering Heat	-	-	Meterial without internal cracks,no meterial between stripped,no deaded light

www.ekingluxs.com Sales@ekingluxs.com



Product size (Unit:mm)





□ 0.5 SQUARE*2



Notes:

1. All dimensions are in millimeters (inches).

2. Tolerance is ±0.25(0.01") unless otherwise noted.

3. Lead spacing is measured where the leads emerge from the package.




LabelStyle



LOT NO.:XXXXXXX

Packaging





Precautions

1. Lead Forming

- 1.1 During lead formation, the leads should be bent at a point at least 3mm from the base of the epoxy bulb.
- 1.2 Lead forming should be done before soldering.
- 1.3 Avoid stressing the LED package during leads forming. The stress to the base may damage the LED's characteristics or it may break the LEDs.
- 1.4 Cut the LED lead frames at room temperature. Cutting the lead frames at high temperatures may cause failure of the LEDs.
- 1.5 When mounting the LEDs onto a PCB, the PCB holes must be aligned exactly with the lead position of the LED. If the LEDs are mounted with stress at the leads, it causes deterioration of the epoxy resin and this will degrade the LEDs.

2. Storage


- 2.1 The LEDs should be stored at 30°C or less and 70%RH or less after being shipped from Everlight and the storage life limits are 3 months. If the LEDs are stored for 3 months or more, they can be stored for a year in a sealed container with a nitrogen atmosphere and moisture absorbent material.
- 2.2 Please avoid rapid transitions in ambient temperature, especially, in high humidity environments where condensation can occur.

3. Soldering

- 3.1 Careful attention should be paid during soldering. When soldering, leave more then 3mm from solder joint to epoxy bulb, and soldering beyond the base of the tie bar is recommended.
- 3.2 Recommended soldering conditions:

Hand Soldering		DIP Soldering		
Temp. at tip of iron	300℃ Max. (30W Max.)	Preheat temp.	100°C Max. (60 sec Max.)	
Soldering time	3 sec Max.	Bath temp. & time	260 Max., 5 sec Max	
Distance	3mm Min.(From solder	Distance	3mm Min. (From solder	
	joint to epoxy bulb)		joint to epoxy bulb)	

3.3 Recommended soldering profile



www.ekingluxs.com

Sales@ekingluxs.com





- 3.4 Avoiding applying any stress to the lead frame while the LEDs are at high temperature particularly when soldering.
- 3.5 Dip and hand soldering should not be done more than one time
- 3.6 After soldering the LEDs, the epoxy bulb should be protected from mechanical shock or vibration until the LEDs return to room temperature.
- 3.7 A rapid-rate process is not recommended for cooling the LEDs down from the peak temperature.
- 3.8 Although the recommended soldering conditions are specified in the above table, dip or hand soldering at the lowest possible temperature is desirable for the LEDs.
- 3.9 Wave soldering parameter must be set and maintain according to recommended temperature and dwell time in the solder wave.

4. Cleaning

- 4.1 When necessary, cleaning should occur only with isopropyl alcohol at room temperature for a duration of no more than one minute. Dry at room temperature before use.
- 4.2 Do not clean the LEDs by the ultrasonic. When it is absolutely necessary, the influence of ultrasonic cleaning on the LEDs depends on factors such as ultrasonic power and the assembled condition. Ultrasonic cleaning shall be pre-qualified to ensure this will not cause damage to the LED

<u>www.ekingluxs.com</u> <u>Sales@ekingluxs.com</u>