



Recommended PCB Layout(Top view)  
Tolerance:±0.05mm

Specifications:

规格:  
Voltage rating:250V AC/DC  
额定电压: 250V AC/DC  
Current rating:2A AC/DC  
额定电流: 2A AC/DC  
Withstanding voltage:1000V AC/minute  
耐受电压: 1000V AC/分钟  
Temperature range:-25°C~+105°C  
温度范围: -25°C~+105°C  
Insulation resistance:≥1000MΩ  
绝缘电阻: ≥1000MΩ  
Contact resistance:≤20mΩ  
接触电阻: ≤20mΩ

X2016 W R - XX B R - LP SN  
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1. Series No
2. Category:W-Wafer
3. Welding Board Angle:R-Stright 90°
4. Row No.Pin No:XX-02~16Pin
5. Special No:B-With Baffle
6. Special No:R-DIP 2.2mm
7. Material:LP-LCP UL94V-0 ,Natural
8. Plating:SN- Tin Plated

Poles	Dimensions (mm)			Poles	Dimensions (mm)		
	A	B	C		A	B	C
02	2.00	4.90	6.00	10	18.00	20.90	22.00
03	4.00	6.90	8.00	11	20.00	22.90	24.00
04	6.00	8.90	10.00	12	22.00	24.90	26.00
05	8.00	10.90	12.00	13	24.00	26.90	28.00
06	10.00	12.90	14.00	14	26.00	28.90	30.00
07	12.00	14.90	16.00	15	28.00	30.90	32.00
08	14.00	16.90	18.00	16	30.00	32.90	34.00
09	16.00	18.90	20.00				

X2016WR-XXBR-LPSN	LCP	Brass	X2016H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connector
DWN		VIEW:	PART NO.: X2016WR-XXBR-LPSN
CHKD		UNIT: mm/in	DWG NO.: X-X2016WR-XXBR-LPSN
APPD		SIZE: A4	WEIGHT SHEET REVISION
			1/1 A0



XKB INDUSTRIAL PRECISION CO.,LIMITED

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

广东星坤科技股份有限公司

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED
Δ	日期			
Δ	日期			
Δ	日期			
REVISIONS				