



$A = 2.0 * \frac{nP}{2} \pm 0.40$
 $B = 2.0 * \frac{nP}{2} - 2.0 \pm 0.20$
 Pin Number=2~80



PCB Layout

Technical Data
 Material:
 Contact material:Brass
 Plating:Gold Flash
 Insulator material:Black polyester UL94V-0
 Standard:PA6T+30%G.F

Electrical:
 Current rating:1.5amps/contact max
 Contact resistance: $\leq 20m\Omega$ /contact
 Insulation resistance: $\geq 1000M\Omega$ at V=100V
 Withstanding voltage:450V AC/minute

Mechanical:
 Soldering temperature: $+260^{\circ}C$ 4s max
 UNSPECIFIED TOLERANCE: ± 0.20

APPROVALS		DATE	DRAWING NO.		
DRAWN	G.M.Chen	2015/7/17	D/2200S-22-XX-64		
CHECKED			CONNECTION		
APPROVALS			PART NO.		
DRAWN		DATE	UNIT: mm	SCALE: 1:1	SHEET 1 OF 1
CHECKED			ANGLE	±2°	PROJ
APPROVALS			TOLERANCES ARE		
DRAWN			30°±0.1°	±0.30	
CHECKED			10°±0.1°	±0.20	
APPROVALS			5°±0.1°	±0.15	
DRAWN			±2°		
CHECKED					
APPROVALS					
ECN NO.	REV.	DATE.	DESCRIPTION.		
	A		NEW		