




RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.


REV.	ECN. NO.	APPD.





SCHMATIC



P.C.B.LAYOUT(TOP VIEW)



A'-A'



A'-A' VIEW

*CRITICAL DIMENSION

ELECTRICAL CHARACTERISTICS

1. RATING: DC 30V 0.1A
2. CONTACT RESISTANCE: 100mΩ MAX
3. INSULATION RESISTANCE: 100MΩ MIN
4. DIELECTRIC STRENGTH: AC 250V (50~60Hz)/60S

MECHANICAL CHARACTERISTICS

1. PRACTICAL TEMPERATURE RANG: -40°C~+85°C
2. OPERATING FORCE: 180±50gf
3. MECHANICAL LIFE: 20,000 cycles

7	CAM STICK	1	SUS	NATURAL
6	TERMINAL	6	BRASS STRIP	Ag COATING
5	CASE	1	PA66	GRAY
4	CONTACT	2	BRONZE	Ag CLAD
3	COVER	1	PPA	BLACK
2	SPRING	1	SUS	NATURAL
1	KNOB	1	POM	BLUE
NO.	PART NAME	Q' TY	MATERIAL	FINSH/COLOR

X.	±0.50	X.°	±2°	UNITS mm
.X	±0.30	.X°	±1°	
.XX	±0.10	.XX°	±0.5°	MAT'L
.XXX	±0.05			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD				FINISH
				Q' TY

yiYUAN 深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO., LTD

PART NO. YTS70NL180DU	TITLE: 拨动开关7.0*7.0 插脚 3.9*3.9 秊秊
APPD: ROGER	DWG NO.: YTS70NL180DU
CHKD: ROC	
DR: BILLY WANG 2020/08/21	
	SCALE SHEET REV. 1/1 1/1 A1