




SCHOTTKY BARRIER RECTIFIERS

FEATURES

- Metal silicon junction, majority carrier conduction
- Guarding for overvoltage protection
- Low power loss, high efficiency
- High current capability
- low forward voltage drop
- High surge capability
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications

PINNING

| PIN | DESCRIPTION |
|-----|-------------|
| 1 | Cathode |
| 2 | Anode |



MECHANICAL DATA

- Case: SOD-123W
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 16mg/0.00056oz

Maximum Ratings and Electrical characteristics

Ratings at 25 °C ambient temperature unless otherwise specified.

| Parameter | Symbols | BAT54WA | Units |
|---------------------------------------------------------------------------------------------------|-----------------|-----------------------------------------|-------|
| Peak Repetitive Reverse Voltage | V_{RRM} | 30 | V |
| RMS reverse voltage | $V_{R(RMS)}$ | 21 | V |
| Maximum Average Forward Current at $T_a=25^\circ C$ | I_o | 0.2 | A |
| Peak Forward Surge Current, 8.3ms single half sine-wave superimposed on rated load (JEDEC method) | I_{FSM} | 0.6 | A |
| Maximum Instantaneous Forward Voltage | V_F | 0.32 @ $I_F=0.001A$ 1.0 @ $I_F=0.1A$ | V |
| Maximum DC Reverse Current at Rated DC Blocking Voltage | I_R | 2.0 @ $V_R=25V$ | uA |
| Typical Thermal Resistance | $R_{\theta JA}$ | 610 | °C/W |
| Typical Junction Capacitance at $V_R=0V$, $f=1MHz$ | C_j | 60 | pF |
| Storage and Operating Junction Temperature Range | T_j, T_{stg} | -55 ~ +125 | °C |

NOTES:(1)P.C.B. mounted with 5*5mm copper pad areas.



Fig.1 Forward Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.4 Typical Forward Characteristics




Fig.4 Typical Junction Capacitance





Fig.5 Typical Transient Thermal Impedance






PACKAGE OUTLINE

Plastic surface mounted package; 2 leads


SOD-123W



SOD-123W mechanical data

| UNIT | | A | C | D | E | E ₁ | L ₁ | b | A ₁ | ∠ |
|------|-----|-----|------|-----|-----|----------------|----------------|-----|----------------|----|
| mm | max | 1.3 | 0.22 | 1.8 | 2.8 | 3.9 | 0.45 | 0.7 | 0.2 | 9° |
| | min | 0.9 | 0.09 | 1.5 | 2.5 | 3.6 | 0.25 | 0.5 | — | |
| mil | max | 51 | 8.7 | 71 | 110 | 154 | 18 | 28 | 8 | 9° |
| | min | 35 | 3.5 | 59 | 98 | 142 | 10 | 20 | — | |

The recommended mounting pad size



Marking

| Type number | Marking code |
|-------------|--------------|
| BAT54WA | L4 |