

### **30V N-Channel Enhancement Mode MOSFET**

#### Description

The AP100N03P/T uses advanced trench technology

to provide excellent R<sub>DS(ON)</sub>, low gate charge and

operation with gate voltages as low as 4.5V. This

device is suitable for use as a Battery protection

or in other Switching application.

### **General Features**

V<sub>DS</sub> = 30V I<sub>D</sub> =100 A

 $R_{\text{DS(ON)}} < 5.5 \text{m}\Omega \textcircled{0} V_{\text{GS}} = 10 \text{V} \quad (\text{Type: } 4.5 \text{m}\Omega)$ 

### Application

Battery protection

Load switch

Uninterruptible power supply

### Package Marking and Ordering Information

Product ID	Pack	Marking	Qty(PCS)	
AP100N03P	TO-220-3L	AP100N03P XXX YYYY	1000	
AP100N03T	TO-263-3L	AP100N03T XXX YYYY	800	

### Absolute Maximum Ratings (Tc=25°Cunless otherwise noted)

Symbol	Parameter Max.		Units	
VDSS	Drain-Source Voltage	30	V	
VGSS	Gate-Source Voltage	je ±20		
I₀@T₀=25℃	Continuous Drain Current, V <sub>GS</sub> @ 10V	Drain Current, V <sub>GS</sub> @ 10V 100		
I <sub>D</sub> @T <sub>C</sub> =100℃	Continuous Drain Current, V <sub>GS</sub> @ 10V	Continuous Drain Current, V <sub>GS</sub> @ 10V 46		
IDM	Pulsed Drain Current note1	Pulsed Drain Current <sup>note1</sup> 300		
EAS	Single Pulsed Avalanche Energy note2	56	mJ	
P₀@Tc=25℃	Total Power Dissipation <sup>4</sup>	68	W	
R₀JA	Thermal Resistance Junction-ambient (Steady State) <sup>1</sup>	62	°C <b>/W</b>	
R₀JA	Thermal Resistance Junction-Ambient $^{1}$ (t ≤10s)	25	°C <b>/W</b>	
RθJC	Thermal Resistance, Junction to Case	2.2	°C <i>I</i> W	
TJ, TSTG	Operating and Storage Temperature Range	-55 to +175 °C		



永源微電子科技有限公司



### **30V N-Channel Enhancement Mode MOSFET**

Symbol	Parameter	Test Condition	Min.	Тур.	Max.	Units
V(BR)DSS	Drain-Source Breakdown Voltage	V <sub>GS</sub> =0V, I <sub>D</sub> =250µA	30	32	-	V
$\triangle BVDSS / \triangle TJ$	BVDSS Temperature Coefficient	Reference to 25°C, ID=1mA		0.028		V/°C
VGS(th)	Gate Threshold Voltage	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> =250µA	1.2	1.6	2.5	V
RDS(on)	Static Drain-Source on-Resistance note3	V <sub>GS</sub> =10V, I <sub>D</sub> =30A	-	4.5	5.5	mΩ
RDS(on)	Static Drain-Source on-Resistance note3	V <sub>GS</sub> =4.5V, I <sub>D</sub> =20A	-	8.0	9.5	mΩ
IDSS	Zero Gate Voltage Drain Current	V <sub>DS</sub> =30V, V <sub>GS</sub> = 0V,	-	-	1.0	μA
IGSS	Gate to Body Leakage Current	V <sub>DS</sub> =0V, V <sub>GS</sub> = ±20V	-	-	±100	nA
Ciss	Input Capacitance		-	1614	-	pF
Coss	Output Capacitance	V <sub>DS</sub> =15V, V <sub>GS</sub> =0V, f = 1.0MHz	-	245	-	pF
Crss	Reverse Transfer Capacitance		-	215	-	pF
Qg	Total Gate Charge		-	33.7	-	nC
Qgs	Gate-Source Charge	V <sub>DS</sub> =15V, I <sub>D</sub> =30A, V <sub>GS</sub> =10V	-	8.5	-	nC
$Q_{gd}$	Gate-Drain("Miller") Charge		-	7.5	-	nC
td(on)	Turn-on Delay Time		-	7.5	-	ns
tr	Turn-on Rise Time	V <sub>DS</sub> =15V, I <sub>D</sub> =30A, R <sub>GEN</sub> =3Ω,	-	14.5	-	ns
td(off)	Turn-off Delay Time	$V_{GS} = 10V$	-	35.2	-	ns
t <sub>f</sub>	Turn-off Fall Time		-	9.6	-	ns
IS	Maximum Continuous Drain to Source Diode Forward Current		-	-	70	А
ISM	Maximum Pulsed Drain to Source Diode Forward Current		-	-	280	А
VSD	Drain to Source Diode Forward Voltage	V <sub>GS</sub> = 0V, I <sub>S</sub> =30A	-	-	1.2	V

### Electrical Characteristics (TJ=25°C, unless otherwise noted)

Note :

 $1_{\mbox{\tiny V}}$  The data tested by surface mounted on a 1 inch2 FR-4 board with 2OZ copper.

 $2 \ensuremath{\,{\ensuremath{\scriptscriptstyle S}}}$  The data tested by pulsed , pulse width .The EAS data shows Max. rating .


3. The test cond $\leq$  300us duty cycle  $\leq$  2%, duty cycle ition is VDD=24VGS=10V,L=0.1mH,IAS=15A

4、The power dissipation is limited by 175°C junction temperature


5. The data is theoretically the same as ID and IDM, in real applications, should be limited by total power dissipation.



### **30V N-Channel Enhancement Mode MOSFET**




#### **Figure1: Output Characteristics**




VGS(V) 10 Vps=15V ID=30A 8 6 4 2 Qg(nC) 0 8 16 24 32 40 0

Figure 3:On-resistance vs. Drain Current


Figure 5: Gate Charge Characteristics



**Figure 2: Typical Transfer Characteristics** 








**Figure 6: Capacitance Characteristics** 

## Typical Characteristics


ω




### **30V N-Channel Enhancement Mode MOSFET**




#### Figure 7: Normalized Breakdown Voltage vs. Junction Temperature










#### Figure 8: Normalized on Resistance vs Junction Temperature



#### Figure 10: Maximum Continuous Drain Current








AP100N03P/T RVE3.9



### **30V N-Channel Enhancement Mode MOSFET**



٩N

Ν

Ο

2.4

0.35

All Dimensions in millimeter

永源微電子科技有限公司

2.8 0.45

С

AP100N03P/T RVE3.9

## **30V N-Channel Enhancement Mode MOSFET**

### Attention

1,Any and all APM Microelectronics products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your APM Microelectronics representative nearest you before using any APM Microelectronics products described or contained herein in such applications.

2,APM Microelectronics assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all APM Microelectronics products described or contained herein.

3, Specifications of any and all APM Microelectronics products described or contained here instipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

4, APM Microelectronics Semiconductor CO., LTD. strives to supply high quality high reliabilityproducts. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. Whendesigning equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

5, In the event that any or all APM Microelectronics products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

6, No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of APM Microelectronics Semiconductor CO., LTD.

7, Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. APM Microelectronics believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

8, Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the APM Microelectronics product that you Intend to use.

永源微電子科技有限公司

ന



### **30V N-Channel Enhancement Mode MOSFET**

Edition	Date	Change	
Rve3.8	2018/1/31	Initial release	
Rve3.9	2019/12/01	Reduce RDS(on) and QG Ciss	

Copyright Attribution"APM-Microelectronice"

J