

### **DEVICE DESCRIPSION**

The TL432 is a three-terminal adjustable shunt regulator highly accurate 1.25V bandgap reference with a 0.5% tolerance. The device offers thermal stability, wide operating current (50mA) and an extended temperature range of 0 to  $105^{\circ}$ C for operation in power supply applications.

The TL432 offers a wide perating voltage range of up to 18V and is an excellent choice for voltage reference requirements in an isolated feedback circuit for 3.0V to 3.3V switching mode power supplies.

The tight tolerance quarantees a lower design cost for the power supply manufacturer by virtually eliminating the need for an extra power supply manufacturing process of the power supply.

#### **FEATURES**

Wide Programmable Prise Output Voltage from 1.25V to 18V.

Low Dynamic Output Resistance:  $0.05\Omega$  Typical.

High Sink Current Capacity from 55uA-100mA.

Low Equivalent Full-Range Temperature Coefficient : 20PPM/°C Typical.

Wide Operating Range of -40 to  $125^{\circ}$ C.

#### APPLICATION


Shunt Regulator High-Current Shunt Regulator Precision Current Limiter

### Package Marking and Ordering Information


Product ID	Pack	Marking	Qty(PCS)
TL432	SOT-23	432	3000

### Absolute Maximum Ratings(Ta=25℃)

Symbol	Parameter	Value	Unit
V <sub>KA</sub>	Cathode Voltage	18	V
IKA	Cathode Current Range (Continuous)	100	mA
I <sub>ref</sub>	Reference Input Current Range	6	μA
PD	Power Dissipation	350	mW
$R_{\Theta JA}$	Thermal Resistance From Junction To Ambient	357	°C/W
T」,T <sub>stg</sub>	Operation Junction And Storage Temperature Range	-40~+125	°C







## **Equivalent Circuit**




## Electrical Characteristics (Ta=25°C unless otherwise specified)


Symbol	Parameter	Test conditions	Min	Тур	Max	Unit
V <sub>ref</sub>	Reference input voltage	VKA=VREF, IKA=10mA	1.225		1.275	V
$ riangle V_{ref} /  riangle T$	Deviation of reference input voltage over temperature (note)	V <sub>KA</sub> =V <sub>REF</sub> , I <sub>KA</sub> =10mA, T <sub>MIN</sub> ≤Ta≤T <sub>MAX</sub>		4.5	16	mV
$ riangle V_{ref} /  riangle V_{KA}$	Ratio of change in reference input voltage to the change in cathode voltage	I <sub>KA</sub> =10mA, $ riangle V_{KA}$ =1.25V $\sim$ 18V			2.4	mV/V
I <sub>ref</sub>	Reference input current	I <sub>KA</sub> =10mA, R1=10KΩ, R2=∞			0.5	μA
$\triangle I_{ref} / \triangle T$	Deviation of reference input current over full temperature range	I <sub>KA</sub> =10mA, R1=10KΩ, R2=∞ T <sub>A</sub> =0 to 70℃			0.6	μA
I <sub>KA(min)</sub>	Minimum cathode current for regulation	V <sub>KA</sub> =V <sub>REF</sub>			0.1	mA
I <sub>KA(OFF)</sub>	Off-state cathode current	V <sub>KA</sub> =36V, V <sub>REF</sub> =0			0.5	μA
ZKA	Dynamic impedance	V <sub>KA</sub> =V <sub>REF,</sub> I <sub>KA</sub> =1∼100mA, f≤1.0KHz			0.5	Ω

#### CLASSIFICATION cZVref

Rank	<sup></sup> 0.5%	1%
Range	2.487-2.513	2.475-2.525

# **Typical Characteristics**





1225


1200

1175


-40

15







**Test Circuit** 




Test Circuit for I<sub>ref</sub>



Test Circuit for Ioff







Test Circuit for  $V_{KA}=V_{ref}(1+R1/R2)+R1*I_{ref}$ 


Test Circuit for  $V_{KA}\!\!=\!\!V_{ref}$ 



# **SOT-23 Package Outline Dimensions**








Symbol	Dimensions In Millimeters		Dimensions In Inches		
	Min	Max	Min	Max	
Α	0.900	1.150	0.035	0.045	
A1	0.000	0.100	0.000	0.004	
A2	0.900	1.050	0.035	0.041	
b	0.300	0.500	0.012	0.020	
С	0.080	0.150	0.003	0.006	
D	2.800	3.000	0.110	0.118	
Е	1.200	1.400	0.047	0.055	
E1	2.250	2.550	0.089	0.100	
e	0.950 TYP		0.037	' TYP	
e1	1.800	2.000	0.071	0.079	
L	0.550 REF		0.022 REF		
L1	0.300	0.500	0.012	0.020	
θ	0°	8°	0°	8°	

# SOT-23 Suggested Pad Layout



Note: 1.Controlling dimension:in millimeters.

General tolerance:± 0.05mm.
 The pad layout is for reference purposes only.



## **Attention**

Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.

• HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.

• Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

• HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other

give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

■ In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

• No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.

Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production.
HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.