



TECH PUBLIC

—台舟电子—

IRLML5203TRPBF

P-Channel Enhancement Mode MOSFET

www.sot23.com.tw

Product Summary

Parameter	Value	Unit
$V_{DS}$	-30	V
$R_{DS(on)}$ (Typ)	$V_{GS} = -10V$	60
	$V_{GS} = -4.5V$	85
$Q_g$	10	nC

Application


- Load/Power Switching
- Interfacing Switching
- Logic Level Shift

Package and Pin Configuration


SOT-23



Circuit diagram



Marking:



" TPM" is TECHPUBLIC MOSFET

Absolute Maximum Ratings ( $T_A=25^{\circ}C$  unless otherwise noted)

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	$V_{DS}$	-30	V
Gate-Source Voltage	$V_{GS}$	$\pm 20$	V
Continuous Drain Current <sup>(Note 1)</sup>	$I_D$	-3	A
Pulsed Drain Current <sup>(Note 2)</sup>	$I_{DM}$	-12	A
Continuous Source Current (Diode Conduction)	$I_S$	-1.7	A
Power Dissipation	$P_D$	$T_a = 25^{\circ}C$	1.25
		$T_a = 75^{\circ}C$	0.8
Operating Junction Temperature	$T_J$	+150	$^{\circ}C$
Storage Temperature Range	$T_{STG}$	-50 to +150	$^{\circ}C$



**Thermal Performance**

Parameter	Symbol	Limit	Unit
Thermal Resistance - Junction to Case	$R_{\theta JC}$	75	$^{\circ}C/W$
Thermal Resistance - Junction to Ambient	$R_{\theta JA}$	130	$^{\circ}C/W$

**Electrical Characteristics ( $T_J=25^{\circ}C$ , unless otherwise noted)**

Parameter	Conditions	Symbol	Min	Typ	Max	Unit
<b>Static</b>						
Drain-Source Breakdown Voltage	$V_{GS} = 0V, I_D = -250\mu A$	$BV_{DSS}$	-30	--	--	V
Drain-Source On-State Resistance	$V_{GS} = -10V, I_D = -3A$	$R_{DS(ON)}$	--	60	90	$m\Omega$
	$V_{GS} = -4.5V, I_D = -2A$		--	75	110	$m\Omega$
Gate Threshold Voltage	$V_{DS} = V_{GS}, I_D = -250\mu A$	$V_{GS(TH)}$	-1	--	-3	V
Zero Gate Voltage Drain Current	$V_{DS} = -30V, V_{GS} = 0V$	$I_{DSS}$	--	--	-1.0	$\mu A$
Gate Body Leakage	$V_{GS} = \pm 20V, V_{DS} = 0V$	$I_{GSS}$	--	--	$\pm 100$	nA
Forward Transconductance <sup>(Note 4)</sup>	$V_{DS} = -10V, I_D = -6A$	$g_{fs}$	--	5	--	S
Diode Forward Voltage	$I_S = -1.7V, V_{GS} = 0V$	$V_{SD}$			-1.2	V
<b>Dynamic</b>						
Total Gate Charge <sup>(Note 3,4)</sup>	$V_{DS} = -15V, I_D = -3A,$ $V_{GS} = -10V$	$Q_g$	--	10	15	nC
Gate-Source Charge <sup>(Note 3,4)</sup>		$Q_{gs}$	--	1.9	--	
Gate-Drain Charge <sup>(Note 3,4)</sup>		$Q_{gd}$	--	2	--	
Input Capacitance	$V_{DS} = -30V, V_{GS} = 0V,$ $f = 1.0MHz$	$C_{iss}$	--	565	--	pF
Output Capacitance		$C_{oss}$	--	126	--	
Reverse Transfer Capacitance		$C_{rss}$	--	75	--	
<b>Switching</b>						
Turn-On Delay Time <sup>(Note 3,4)</sup>	$V_{DD} = -15V, R_L = 15\Omega,$ $I_D = -1A, V_{GEN} = -10V,$ $R_G = 6\Omega$	$t_{d(on)}$	--	10	20	ns
Turn-On Rise Time <sup>(Note 3,4)</sup>		$t_r$	--	9	20	
Turn-Off Delay Time <sup>(Note 3,4)</sup>		$t_{d(off)}$	--	27	50	
Turn-Off Fall Time <sup>(Note 3,4)</sup>		$t_f$	--	7	16	



Typical Electrical and Thermal Characteristics




Figure 1. Output Characteristics




Figure 2. On-Resistance Variation with Temperature




Figure 3. Gate Threshold Variation with Temperatures




Figure 4. On-Resistance Variation with Drain Current




Figure 5. Capacitance Variation with Drain-source Voltage





Figure 6. Maximum Safe Operating Area



SOT-23 Package Information



Symbol	Dimensions in Millimeters	
	MIN.	MAX.
A	0.900	1.150
A1	0.000	0.100
A2	0.900	1.050
b	0.300	0.500
c	0.080	0.150
D	2.800	3.000
E	1.200	1.400
E1	2.250	2.550
e	0.950TYP	
e1	1.800	2.000
L	0.550REF	
L1	0.300	0.500
$\theta$	0°	8°

Marking:

