

SuperESD - SR05

1. Description

The SR05 is Ultra low capacitance double rail-to-rail Electro Static Discharge (ESD) protection diode in a small SOT143 Surface Mounted Device (SMD) plastic package designed to protect two Hi-Speed data lines or high frequency signal lines from the damage caused by ESD and other transients.

2. Features

- IEC 61000-4-2 Level 4 ESD Protection
 - ±15kV Contact Discharge
 - ±15kV Air Discharge
- IEC61000-4-4 (EFT) 40A (5/50ns)
- IEC61000-4-5 (Surge) 5A (8/20µs)

- Protect two I/O lines
- Low operating and clamping voltage
- Low leakage current
- Solid-state silicon technology

3. Applications

- USB 2.0
- DVI and HDMI interfaces
- Mobile and cordless phones
- Personal Digital Assistants (PDA)

- Digital cameras
- PCs, notebooks, printers and other PC peripherals

4. Ordering Information

Part Number	Package	Marking	Material	Packing	Quantity Flammability per reel Rating		Reel Size
SR05	SOT-143	R05	Halogen free	Tape & Reel	3,000 PCS	UL 94V-0	7 inches

Table-1 Ordering information

5. Pin Configuration and Functions

SR05 Rev-1.1

Pin	Name	Description	Outline	Circuit Diagram
1	GND	Connect to GND	4 3	°4 3°
2	Ю	Connect to IO	DOE I	
3	Ю	Connect to IO	R05	
4	Vcc	Connect to Vcc	1 2	°1 2°

Table-2 Pin configuration

6. Specification

6.1. Absolute Maximum rating

Over operating free-air temperature range (unless otherwise noted)

Parameters	Symbol	Min.	Max.	Unit
Peak pulse power (tp=8/20us)@25°C	P_{pk}	-	75	W
Peak pulse current (tp=8/20us)@25°C	I _{PP}		5	А
ESD (IEC61000-4-2 air discharge) @25°C	V_{ESD}	-	±15	kV
ESD (IEC61000-4-2 contact discharge) @25°C	V_{ESD}	-	±15	kV
Junction temperature	TJ	-	150	°C
Operating temperature	T _{OP}	-40	125	°C
Storage temperature	T _{STG}	-55	150	°C
Lead temperature	TL	-	260	°C

Table-3 Absolute Maximum rating


6.2. Electrical Characteristics

At $TA = 25^{\circ}C$ unless otherwise noted


Parameter	Symbol	Conditions	Min.	Тур.	Max.	Units
Reverse Stand-off Voltage	V_{RWM}				5	V
Reverse Breakdown Voltage	V _{BR}	IT=1mA	6			V
Reverse Leakage Current	I _R	V _{RWM} =5V			1	uA
Clamping Voltage	Vc	I _{PP} =1A; tp=8/20us		10		V
Clamping Voltage	Vc	I _{PP} =5A; tp=8/20us		15		V
Junction Capacitance	Сл	V _R =0V; f=1MHz I/O pin to I/O pin		0.6		pF
Junction Capacitance	Сл	V _R =0V; f=1MHz I/O pin to GND		1.2		pF

Table-4 Electrical Characteristics

Symbol	Parameters					
V_{RWM}	Peak Reverse Working Voltage					
I _R	Reverse Leakage Current @ V _{RWM}					
V _{BR}	Breakdown Voltage @ I⊤					
Ι _Τ	Test Current					
I _{PP}	Maximum Reverse Peak Pulse Current					
Vc	Clamping Voltage @ IPP					
l _F	Forward Current					
VF	Forward Voltage @ I _F					




7. Typical Characteristic



Rev-1.1


8. Typical Application




Typical Interface Application

9. Dimension







SOT-143




All dimension in millimeters

Symbol	Α	В	С	D	Е	F	G	Н	J	K
Min	2.70	1.10	0.90	0.78	1.80	0.37	1.59	0.02	0.05	2.20
Max	3.10	1.50	1.10	0.88	2.00	0.43	1.79	0.10	0.15	2.60

Table-5 Product dimensions

10. Recommended Land Pattern





Note:

- 1. Controlling dimension: in millimeters
- 2. General tolerance: ±0.05mm
- 3. The pad layout is for reference only

DISCLAIMER



SR05 Rev-1.1 <u>www.Elecsuper.com</u>

ELECSUPER SUPERESD PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with ElecSuper products. You are solely responsible for

- (1) selecting the appropriate ElecSuper products for your application;
- (2) designing, validating and testing your application;
- (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements.

These resources are subject to change without notice. ElecSuper grants you permission to use these resources only for development of an application that uses the ElecSuper products described in the resource. Other reproduction and display of these resources are prohibited. No license is granted to any other ElecSuper intellectual property right or to any third party intellectual property right. ElecSuper disclaims responsibility for, and you will fully indemnify ElecSuper and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources. ElecSuper's products are provided subject to ElecSuper's Terms of Sale or other applicable terms available either on www.elecsuper.com or provided in conjunction with such ElecSuper products. ElecSuper's provision of these resources does not expand or otherwise alter ElecSuper's applicable warranties or warranty disclaimers for ElecSuper products.