

## 塑封外延快恢复整流二极管


反向电压 50 ~ 600 V

正向电流 5.0 A

## Plastic Epitaxial Fast Recovery Rectifiers

Reverse Voltage 50 ~ 600 V

Forward Current 5.0 A



### 特征 Features

- 反向漏电流低 Low reverse leakage
- 正向浪涌承受能力强 High forward surge capability
- 高信赖性 High reliability
- 高温焊接保证 High temperature soldering guaranteed:
  - 260°C/10 秒
  - 260°C/10seconds
- 引线 and 管体皆符合RoHS标准
  - Lead and body according with RoHS standard
- 型号后缀“-F”标记无卤素产品
  - Green compound with suffix "-F" on Marking

### 机械数据 Mechanical Data

- 封装外形:DO-214AB 塑封 Case:DO-214AB Molded plastic
- 环氧树脂:UL易燃等级:94V-0
  - Epoxy:UL 94V-0 rate flame retardant
- 引脚:镀锡,无铅 Lead:Pure tin plated, lead free

### 最大值和特性 TA = 25°C 除非另有规定。

### Maximum Ratings & Characteristics Ratings at 25°C ambient temperature unless otherwise specified.

参数 Parameter	符号 Symbols	MURS 505	MURS 510	MURS 520	MURS 540	MURS 560	单位 Unit
最大可重复峰值反向电压 Maximum repetitive peak reverse voltage	$V_{RRM}$	50	100	200	400	600	V
最大均方根电压 Maximum RMS voltage	$V_{RMS}$	35	70	140	280	420	V
最大直流阻断电压 Maximum DC blocking voltage	$V_{DC}$	50	100	200	400	600	V
最大正向平均整流电流 Maximum average forward rectified current	$I_{F(AV)}$	5.0					A
正向不重复浪涌电流 8.3 ms单一正弦半波 Non-repetitive peak forward surge current 8.3 ms singlehalf sine-wave	$I_{FSM}$	125					A
最大正向电压 @IF=5.0A Maximum forward voltage	$V_F$	0.93			1.30		V
最大反向电流 @V <sub>DC</sub> Maximum reverse current	$I_R$	5					μA
TA= 25°C		100					
最大反向恢复时间 IF=0.5A, IR=1.0A, IRR=0.25A MAX. reverse recovery time	$T_{RR}$	25			50		nS
典型热阻 Typical thermal resistance (Note 1)	$R_{\theta JA}$	65					°C/W
典型结电容 VR=4.0V, f=1MHz Type junction capacitance	$C_J$	210			185		pF
工作结温和存储温度 Operating junction and storage temperature rang	$T_J, T_{STG}$	-55 --- +150					°C

备注 Note:


1) 引线长度 0.375" (9.5 mm), 安装在PCB板上, 从PN结到周围环境的热阻。

1) Thermal resistance from junction to ambient at 0.375" (9.5 mm) lead length, PCB mounted.

## 特性曲线 Characteristic Curves


正向特性曲线 (典型值)

TYPICAL FORWARD CHARACTERISTIC




正向电流降额曲线

FORWARD CURRENT DERATING CURVE



浪涌特性曲线 (最大值)

MAXIMUM NON REPETITIVE  
PEAK FORWARD SURGE CURRENT



反向特性曲线

Typical Reverse Characteristics

