



Specifications规格  
 Rated额定参数:300V , 25A  
 Dielectric strength抗电强度:AC2000V/1 Minute  
 Screw Torque螺丝扭矩:1.3Nm(10.53LB. in)  
 Wire Range线径:22~12AWG  
 Temp. range操作温度:-40°C~+105°C  
 Max soldering瞬时温度:+250°C. 5s  
 Housing Material塑胶材料:PA66  
 Contact端子:Brass, Tin plating黄铜, 镀锡  
 Screw螺丝:M4.0 Steel, Ni plating M3.0, 钢, 镀镍



		9500		上海洲日电子有限公司 Shanghai Zhouri Electronics CO.,LTD	
				上海康司玛电子设备进出口有限公司 Shanghai KangSiMa Eletronic Equipment import and export Co.,LTD	
X.	±0.3	±5°	20171018 A/0		TEL:86-21-34975176/51571121
X.X	±0.2	±3°	ZR20171018-344		
X.XX	±0.15				
		物料编号		1:1	mm 图幅 A4
				: 1 1	

