


SR5150 THRU SR5200
VOLTAGE RANGE
150 to 200 Volts
CURRENT
5.0 Ampere
 Features

- Low forward voltage drop
- High current capability
- High reliability
- High surge current capability
- Epitaxial construction






DO-27

 Mechanical data

- Case : Molded plastic
- Epoxy : UL 94V-0 rate flame retardant
- Lead : Axial leads, solderable per MIL-STD-202, method 208 guaranteed
- Polarity : Color band denotes cathode end
- Mounting position : Any
- Weight : 1.10 grams

 Maximum ratings and Electrical characteristics

TYPE	SB5150	SB5200	UNIT
Maximum Recurrent Peak Reverse Voltage	150	200	V
Maximum RMS Voltage	105	140	V
Maximum DC Blocking Voltage	150	200	V
Maximum Average Forward Rectified Current	5.0		A
Peak Forward SSurge Current, 8.3ms single half sine-wave superimposed on rated load	100		A
Maximum Instantaneous Forward Voltage at 5.0A	0.85	0.87	V
Maximum DC Reverse Current at Rated DC	Ta = 25°C	0.01	mA
Blocking Voltage	Ta = 100°C	10	
Typical Junction Capacitance	380		pF
Typical Thermal Resistance ReJA	10		°C/W
Operating Temperature Range TJ	-50 - 125		°C
Storage Temperature Range TSTG	-65 - 150		°C

Note: Pulse Test : 380μs pulse width, 2% duty cycle

SR502 THRU SR510
VOLTAGE RANGE
20 to 100 Volts
CURRENT
5.0 Ampere

Figure 1. Forward Current Derating Curve

Figure 2. Maximum Non-repetitive Surge Current

Figure 3. Typical Junction Capacitance

Figure 4. Typical Forward Characteristics

Figure 5. Typical Reverse Characteristics