



REV.	SPECIFICATION	ECN NO.	APPD.
R6		BICNZ28502	



Material and plating:

Housing: PBT, UL94V-0, Beige.

Contacts: Brass.

Gold Plated on Contact Area and 80 u" min Tin or Gold Flash Plated on Solder Tail or Press Fit over 50 u" min Nickel

Electrical Characteristics:

Current Rating: 2 AMP.




Dielectric Withstanding Voltage: AC 1000V For 1 minute.

Insulator Resistance: 10⁶ MΩ min. at DC 500V.


Contact Resistance: 20mΩ max. at DC 100mA.

Operating Temperature: -55°C~+125°C .


*RoHS Compliant




Dip Type



Press Fit Type



P.C. Board Layout
(Tolerance:±0.05)



Length	1	2	W1	W2
X	4.0	2.5	13	17
Y	4.6	6.3	13	17

Pitch	Position	Rows with Contacts	Contact Arrange	P/N
2.54mm	96	a b c		9001-1396xCxxxA
	64	a - c		9001-1364xCxxxA
	32	a - -		9001-1332xCxxxA

Tolerances	Dwg No.	9001D13001		
x = ±0.5	Projection			
.x = ±0.25	Unit	mm	Scale	1:1
.xx = ±0.15	Drawn By	ZY 05/05'22		

Title:	9001 Series
	DIN41612 R Type Male

深圳市格林柏电子技术开发有限公司			
P/N:	9001-13xxxCxxxA	Ver.No.	R6
SHEET	1/1		